


## Features

- 16 Time Ranges in Single Timer (0.1 sec. to 120 min.)
- User Sets Time Ranges  
No Math – Just Flip Switches
- Instructions Right on Unit
- Fine Tuning Knob for Precision Timing
- Pin for Pin Interchangeable with Timers in the Field – No Rewiring
- AC or DC Operation
- CMOS Digital Circuitry – 0.5% Repeatable Accuracy



## OPERATION

**SINGLE SHOT**– Upon closure of the control switch, output switch operates and time period begins. The time period is not affected by duration of the control switch closure. At the end of time period, output switch returns to normal. Continuous power must be furnished to this timer.



## AC or DC OPERATED

NTE Type No.	Nom. Voltage	Contact Arr.	Input Cur. Nom.	Max. Contact Cur. @ 28VDC or 120VAC	Diag No.
R62-11AD10-12	12VAC/DC	DPDT	167mA	10A	D36
R62-11AD10-24	24VAC/DC	DPDT	83mA	10A	D36
R62-11AD10-120	120VAC/DC	DPDT	17mA	10A	D36

## ACCESSORIES


MOUNTING STYLES	DESCRIPTION	NTE TYPE NO.
SURFACE MOUNT	11-PIN OCTAL	R95-104
PANEL MOUNT	11-PIN OCTAL	R95-119
DIN RAIL MOUNT	11-PIN OCTAL	R95-114
DIN RAIL MOUNT	11-PIN OCTAL	R95-182

# R62 Series




## Programmable, DPDT, 10 Amp, AC or DC, Single Shot Time Delay Relays.

### D36



### DPDT, 2 Form "C"



## Electrical Specifications

### Contact

**Rating:** 10 Amps 240VAC or less, 1/3 HP, 240VAC or 120VAC Pilot Duty 345VA, 120VAC or 240VAC, 50/60Hz  
**Life:** 500,000 operations at full load  
**Mechanical Life:** 7,000,000 operations at no load

### Input

**Nominal Input voltage:** See Chart  
**Steady state input current:** See Chart

### Timing

**Timing adjustment modes available:** See Timing Range Chart

### Repeat Accuracy

± 0.5% – after established at steady temperature (4 hours)  
**Timing tolerance at high end of range:** -0, +10%  
**Timing tolerance at low end of range:** +0, -50%  
**Reset Time:** 60 mS typ

### Protection

**Transient:** surge test 10,000V for 20 mS  
**Dielectric Breakdown**

**Coil To Contact:** 1850 VAC  
**Across Open Contact:** 1850 VAC

### Environmental Characteristics

**Operating:** -20°C to +55°C

### Weight

**Std:** 4.5 oz (130 grams) approx.