

# Knockdown Steel 2-Post Heavy Duty Robust Rack

## *DNRRHDKB Series*

### 10-32 Front and Rear Tapped Rails



When strength and reliability is the highest priority, be sure to choose the Data/Networking Robust Rack (DNRR) from Hammond Manufacturing. Designed to support your rack mount infrastructure, regardless of the application, the DNRR includes premium features not found on most other racks.

### Features

- Weighing in at just over 75 lbs., the DNRR Heavy Duty Knockdown Series boasts a 10-Gauge steel frame which is the thickest steel rack on the market.
- Tested to nearly double the suggested load rating of 1,200 lbs, Hammond engineered the DNRR\*\*HDKB to exceed your weight expectations.
- The knockdown self-squaring design takes just minutes to assemble.
- Our automated tapping assembly provides EIA-310-D compliant tapped rails on both the front and back to ensure flexibility when mounting equipment.
- When connecting multiple racks together, Hammond provided a 1.25" cable pass-thru. In addition we added numerous tapped and non-tapped holes for mounting power distribution, cable management and other accessories.
- Includes two (2) pairs of integrated 10-32 ground studs, spaced 5/8" apart. Stud pairs are conveniently located across from each other inside the rail channel. For added convenience, a pair is located near the top of the rack, while the other at lower side.
- To keep it looking great, the DNRR undergoes a three-stage paint process which includes a coat of premium smooth black powder paint.
- Before sending the DNRR on it's way we cover the rails and base with a thick layer of cardboard to prevent any damage that may occur during transportation.
- RoHS Compliant.
- Manufactured in North America.

### Accessories

- Top Wire Management
- Universal Rack Shelf
- Two Post Mounting Adjustable Shelf
- Two Post Mounting Deep Channel Battery Shelf
- Two Post Mounting Deep Channel Shelf
- Hinged Acrylic Door Panel Cover
- Two Post Equipment Rail Depth Adapter
- Two Post Mounting Clamping Shelf
- Two Post Centered Shelf
- Two Post Mounting Keyboard & Equipment Shelf
- Adjustable Depth DIN Rail Panel
- Outlet Strips

- Cable Management
- 10-32 Countersunk Rack Screw with Plastic Cup Washer
- 10-32 Rack Screws with Pilot Point
- Rack Isolation Kit
- Rack Unit Label
- 2-Post Rack Low Profile Dolly
- Bolt Down Kit
- 10-32 Black Rack Screw with Nylon Washer
- Small Head 10-32 Thumb Screw
- Grounding
- Rack Panels
- Light Duty Caster Set for Open Frame Rack
- Rack and Cabinet Baying/Ganging/Joining Kit

Part No.	Overall Dimensions			Mounting Dimensions			
	Height	Width	Depth	Height	Width	Rack Units	Wt. lbs.
<b>DNRR63HDKB</b>	69.13	20.00	15.00	63.00	19.00	36U	77
<b>DNRR70HDKB</b>	76.13	20.00	15.00	70.00	19.00	40U	80
<b>DNRR77HDKB</b>	83.13	20.00	15.00	77.00	19.00	44U	82
<b>DNRR84HDKB</b>	90.13	20.00	15.00	84.00	19.00	48U	87

*Data subject to change without notice*