



Type GTC 23 and 24

Mechanical Grounding T&B Catalog Number:

UPC Number:
Status:
Description:

GTC24
78378633313
Active

Copper Tower Ground Clamp for Wire Range 2/0 Str. - 250 kcmil

Features

Castings of high-strength, corrosion-resistant copper alloy. Bolt features square shank to prevent turning and enable clamp to be tightened with a single wrench.

These two-piece clamps are designed for connecting ground lead cable to flat metal surface - ideal for grounding substations on tower footings.

General

Style	Type GTC - Tower Clamps
Material	Copper
Wire Range	2/0 Str. - 250 kcmil

Dimension Information

A (inches)	1 61/64
B (inches)	5/8
D (inches)	3/4
E (inches)	1 15/16
G (inches)	1 3/8
H (inches)	1/2

Packaging

T&B Inner Pack	1
Package in Units	25
T&B Sold in UOM	Each
T&B Weight Per UOM	40 lbs. per 100

Application Support

Overview	Available on Website
----------	----------------------

Notes

Add suffix L to catalog number for 1/2 inch channel thickness.

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com