

Deep Channel Knockdown Steel 2-Post Robust Rack **DNRRDCK**

Series

10-32 Front and Rear Tapped Rails



Features

- Constructed in 12-gauge steel (base) and 14-gauge steel (rails).
- EIA-310-D compliant 10-32 front and rear tapped (8" deep) rails with 19" mounting.
- Includes large base for freestanding support of equipment.
- Finished in smooth black powder paint.
- Knockdown design ships unassembled for easy handling and shipping protection.
- Tested to nearly double the suggested load rating of 1,200 lbs.
- RoHS Compliant.
- Manufactured in North America.

Accessories

- Universal Rack Shelf
- Two Post Mounting Clamping Shelf
- Two Post Mounting Keyboard & Equipment Shelf
- Outlet Strips
- 10-32 Black Rack Screw with Nylon Washer
- 10-32 Countersunk Rack Screw with Plastic Cup Washer
- Small Head 10-32 Thumb Screw
- Rack Panels
- Rack and Cabinet Baying/Ganging/Joining Kit
- Two Post Mounting Adjustable Shelf
- Two Post Mounting Deep Channel Battery Shelf
- Adjustable Depth DIN Rail Panel
- Hinged Acrylic Door Panel Cover
- Cable Management
- 10-32 Rack Screws with Pilot Point
- Grounding
- Rack Unit Label

Part No.	Overall Dimensions			Mounting Dimensions		
	Height	Width	Depth	Height	Width	Rack Units
DNRR1942DCK	45.13	20.88	26.00	42.00	19.00	24U
DNRR1970DCK	73.13	20.88	26.00	70.00	19.00	40U
DNRR1977DCK	80.13	20.88	26.00	77.00	19.00	44U

Data subject to change without notice

