

## Waber-by-Tripp Lite 6-Outlet Industrial Power Strip, 15-ft. Cord, 5-20P Plug

MODEL NUMBER: **UL620-15**



### Description

The Waber-by-Tripp Lite UL620-15 Power Strip offers a convenient method of power distribution in workbench, wallmount or floor mount applications. Includes 6 NEMA 5-15R/20R output receptacles with 1.625 inch center-to-center spacing, 15 foot AC line cord and keyhole mounting tabs for installation in a wide variety of applications. Corded, multi-outlet strip reduces cabling clutter and enables the connection of multiple electrical devices to a single AC wall socket. Unfiltered electrical pass-through makes UL620-15 ideal for distributing alternate waveform UPS or generator power. Features rugged all-metal housing, lighted power switch with transparent guard to prevent accidental shutoff, 20 amp resettable circuit breaker and attractive blue/gray color scheme.

PLUG/OUTLETS - Input: NEMA 5-20P/Output: 6 NEMA 5-15R/20R

ELECTRICAL - 120V AC, 50/60Hz, 20A (Requires standard NEMA 5-20R wall receptacle)

FORMAT - Corded power distribution strip

### Features

- Multi-outlet power strip offers convenient power distribution in workbench, wallmount or floor mount applications
- Includes 6 NEMA 5-15R/20R output receptacles with 1.625 inch center-to-center outlet spacing
- Lighted power switch with transparent snap-over guard to prevent accidental shutoff
- Keyhole mounting tabs for installation in a wide variety of applications
- UL1363 (USA), cUL (Canada)
- 20 amp power handling capacity with circuit breaker
- 15 foot AC line cord

## Specifications

### Highlights

- 6 outlets accept NEMA5-15P or 5-20P input plugs
- 15 ft. cord
- 12.5" length
- 20-amp circuit breaker
- Lighted master switch
- All metal housing

### Applications

- Offers multiple outlet power distribution in workbench, wallmount or floor mount applications. Unfiltered electrical pass-through makes UL620-15 ideal for distributing alternate waveform UPS or generator power to protected equipment.

### Package Includes

- UL620-15 Power Strip
- Warranty information
- Instruction manual



General Info	
RoHS	Y
OVERVIEW	
Style	Strip
OUTPUT	
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(6) 5-15/20R
Circuit Breaker (amps)	20
Outlet Spacing	1.625 in.
Outlet Orientation	Single row of 6
INPUT	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	20A 120V
Input Connection Type	Nema 5-20P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.572
Input Cord Gauge Type	12 gauge, SJT
Voltage Compatibility (VAC)	120
USER INTERFACE, ALERTS & CONTROLS	
Switches	Lighted 2 position switch controls power to all outlets
Locking Switch Cover	Transparent on/off switch cover prevents accidental turn-off
PHYSICAL	
Unit Dimensions (hwd / in.)	12.5 x 2.5 x 1.5
Unit Dimensions (hwd / cm)	31.75 x 6.35 x 3.8
Material of Construction	Metal
Integrated Keyhole Mounting Tabs	Keyhole mounting tabs enable mounting to a variety of surfaces
Receptacle Color	Black
Color (AC Line Cord)	Black
Outlets Measurement (Center to Center)	41.3mm
Keyhole Slot Mounting Measurement (Center to Center)	261.92mm



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<b>CERTIFICATIONS</b>	
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All trademarks are the sole property of their respective owners. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Photos may differ slightly from final products.