

Features

- ◆ Highest power density 30W converter!
Ultra compact size: 1.0" x 1.0" x 0.4"
- ◆ Shielded metal case with isolated baseplate
- ◆ Ultrawide 4:1 input voltage range
- ◆ Very high efficiency across full load range up to 92%
- ◆ No minimum load required
- ◆ Remote On/Off control
- ◆ Operating temp. range -40°C to +80°C and up to 85 °C with heat-sink
- ◆ Over temperature protection
- ◆ Output voltage adjustable
- ◆ I/O isolation voltage 1500 VDC
- ◆ RoHS 2011/65/EU compliant
- ◆ 3-year product warranty



The THN-30WI series is the latest generation of high performance DC/DC converter modules with highest power density. The product achieves 30W output power while it comes in a metal case with dimensions of only 1.0"x 1.0"x 0.4".

All models have an ultra wide 4:1 input voltage range and precisely regulated output voltages, even under no load conditions. Highest efficiency across full load range makes this product very reliable and applicable in temperature ranges of up to 85°C. With a low input current at minimal load and remote On/Off control these converters are the ideal solution for battery-operated systems. Typical applications are in mobile equipments, instrumentation, distributed power architectures in communication and industrial electronics and everywhere where space on the PCB is critical.

Models

Order code	Input voltage range	Output voltage	Output current max.	Efficiency typ.
THN 30-2410WI	9 – 36 VDC (24 VDC nominal)	3.3 VDC	7000 mA	86 %
THN 30-2411WI		5.0 VDC	6000 mA	89 %
THN 30-2412WI		12 VDC	2500 mA	89 %
THN 30-2413WI		15 VDC	2000 mA	89 %
THN 30-2415WI		24 VDC	1250 mA	89 %
THN 30-2425WI*		48 VDC	625 mA	91 %
THN 30-2422WI		±12 VDC	±1250 mA	89 %
THN 30-2423WI		±15 VDC	±1000 mA	91 %
THN 30-2425WI		±24 VDC	±625 mA	91 %
THN 30-4810WI	18 – 75 VDC (48 VDC nominal)	3.3 VDC	7000 mA	87 %
THN 30-4811WI		5.0 VDC	6000 mA	90 %
THN 30-4812WI		12 VDC	2500 mA	90 %
THN 30-4813WI		15 VDC	2000 mA	91 %
THN 30-4815WI		24 VDC	1250 mA	91 %
THN 30-4825WI*		48 VDC	625 mA	91 %
THN 30-4822WI		±12 VDC	±1250 mA	91 %
THN 30-4823WI		±15 VDC	±1000 mA	92 %
THN 30-4825WI		±24 VDC	±625 mA	92 %

* This dual ±24 VDC converter can be used as single 48 VDC converter (open common contact)

Input Specifications

Input current at no load (at nominal input voltage)	24 V models: 10 mA typ. 48 V models: 8 mA typ.
Start-up voltage	24 V models: < 9.0 VDC 48 V models: < 18 VDC
Under voltage shut down (lock-out circuit)	24 V models: 8.0 VDC typ. 48 V models: 16 VDC typ.
Surge voltage (1 sec. max.)	24 V models: 50 V max. 48 V models: 100 V max.
Reflected input ripple current	30 mAp-p typ.
Conducted noise (input)	EN 55022 level A, FCC part 15, level A with external capacitor see: application note
ESD (electrostatic discharge)	EN 61000-4-2, air ± 8 kV, contact ± 6 kV, perf. criteria A
Radiated immunity	EN 61000-4-3, 10 V/m, perf. criteria A
Fast transient / Surge	EN 61000-4-4, ± 2 kV, perf. criteria A EN 61000-4-5, ± 2 kV perf. criteria A With external input capacitor e.g. Nippon chemi-con KY 220 μ F, 100 V, ESR 48 mOhm
Conducted immunity	EN 61000-4-6, 10 Vrms, perf. criteria A
Recommended input fuse (slow blow)	24 V models: 6300 mA 48 V models: 3150 mA

Output Specifications

Voltage set accuracy		±1 %
Output voltage adjustment range (see application note)	15 & 24 VDC models: other single output models:	+20 / -10 % ±10 %
Regulation	- Input variation ($V_{min} - V_{max}$) single output models: dual output models: - Load variation (0 – 100 %) single output models: dual output models balanced load: dual output models unbalanced load (25% /100%):	0.2 % max. 0.5 % max. 0.2 % max. 1.0 % max. 5.0 % max.
Minimum load		not required
Ripple and noise (measured with output capacitor) (20 MHz bandwidth)	3.3 & 5.0 VDC models: 12 & 15 VDC models: 24 VDC models: dual output models:	75 mVp-p with (22µF/25V X7R 1812 MLCC) 75 mVp-p with (2x 22µF/25V X7R 1812 MLCC) 75 mVp-p with (2x 6.8µF/50V X7R 1812 MLCC) 60 mVp-p with (10µF/50V X7R 1812 MLCC)
Temperature coefficient		±0.02 %/K
Output current limitation		at 170 % of Iout max.
Short circuit protection		hiccup, automatic recovery
Over voltage protection	3.3 VDC models: 5 VDC models: 12 VDC models: 15 VDC models: 24 VDC models:	3.7 – 5.4 Vout 5.6 – 7.0 Vout 13.5 – 19.6 Vout 18.3 – 22.0 Vout 29.1 – 32.5 Vout
Start up time (nominal Vin and constant resistive load)		30 ms max. (for power on and remote on)
Transient response setting time		250 µs typ. (25% load step change)
Max. capacitive load	3.3 VDC models: 5 VDC models: 12 VDC models: 15 VDC models: 24 VDC models: ±12 VDC models: ±15 VDC models:	10'000 µF 7'200 µF 1'200 µF 1'000 µF 375 µF 750 µF (each output) 500 µF (each output)

General Specifications


Temperature ranges	– Operating without heat sink – Operating with heat sink – Case temperature – Storage	–40°C to +80°C (with derating) –40°C to +85°C (with derating) +105°C max. –55°C to +125°C
Power derating	– Operating without heat sink – Operating with heat sink	2.2 %/K above +55°C 2.5 %/K above +60°C
Thermal impedance	– Natural convection – Natural convection with heat sink	15.0°C/W 13.8°C/W
Thermal protection		shutdown at 115°C
Humidity (non condensing)		5 % to 95 % rel H max.
Reliability, calculated MTBF (MIL-HDBK-217F, at +70°C, ground benign)		1.2 Mio. h
Isolation voltage (60sec.)	– Input/Output – Input, Output/Case	1'500 VDC 1'000 VDC
Isolation capacitance	– Input/Output	1'500 pF max.
Isolation resistance	– Input/Output (500 VDC)	>1 GOhm
Remote On/Off	– On: – Off: – Off idle current:	3.0 to 15 VDC or open circuit 0 to 1.2 VDC or short circuit pin 6 and pin 2 2.0 mA
Switching frequency (fixed, pulse width modulation)	3.3 & 5.0 Vout models: other models:	275 kHz ±10% 330 kHz ±10%
Vibration and thermal shock		MIL-STD-810F
Safety standards		UL/cUL 60950-1, IEC/EN 60950-1
Safety approvals	– Online certification for UL/cUL 60950-1 – CB test report for IEC/EN 60950-1	www.ul.com -> certifications -> File e188913 copy: QQQQ2 (USA) QQQQ8 (Canada) pending

Physical Specifications

Casing material	copper
Baseplate	non conductive FR4
Potting material	silicone (UL 94V-0 rated)
Weight	16.5 g (0.58oz)
Soldering temperature	max. 265°C / 10sec.
Environmental compliance	– Reach – RoHS www.tracopower.com/products/reach-declaration.pdf RoHS directive 2011/65/EU

Application note: www.tracopower.com/products/thn30wi-application.pdf

Outline Dimensions



Pin-Out

Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+Vout	+Vout
4	Trim	Common
5	-Vout	-Vout
6	Remote On/Off	

Dimensions in [mm], () = Inch
Pin diameter $\varnothing$ 1.0 (0.04)
Pin pitch tolerances: ± 0.25 (± 0.01)
Tolerances: ± 0.5 (± 0.02)

Heat-Sink (Option)

Order code: THN-HS1

(cont.: heat-sink, thermal pad, 2 clamps)

Material: Aluminum

Finish: Anodic treatment (black)




Weight: 8 g (0.28oz) without converter

Thermal impedance after assembling: 13.8 K/W



Note:

The product label on converter has to be removed before mounting the heat-sink.
For volume orders converters will be supplied with heat-sink already mounted. Please contact factory for quotation.
Separate heat-sinks are only available for prototypes and small quantity orders.



Specifications can be changed without notice! Make sure you are using the latest documentation, downloadable at www.tracopower.com