

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [151059-0001](#)  
**Status:** **Active**  
**Overview:** SIM - Smart Card Connectors  
**Description:** Block-Style SIM Connector (0.34mm Height) with Nano-SIM Card Socket Shell, 0.50µm Gold(Au) Plating, 6 circuits, Halogen-free

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Product Specification PS-151059-0001 \(PDF\)](#)

**General**

Product Family	Memory Card Sockets
Series	<a href="#">151059</a>
Comments	Housing Height: 0.30mm; Soldertail Height: 0.04mm
Component Type	Header/Socket (Host)
Overview	<a href="#">SIM - Smart Card Connectors</a>
Product Name	Block SIM
Style	Block
Type	N/A
UPC	887191907437

**Physical**

Card Detection Switch	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Black
Durability (mating cycles max)	750
Ejector Button	No
Ejector Button Side	N/A
Entry Angle	Horizontal
Keying to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Matte Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	56.879/mg
PCB Locator	No
PCB Mounting Side	Normal
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Plating min - Mating	0.508µm
Plating min - Termination	2.032µm
Ports	1
Temperature Range - Operating	-40°C to +85°C
Termination Interface: Style	Surface Mount

**Electrical**

Current - Maximum per Contact	0.5A
Shielded	No
Voltage - Maximum	10V

**Solder Process Data**

Duration at Max. Process Temperature (seconds)	40
Lead-free Process Capability	Reflow Capable (SMT only)



*Series  
image - Reference only*

**EU RoHS**

**ELV and RoHS  
Compliant**

**REACH SVHC**

**Contains SVHC: No  
Low-Halogen Status  
Low-Halogen**

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

151059Series

**Mates With**

Nano-SIM Card

**Use With**

Nano-SIM Card

Max. Cycles at Max. Process Temperature	3
Process Temperature max. C	260

### **Material Info**

### **Reference - Drawing Numbers**

Product Specification	PS-151059-0001
Sales Drawing	SD-151059-0001

This document was generated on 12/29/2014

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**