

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

39-00-0213

Status:

Active

Overview:

Mini-Fit Jr.™ Power Connectors

Description:

Mini-Fit® Female Crimp Terminal, Tin (Sn) over Phosphor Bronze, 18-24 AWG, Reel



Series

image - Reference only

Documents:

- [Drawing \(PDF\)](#)
- [Product Specification PS-5556-001 \(PDF\)](#)
- [Product Specification PS-5556-002 \(PDF\)](#)
- [Packaging Specification PK-5556-001 \(PDF\)](#)
- [Test Summary TS-5556-002 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	5556
Application	Power
Crimp Quality Equipment	Yes
Overview	Mini-Fit Jr.™ Power Connectors
Product Name	Mini-Fit®
UPC	800754319577

Physical

Durability (mating cycles max)	30
Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.140/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	1.270µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Material Info

Old Part Number	5556-PBSP
-----------------	-----------

Reference - Drawing Numbers

Packaging Specification	PK-5556-001
Product Specification	PS-5556-001, PS-5556-002
Sales Drawing	SD-5556-SP*
Test Summary	TS-5556-002

EU RoHS

ELV and RoHS
Compliant

REACH SVHC
Contains SVHC: No
Low-Halogen Status
Low-Halogen

China RoHS



Need more information on product
environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

5556Series

Mates With

5558 Mini-Fit® Crimp Male Terminals. Mini-
Fit Jr.™ Header, Dual Row, 5566 , 5569

Use With

5557 Mini-Fit Jr.™ Receptacle Housing,
30067 Mini-Fit® TPA, 42474 Mini-Fit®
BMI Panel Mount, 5559 Mini-Fit Jr.™ Plug
Housing, Dual Row

Application Tooling | FAQ

Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.

Global

Description	Product #
Extraction Tool	0011030044
Hand Crimp Tool for Male and Female	0638190900

Crimp Terminals, 16-24 AWG Wire	
FineAdjust™	<u>0639002600</u>
Applicator for Insulation OD 2.50-2.95mm, 18-24 AWG Wire	
FineAdjust™	<u>0639002900</u>
Applicator for Insulation OD 1.65-2.05mm, 18-24 AWG Wire	
FineAdjust™	<u>0639015600</u>
Applicator for Insulation OD 1.90-2.30mm - 18-24 AWG	
FineAdjust™	<u>0639023900</u>
Applicator for Insulation OD 1.40-1.70mm - 18-24 AWG	
FineAdjust™	<u>0639024800</u>
Applicator for Insulation OD 2.50-2.95mm Optimized for 18 AWG Only	
FineAdjust™	<u>0639024900</u>
Applicator for Insulation OD 2.30-2.60mm - 18-24 AWG	
T2 Terminator™	<u>0639102600</u>
for insulation OD 2.50-2.95mm - 18-24 AWG	
T2 Terminator™ for insulation OD 1.65 – 2.05mm – 18 – 24 AWG	<u>0639102900</u>
T2 Terminator™	<u>0639115600</u>
for insulation OD 1.90-2.30mm - 18-24 AWG	
T2 Terminator™	<u>0639123900</u>
for insulation OD 1.40-1.70mm - 18-24 AWG	
T2 Terminator™	<u>0639124800</u>
for insulation OD 2.50-2.95mm optimized for 18 AWG only	
T2 Terminator™	<u>0639124900</u>
for insulation OD 2.30-2.60mm - 18-24 AWG	