

Cable Cutters (ratchet action) for steel wire armoured cables (SWA cable)



95 32 315 A



95 36 315 A



- cuts through steel wire armoured cables with a diameter of up to 45 mm / 380 mm² (e.g. 4 x 95 mm²) using one or two-handed operation
- **Sturdy. Easy to use. Stable.**
- simple handling due to low weight (800 g) and compact design (315 mm length) – can also be used in confined areas
- precision ground blades and induction hardened cutting edges cut smoothly and neatly without crushing
- innovative high leverage three-stage ratchet-drive
- support area for putting down the pliers when cutting
- not suitable for cutting ACSR cable and wire rope!
- High-grade special tool steel, forged, oil-hardened

Article No.	EAN 4003773-		Tool	Handles	Ø mm	mm ²	MCM	mm	g
95 32 315 A	078562		black lacquered	with multi-component grips	45	380	750	315	800
95 36 315 A	078579		black lacquered	insulated with multi-component grips, VDE-tested	45	380	750	315	800


technical change and errors excepted



Precision milled and induction hardened cutting edge



Cross-section of a steel wire armoured cable



Cross-section of a steel wire armoured cable

Accessories (2)

Article No.	EAN	
95 39 315 A01	4003773078586	Pivot cutter repair kit for 95 32 315 A and 95 36 315 A (ratchet action)
95 39 315 A02	4003773078593	Fixed cutter repair kit for 95 32 315 A and 95 36 315 A (ratchet action)