

Capacitor, film, 0.1 uF, +/-5% Tol, -55/+105C, General Purpose, 250 VDC@85C, Lead Spacing=5 mm



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	7.2	+0.3
H	11	+0.1
T	6	+0.1
S	5	+/-0.4
LL	4	+1.5
F	0.5	+/-0.05

Notes:

-L,H,T are nominal dimensions and do not imply a minimum.

General Information	
Supplier:	KEMET
Dielectric:	Metallized Polypropylene
Application:	General Purpose
Sub Application:	Pulse
Style:	Radial Box
Lead Form:	Cut
RoHS:	Yes

Specifications	
Capacitance:	0.1 uF
Voltage:	250 VDC
Tolerance:	+/-5%
Voltage AC:	160 VAC
Rated Temperature:	85C
Temperature Range:	-55/+105C
Dissipation Factor @ 1 kHz:	0.06%
Dissipation Factor @ 10 kHz:	0.1%
Dissipation Factor @ 100kHz:	0.3%
Insulation Resistance:	100 GOhm
Inductance:	6
Maximum dVdT:	250 v/us
Miscellaneous:	Above 85C DC and AC voltage derating is 1.25%/C

Packaging Specifications	
Package Kind:	Bulk
Package Quantity:	2000