

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [74728-0001](#)
Status: **Active**
Overview: SFP+ and SFP Interconnect Solutions
Description: SFP Cage Lightpipe Cover Assembly, 1-by-4, Rear Mount

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-74728-001 \(PDF\)](#)

General

| | |
|----------------|---|
| Product Family | I/O Connectors |
| Series | 74728 |
| Application | Module-to-Board |
| Comments | Rear mount lightpipe location |
| Component Type | Lightpipe |
| Overview | SFP+ and SFP Interconnect Solutions |
| Product Name | SFP |
| Type | N/A |
| UPC | 822348438341 |

Physical

| | |
|--------------------------------|--------------------|
| Circuits (Loaded) | N/A |
| Keying to Mating Part | None |
| Lock to Mating Part | Yes |
| Material - Metal | Copper-Nickel-Zinc |
| Material - Plating Mating | Unplated |
| Net Weight | 5.800/g |
| Orientation | N/A |
| PCB Retention | None |
| Packaging Type | Tray |
| Panel Mount | No |
| Pitch - Mating Interface | N/A |
| Polarized to Mating Part | No |
| Ports | 4 |
| Surface Mount Compatible (SMC) | No |
| Temperature Range - Operating | -55°C to +105°C |
| Termination Interface: Style | N/A |
| Wire Size AWG | N/A |


Electrical

| | |
|-------------------------------|-----|
| Current - Maximum per Contact | N/A |
| Grounding to Panel | N/A |
| Shielded | No |

Material Info

Reference - Drawing Numbers

| | |
|-----------------------|--------------|
| Product Specification | PS-74728-001 |
| Sales Drawing | SD-74728-001 |



EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Contains SVHC: No**
**Low-Halogen Status
Low-Halogen**

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[74728Series](#)

Use With

[74728 1 x 4 Cages](#)