


Two Post Centered Shelf *DNDM Series*

Features



- 16-gauge steel construction.
- The vented version provides a sturdy shelf without obstructing upward heat movement.
- Front & rear lip folded for extra strength & become equipment retainers.
- Rugged textured black powder paint finish.
- Solid version available in either 19" or 23" rack panel width.
- Tested to nearly double the suggested load rating of 200 lbs.
- Finished in textured black powder paint.
- RoHS Compliant.
- Manufactured in North America.

Accessories

- Mounting Hardware
- Hook and Loop Roll

Part No. Vented	Part No. Solid	Overall Dimensions		Rack Units	Mounting Dimensions	
		Height	Depth		Width	Depth
DNDMV19BK1	DNDMS19BK1	3.50	19.50	2U	19.00	19.39
-	DNDMS23BK1	3.50	19.50	2U	23.00	19.39

Data subject to change without notice