

Technical data sheet - LÜTZE SUPERFLEX® PLUS (C) PUR UL FEEDBACK

Encoder cables for Siemens and other systems

For highest requirements in drive technology



PUR feedback cables - C-track compatible

Identification	Type	(2×(0.5)+3×(2×0.14))
	Part-No.	111459

Use/Application/Characteristics

Application	<ul style="list-style-type: none"> • Incremental encoder cable, termination cable for tachometer sensor, brake sensor, speed sensor • Through full PUR jacket and TPE cable insulation optimally suited for c-tracks, extremely harsh operating conditions, aggressive coolants and lubricants • Especially for industrial environments, machines and plants
Characteristics	<ul style="list-style-type: none"> • High active and passive interference resistance (EMC) • Braided shield optimised for continuous flexing applications • Very good flexing strength • Low adhesion, Abrasion-resistant, Tear resistant • Hydrolysis-resistant, microbe-resistant, and rot-resistant • Weathering, ozone and UV resistant (normal lighting conditions) • Good resistance to wear and salt water • Excellent coolant and lubricant resistance • Largely resistant to oils, greases, alcohol-free benzines and kerosene (See tech. information) • Silicone free • RoHS-compliant

Technical data

28.10.2014 – Subject to technical modification

Part-No. 111459

USA: LUTZE INC.

13330 South Ridge Drive • Charlotte, NC 28273, USA
 Tel. +1 (704) 504-0222 • Fax +1 (704) 504-0223
 www.lutze.com • info@lutze.com

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
 Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
 Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2
 www.lutze.com • sales.gb@lutze.co.uk

Technical data sheet - LÜTZE SUPERFLEX® PLUS (C) PUR UL FEEDBACK

Encoder cables for Siemens and other systems

For highest requirements in drive technology

UL approval	AWM 20236	
Nominal voltage	30 V 80 °C	
Test voltage	500 V	
Insulation resistance	min. 200 MΩ × km	
Inductance	approx. 0.65 µH/m	
Temperature range	moving	-25 °C to +80 °C
	fixed	-40 °C to +80 °C
Minimum bending radius	moving	D × 12
	fixed	D × 6
Jacket material	PUR	
Burning behavior	Flame-retardant according to VDE 0482 part 265-2 DIN EN 50265-2, IEC 60332-1, UL 1581 section 1080 VW-1, CSA FT 1	
Halogen-free	according to EN 50267-2-1	
Approvals	UL/CSA/CE UL-VW-1 CSA FT1 IEC 60332-1 Halogen free per DIN EN 50264-1 EN 50267-2-1 EN 60684-2 Oil Res II RoHS	
OD-∅	0.343 inches	
Weight	86.0 Lbs/Mft	
Copper	46 Lbs/Mft	

Construction

Number of strands/cross-section	(2×(0.5)+3×(2×0.14))
Number of strands/cross-section	(2C/AWG 20 + 3 TSP AWG 26)
Strand colors	0.5: black, red
	0.14: black/brown, red/orange, green/yellow
Conductor structure	Bare copper wire, finest multi-strand according to DIN VDE 0295 class 6, IEC 60228 class 6
Conductor insulation	Special TPE conductor insulation, UL qualified
Conductor marking	Conductors colour-coded for specific system
Stranding	Conductors twisted without mechanical stress, layer pitch optimised
Banding	Non-woven material over stranded cable

28.10.2014 – Subject to technical modification

Part-No. 111459

USA: LUTZE INC.

13330 South Ridge Drive • Charlotte, NC 28273, USA

Tel. +1 (704) 504-0222 • Fax +1 (704) 504-0223

www.lutze.com • info@lutze.com

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park

Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU

Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2

www.lutze.com • sales.gb@lutze.co.uk



SYSTEMATIC TECHNOLOGY

Technical data sheet - LÜTZE SUPERFLEX® PLUS (C) PUR UL FEEDBACK

Encoder cables for Siemens and other systems


For highest requirements in drive technology

Overall shield	Braid from tinned copper wire, optical covering ≥ 85 %
Outer jacket	Full polyurethane jacket, matt, adhesion-free surface
Jacket color	green RAL 6018

General

Note	CE These products are in conformity to the EC Low Voltage Directive 73/23/EWG or 93/68/EWG respectively *Siemens and DRIVE CliQ are registered trademarks
------	--

Symbols



28.10.2014 – Subject to technical modification

Part-No. 111459

USA: LUTZE INC.

13330 South Ridge Drive • Charlotte, NC 28273, USA
Tel. +1 (704) 504-0222 • Fax +1 (704) 504-0223
www.lutze.com • info@lutze.com

United Kingdom: LÜTZE Ltd.

Unit 3, Sandy Hill Park
Sandy Way, Amington • GB-Tamworth, Staffs B77 4DU
Tel. +44 (0)1827 31333-0 • Fax +44 (0)1827 31333-2
www.lutze.com • sales.gb@lutze.co.uk



SYSTEMATIC TECHNOLOGY