



- Fast and easy tip change
- Exceptionally short heat up time
- Energy saving with standby function
- Excellent response time




- Low price interchangeable soldering tips
- Maximum heat transfer
- Improved heater sensor positioning
- Short recovery time

**WXMT-MS micro desoldering tweezers set with tweezers tips RTW2-MS and WDH60 safety rest**

Slim tweezers. Ideal for soldering and desoldering very small SMD components.  
2 x 40w | 12v | Max. temperature 450°C / 850°F | Order no. T0051320399

Chisel



RTW				RTW-MS			
Type	Ø a mm	b mm	Order no.	Type	Ø a mm	b mm	Order no.
RTW2 45°	0.7	0.4	T0054465299	RTW2MS 45°	0.7	0.4	T0054465799
RTW3 45°	3.0	1.0	T0054465399	RTW3MS 45°	3.0	1.0	T0054465899
RTW4 45°	6.0	1.0	T0054465499	RTW4MS 45°	6.0	1.0	T0054465999
RTW9	3.0	1.0	T0054466699	RTW9MS	3.0	1.0	T0054466999
RTW11	6.0	1.0	T0054466799	RTW11MS	6.0	1.0	T0054467099
RTW10	10.0	1.0	T0054466899	RTW10MS	10.0	1.0	T0054467199
RTW8	1.3	0.4	T0054466499	RTW8MS	1.3	0.4	T0054466599
				RTW7NWMS*	0.8	0.4	T0054466371

Conical



Type	Ø a mm	Order no.	Type	Ø a mm	Order no.
RTW1 45°	0.4	T005 44 651 99	RTW1MS 45°	0.4	T005 44 655 99
RTW6NW* 45°	0.2	T005 44 656 99	RTW6NWMS* 45°	0.2	T005 44 656 71

\* Non-wettable

MS tips: separate ground


**MS handles and MS tweezer cartridges have to be used together.**  
**MS tweezer cartridges are for use with MS handles only.**  
**MS tips provides separate ground.**

**MS handles for RTW-MS (WXMT-MS) soldering tips:**  
T0051317999 **WXMT-MS tweezer, no tip cartridge**  
T0051320399 **WXMT-MS tweezer with RTW2MS tips and WDH60 safety rest**

**WXP65 soldering iron set with XNTA tip and WDH10 safety rest**

Small fast soldering iron. Suitable for fine soldering jobs with a high heat demand.  
65w | 24v | Max. temperature 450°C / 850°F | Order no. T0052921299

Chisel



XNT				Type	Ø a mm	b mm	c mm	Order no.	
XNT 1SCNW*	0.3	0.1	27.0	T0054488199	XNT C	3.2	0.8	27.0	T0054485899
XNT 1SC	0.4	0.15	27.0	T0054486299	XNT D	4.0	0.8	28.0	T0054485399
XNT H	0.8	0.4	28.0	T0054485999	XNT HX 45°	0.8	0.4	36.5	T0054487399
XNT K	1.2	0.4	28.0	T0054486099	XNT 4X 45°	1.2	0.4	34.6	T0054487499
XNT A	1.6	0.4	28.0	T0054485199	XNT AX	1.6	0.8	28.0	T0054486499
XNT 6	1.6	0.4	29.5	T0054485699	XNT BX	2.4	0.8	36.5	T0054488299
XNT B	2.4	0.8	27.0	T0054485799	XNT MX	3.2	0.8	37.5	T0054488399

Sloped




Type	a mm	Order no.	Type	a mm	Order no.
XNT 4	1.2	T0054485599	XNT CC 45°	3.2	T0054488699
XNT AA 45°	1.6	T0054488499	XNT F 45°	1.2	T0054488799
XNT BB 45°	2.4	T0054488599			

Conical



Type	Ø a mm	c mm	Order no.	Type	Ø a mm	c mm	Order no.
XNT 1	0.5	27.0	T0054485099	XNT S	0.4	37.5	T0054486899

Knife



Type	Ø a mm	c mm	Order no.
XNT KN	2.0	33.0	T0054486399

\* Non-wettable