

Tube Axial Fans *DNMF Series*



Features

- Choice of 4.70" (120mm), 3.15" (80mm), 5.91" (150mm) or 10" (254mm).
- Choice of either 115 or 230 VAC, 50/60 Hz.
- Impedance protected motor.
- Class-B insulated.
- Ball bearing construction, metal or plastic blades.
- Diecast aluminum body.
- DNMF100AC, FAN150AC and FAN10A fans have male plug terminations (requires fan cords).
- FAN80AC fans have 11" long lead wires.
- Fan is cooled by incoming air.
- Fan component is recognized to UL 507 and CSA certified.
- Includes mounting hardware.



Accessories

- Fan Cords

Part No. 115 VAC	Part No. 230 VAC	Overall Dimensions			CFM	Wattage		Speed (RPM)	Noise (dB)	Use With Fan Guard Part No.	Use With Filter Grill Part No.
		Height	Width	Depth		50Hz	60Hz				
FAN80AC115	FAN80AC230	3.15	3.15	1.50	32	11	10	3100	34	FAN80FG	XPFA80*
DNMF100AC115	DNMF100AC230	4.70	4.70	1.50	105	24	22	3000	50	DNFG	XPFA120*
FAN150AC115	FAN150AC230	5.75 & 5.90	6.72	2.00 & 2.20	210 & 230	27 & 46	26 & 40	3100 & 3400	63 & 53	FAN150FG	n/a
FAN10A115	FAN10A220	10.00 dia.		3.50	550	30	35	1650	55	FAN10FG	XPFA254*

Data subject to change without notice