## Heat Shrinkable Tubing 3:1 in a Kit

## • ShrinKit 321 Universal

With ShrinKit 321 HellermannTyton has set a new standard in heat shrink tubing: ShrinKit tubings cover many applications with their ideal shrink ratio of 3:1.

## **Features and Benefits**

- Attractive and reusable kit
- Wide range of sizes, colours and lengths
- For insulation, bend protection and identification
- Case can be re-used for storing nails, screws, nuts, fish hooks, etc.
- Size of compartments changeable by simply moving yellow space dividers



ShrinKit 321 Universal.

MATERIAL	Polyolefin, cross-linked (PO-X)			
Shrink Ratio	3:1			
Operating Temperature	-55 °C to +135 °C			
Minimum Shrink Temperature	+90 °C			
Longitudinal change after shrinkage	+5%/-10% max.			
Dielectric Strength	20 kV/mm according to ASTM D 2671			
Flammability	self-extinguishing (except for transparent)			
Insulation Class	B (VDE 0530)			
Specifications	SAE - AMS - DTL-23053/5 Class 1 (colours), SAE - AMS - DTL-23053/5 Class 2 (clear)			



Heat Shrinkable Tubing 3:1



COMP.	Supplied Ø D min.	Recov. Ø d max.	Length (L)	Wall (WT)	Colour	Content (pcs.)	Article-No.
1	6.0	2.0	60.0	0.70	Black (BK)	50	380-03002
2	12.0	4.0	100.0	0.70	Black (BK)	15	
3	24.0	8.0	200.0	1.00	Black (BK)	10	
4	6.0	2.0	60.0	0.70	Green/Yellow (GNYE)	50	
5	3.0	1.0	50.0	0.55	Transparent (CL)	100	
6	3.0	1.0	50.0	0.55	Black (BK)	100	
7	12.0	4.0	100.0	0.70	Transparent (CL)	15	
8	12.0	4.0	100.0	0.70	Red (RD)	15	
9	3.0	1.0	50.0	0.55	Red (RD)	100	
10	3.0	1.0	40.0	0.55	Blue (BU)	100	
11	3.0	1.0	40.0	0.55	Green/Yellow (GNYE)	100	
12	1.5	0.5	40.0	0.45	Black (BK)	75	
12	1.5	0.5	40.0	0.45	Green/Yellow (GNYE)	75	
13	6.0	2.0	60.0	0.70	Blue (BU)	50	
14	6.0	2.0	60.0	0.70	Red (RD)	50	
15	6.0	2.0	60.0	0.70	Transparent (CL)	50	
16	12.0	4.0	170.0	0.70	Green/Yellow (GNYE)	10	
17	12.0	4.0	170.0	0.70	Blue (BU)	10	

All dimensions in mm. Subject to technical changes.



Please note! Not all products listed on this page may have this approval. For product specific approvals please refer to the Appendix.