

Flush-type connector - SACC-DSI-M 8FS-6CON-M12/0,5 - 1453465

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Sensor/actuator flush-type socket, 6-pos., M8, rear/screw mounting with M12 thread, with 0.5 m TPE litz wire, 6 x 0.14 mm²



Key commercial data

Packing unit	1 pc
GTIN	 4 046356 554398
Weight per Piece (excluding packing)	21.0 g
Custom tariff number	85444290
Country of origin	Germany
Product key	ABQBBD

Technical data

Dimensions

Length of cable	0.5 m
-----------------	-------

Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C (Socket)
Degree of protection	IP67

General

Rated current at 40°C	2 A
Rated voltage	30 V
Number of positions	6
Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Coding	A - standard
Standards/regulations	M8 connector IEC 61076-2-104
Status display	No
Surge voltage category	II
Pollution degree	3

Flush-type connector - SACC-DSI-M 8FS-6CON-M12/0,5 - 1453465

Technical data

General

Connection method	Individual wires
Mounting type	Rear mounting M12 x 1

Material

Inflammability class according to UL 94	HB
Contact material	Cu alloy
Contact surface material	Au
Contact carrier material	PUR / PA66
Material, knurls	Nickel-plated brass
Sealing material	Viton

Cable

Cable type	TPE litz wire
Conductor cross section	0.14 mm ²
AWG signal line	26
Conductor structure signal line	18x 0.10 mm
Wire colors	Black, brown, blue, white, gray, pink
Material conductor insulation	TPE
Conductor material	Tin-plated Cu litz wires
Insulation resistance	≥ 20 MΩ*km
Conductor resistance	≥ 80 Ω/km
Nominal voltage, cable	300 V
Test voltage, cable	2000 V AC
Ambient temperature (operation)	-25 °C ... 90 °C (cable, fixed installation)

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27260701
eCl@ss 5.1	27260701
eCl@ss 6.0	27279220
eCl@ss 7.0	27440103
eCl@ss 8.0	27440103

ETIM

ETIM 3.0	EC002061
ETIM 4.0	EC002061
ETIM 5.0	EC002061

Flush-type connector - SACC-DSI-M 8FS-6CON-M12/0,5 - 1453465

Classifications

UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

Approvals

Approvals


Approvals
EAC
Ex Approvals
Approvals submitted

Approval details

EAC


Drawings

Schematic diagram



Pin assignment M8 socket, 6-pos.


Dimensioned drawing



M8 flush-type socket

Flush-type connector - SACC-DSI-M 8FS-6CON-M12/0,5 - 1453465

Dimensioned drawing



Housing cutout for M8 flush-type connector, socket, one-section