

Flush-type connector - SACC-DSI-M 8FS-6CON-L180 - 1436534


Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)



Sensor/actuator flush-type connector, socket, 6-pos., M8, rear/screw mounting with M12 thread, with straight solder connection



Key commercial data

Packing unit	20 pc
Minimum order quantity	20 pc
GTIN	 4 046356 434898
Weight per Piece (excluding packing)	13.6 g
Custom tariff number	85366990
Country of origin	Germany
Product key	ABQBAB
Note	Made to Order (non-returnable)

Technical data

Ambient conditions

Ambient temperature (operation)	-25 °C ... 85 °C
Degree of protection	IP67

General

Rated current at 40°C	1.5 A
Rated voltage	30 V
Number of positions	6
Contact resistance	≤ 3 mΩ
Insulation resistance	≥ 100 MΩ
Coding	A - standard
Standards/regulations	M8 connector IEC 61076-2-104
Status display	No
Surge voltage category	II
Pollution degree	3

Flush-type connector - SACC-DSI-M 8FS-6CON-L180 - 1436534

Technical data

General

Connection method	Solder pins
Mounting type	Rear mounting M12 x 1 With locking nut

Material

Inflammability class according to UL 94	HB
Contact material	CuSn
Contact surface material	Au
Contact carrier material	PA 66
Material, knurls	Nickel-plated brass
Sealing material	NBR

Classifications

eCl@ss

eCl@ss 4.0	27250313
eCl@ss 4.1	27250313
eCl@ss 5.0	27143423
eCl@ss 5.1	27143423
eCl@ss 6.0	27143423
eCl@ss 7.0	27449001
eCl@ss 8.0	27440103

ETIM

ETIM 3.0	EC002061
ETIM 4.0	EC002061
ETIM 5.0	EC002061

UNSPSC

UNSPSC 6.01	31251501
UNSPSC 7.0901	31251501
UNSPSC 11	31251501
UNSPSC 12.01	31251501
UNSPSC 13.2	31251501

Approvals

Approvals

Approvals

EAC

Flush-type connector - SACC-DSI-M 8FS-6CON-L180 - 1436534

Approvals

Ex Approvals


Approvals submitted

Approval details


EAC

Drawings

Dimensioned drawing




Schematic diagram




Pin assignment M8 socket, 6-pos.

Housing cutout for M8 flush-type connector, socket, one-section

Dimensioned drawing



Drilling diagram



M8 flush-type socket

Drilling diagram