



SAFETY DATA SHEET

Swarfega Jizer Bio

According to Regulation (EC) No 1907/2006, Annex II, as amended by Regulation (EU) No 453/2010

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1. Product identifier

Product name Swarfega Jizer Bio
Product number JIB608RS,JIB60K,JIB76R

1.2. Relevant identified uses of the substance or mixture and uses advised against

Identified uses Detergent. . For full details regarding recommended uses please refer to the product label.

1.3. Details of the supplier of the safety data sheet

Supplier Deb Ltd
Denby Hall Way
Denby
Derbyshire
DE5 8JZ
Main Tel. 01773 855100
Technical Tel 01773 855105
reach@deb.co.uk

1.4. Emergency telephone number

Emergency telephone National Poisons Information Service (UK) 0844 8920111

SECTION 2: Hazards identification

2.1. Classification of the substance or mixture

Classification

Physical hazards Not Classified
Health hazards Skin Irrit. 2 - H315 Eye Dam. 1 - H318
Environmental hazards Not Classified

Classification (67/548/EEC or 1999/45/EC) Xi;R38,R41.

Environmental The product does not meet the requirement for classification as an environmental hazard in accordance with directive 1999/45/EEC

2.2. Label elements

Pictogram



Signal word Danger

Swarfega Jizer Bio

Hazard statements	H315 Causes skin irritation. H318 Causes serious eye damage.
Precautionary statements	P264 Wash contaminated skin thoroughly after handling. P280 Wear protective gloves/protective clothing/eye protection/face protection. P302+P352 IF ON SKIN: Wash with plenty of water. P305+P351+P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing. P332+P313 If skin irritation occurs: Get medical advice/attention. P362+P364 Take off contaminated clothing and wash it before reuse. P337+P313 If eye irritation persists: Get medical advice/attention.
Contains	REACTION PRODUCTS OF C12-18-(EVEN NUMBERED)-ALKYLAMINES & ACRYLIC ACID & SODIUM HYDROXIDE, C9-C11 ALCOHOL ETHOXYLATE + 6 MOLES ETHYLENE OXIDE, SODIUM METASILICATE, DIETHANOLAMINE
Detergent labelling	5 - < 15% non-ionic surfactants, < 5% amphoteric surfactants, < 5% EDTA and salts thereof
Supplementary precautionary statements	P302+P352 IF ON SKIN: Wash with plenty of water. P310 Immediately call a POISON CENTER/doctor. P321 Specific treatment (see medical advice on this label). P332+P313 If skin irritation occurs: Get medical advice/attention. P362 Take off contaminated clothing.

2.3. Other hazards

This product does not contain any substances classified as PBT or vPvB.

SECTION 3: Composition/information on ingredients

3.2. Mixtures

C9-C11 ALCOHOL ETHOXYLATE (6MEO)	5-10%
CAS number: 68439-46-3	
Classification Eye Dam. 1 - H318 Acute Tox. 4 - H302	Classification (67/548/EEC or 1999/45/EC) Xn;R22. Xi;R41.
SODIUM METASILICATE	1-5%
CAS number: 6834-92-0	EC number: 229-912-9
REACH registration number: 01-2119449811-37-XXXX	
Classification Skin Corr. 1B - H314 STOT SE 3 - H335 Eye Dam. 1 - H318	Classification (67/548/EEC or 1999/45/EC) C;R34. Xi;R37.

Swarfega Jizer Bio

REACTION PRODUCTS OF C12-18-(EVEN NUMBERED)- ALKYLAMINES & ACRYLIC ACID & SODIUM HYDROXIDE	1-5%
CAS number: —	EC number: 939-647-7
	REACH registration number: 01-2119980672-29-0000
Classification Skin Irrit. 2 - H315 Eye Dam. 1 - H318	Classification (67/548/EEC or 1999/45/EC) Xi;R41,R38.
DIETHANOLAMINE	1-5%
CAS number: 111-42-2	EC number: 203-868-0
Classification Acute Tox. 4 - H302 Skin Irrit. 2 - H315 Eye Dam. 1 - H318 STOT RE 2 - H373 Aquatic Chronic 3 - H412	Classification (67/548/EEC or 1999/45/EC) Xn;R22,R48/22 Xi;R38,R41
DIHYDROXYETHYL COCAMINE OXIDE	<1%
CAS number: 61791-47-7	EC number: 263-180-1
M factor (Acute) = 1	
Classification Skin Irrit. 2 - H315 Eye Dam. 1 - H318 Aquatic Acute 1 - H400	Classification (67/548/EEC or 1999/45/EC) Xi;R38,R41. N;R50.
SODIUM HYDROXIDE	<1%
CAS number: 1310-73-2	EC number: 215-185-5
	REACH registration number: 01-2119457892-27-XXXX
Classification Met. Corr. 1 - H290 Skin Corr. 1A - H314 Eye Dam. 1 - H318	Classification (67/548/EEC or 1999/45/EC) C;R35

The Full Text for all R-Phrases and Hazard Statements are Displayed in Section 16.

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation	Move affected person to fresh air at once. Get medical attention if any discomfort continues.
Ingestion	Never give anything by mouth to an unconscious person. Do not induce vomiting. Rinse mouth thoroughly with water. Get medical attention.
Skin contact	Remove affected person from source of contamination. Remove contaminated clothing. Wash skin thoroughly with soap and water. Get medical attention if irritation persists after washing.

Swarfega Jizer Bio

Eye contact Remove affected person from source of contamination. Remove any contact lenses and open eyelids wide apart. Continue to rinse for at least 15 minutes. Get medical attention if irritation persists after washing.

4.2. Most important symptoms and effects, both acute and delayed

Inhalation Irritation of nose, throat and airway.

Ingestion May cause discomfort if swallowed. May cause stomach pain or vomiting.

Skin contact This product is strongly irritating.

Eye contact This product is strongly irritating.

4.3. Indication of any immediate medical attention and special treatment needed

Notes for the doctor No specific recommendations. If in doubt, get medical attention promptly.

SECTION 5: Firefighting measures

5.1. Extinguishing media

Suitable extinguishing media The product is not flammable. Use fire-extinguishing media suitable for the surrounding fire.

5.2. Special hazards arising from the substance or mixture

Hazardous combustion products Does not decompose when used and stored as recommended.

5.3. Advice for firefighters

Protective actions during firefighting No specific firefighting precautions known.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Personal precautions Wear protective clothing as described in Section 8 of this safety data sheet.

6.2. Environmental precautions

Environmental precautions Collect and dispose of spillage as indicated in Section 13. Avoid discharge to the aquatic environment.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Stop leak if possible without risk. Absorb in vermiculite, dry sand or earth and place into containers. Flush contaminated area with plenty of water. Avoid contamination of ponds or watercourses with washing down water.

6.4. Reference to other sections

Reference to other sections For personal protection, see Section 8. For waste disposal, see Section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Usage precautions Avoid spilling. Avoid contact with skin and eyes.

7.2. Conditions for safe storage, including any incompatibilities

Storage precautions Store in closed original container at temperatures between 0°C and 30°C.

Storage class Chemical storage.

7.3. Specific end use(s)

Swarfega Jizer Bio

Specific end use(s) The identified uses for this product are detailed in Section 1.2.

SECTION 8: Exposure Controls/personal protection

8.1. Control parameters

Occupational exposure limits

SODIUM HYDROXIDE

Short-term exposure limit (15-minute): WEL 2 mg/m³

WEL = Workplace Exposure Limit

Ingredient comments EU = Indicative Values according to Commission Directive 91/322/EEC.

SODIUM METASILICATE (CAS: 6834-92-0)

DNEL	Workers - Inhalation; Long term systemic effects: 6.22 mg/m ³ Workers - Dermal; Long term systemic effects: 1.49 mg/kg/day General population - Inhalation; Long term systemic effects: 1.55 mg/m ³ General population - Dermal; Long term systemic effects: 0.74 mg/kg/day General population - Oral; Long term systemic effects: 0.74 mg/kg/day
PNEC	- Fresh water; 7.5 mg/l - Marine water; 1 mg/l - STP; 1000 mg/l

REACTION PRODUCTS OF C12-18-(EVEN NUMBERED)-ALKYLAMINES & ACRYLIC ACID & SODIUM HYDROXIDE

DNEL	Professional - Dermal; Long term systemic effects: 5.3 mg/kg/day Professional - Inhalation; Long term systemic effects: 3.8 mg/m ³ Consumer - Dermal; Long term systemic effects: 2.7 mg/kg/day Consumer - Inhalation; Long term systemic effects: 0.9 mg/m ³ Consumer - Oral; Long term systemic effects: 0.3 mg/kg/day
PNEC	- Marine water; 0.0003 mg/l - Soil; 0.0041 mg/kg - Fresh water; 0.03 mg/l - Sediment (Freshwater); 0.108 mg/kg - Intermittent release; 0.042 mg/l - STP; 9.9 mg/l - Sediment (Marinewater); 0.0108 mg/kg

DIETHANOLAMINE (CAS: 111-42-2)

DNEL	Workers - Inhalation; Long term local effects: 1 mg/m ³ Workers - Dermal; Long term systemic effects: 0.13 mg/kg/day General population - Inhalation; Long term local effects: 0.25 mg/m ³ General population - Dermal; Long term systemic effects: 0.07 mg/kg/day General population - Oral; Long term systemic effects: 0.06 mg/kg/day
-------------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Swarfega Jizer Bio

PNEC	<ul style="list-style-type: none"> - Fresh water; 0.0022 mg/l - Marine water; 0.00022 mg/l - Intermittent release; 0.022 mg/l - Sediment (Freshwater); 0.012 mg/kg - Sediment (Marinewater); 0.0012 mg/kg - Soil; 0.0011 mg/kg - ;
-------------	---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

TETRASODIUM ETHYLENE DIAMINE TETRAACETATE (CAS: 64-02-8)

DNEL	<ul style="list-style-type: none"> Consumer - Oral; Long term systemic effects: 28 mg/kg/day Professional - Inhalation; Short term systemic effects: 2.8 mg/m³ Professional - Inhalation; Long term local effects: 2.5 mg/m³ Consumer - Inhalation; Short term systemic effects: 1.5 mg/m³ Professional - Inhalation; Long term systemic effects: 2.5 mg/m³ Consumer - Inhalation; Long term local effects: 1.5 mg/m³ Professional - Inhalation; Short term systemic effects: 2.5 mg/m³ Professional - Inhalation; Short term local effects: 2.5 mg/m³
-------------	-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

PNEC	<ul style="list-style-type: none"> - Fresh water; 2.2 mg/l - Soil; 0.72 mg/kg - STP; 43 mg/l - Marine water; 0.22 mg/l - ; Intermittent release 1.2 mg/l
-------------	-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

SODIUM HYDROXIDE (CAS: 1310-73-2)

DNEL	<ul style="list-style-type: none"> Industry - Inhalation; Long term local effects: 1 mg/m³ Consumer - Inhalation; Long term local effects: 1 mg/m³
-------------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

8.2. Exposure controls

Protective equipment



Eye/face protection

Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible. The following protection should be worn: Chemical splash goggles or face shield.

Hand protection

Chemical-resistant, impervious gloves complying with an approved standard should be worn if a risk assessment indicates skin contact is possible. The most suitable glove should be chosen in consultation with the glove supplier/manufacturer, who can provide information about the breakthrough time of the glove material. Wear protective gloves made of the following material: Neoprene. Nitrile rubber. Polyethylene. Polyvinyl chloride (PVC).

Other skin and body protection

Wear appropriate clothing to prevent any possibility of skin contact.

Hygiene measures

Wash hands at the end of each work shift and before eating, smoking and using the toilet. Wash promptly if skin becomes contaminated. Promptly remove any clothing that becomes contaminated.

SECTION 9: Physical and Chemical Properties

9.1. Information on basic physical and chemical properties

Swarfega Jizer Bio

Appearance	Clear liquid.
Colour	Green.
Odour	Characteristic.
Odour threshold	Not determined. Not determined.
pH	Not determined.
Melting point	Not determined.
Initial boiling point and range	Not determined.
Flash point	Not determined.
Evaporation rate	Not determined.
Upper/lower flammability or explosive limits	Scientifically unjustified. : : Scientifically unjustified.
Vapour pressure	Not determined.
Vapour density	Not determined.
Relative density	1.045-1.060 @ at 25 deg C°C
Solubility(ies)	Soluble in water.
Auto-ignition temperature	Scientifically unjustified.
Decomposition Temperature	Not determined.
Viscosity	Not determined.
Explosive properties	Scientifically unjustified.
Oxidising properties	Does not meet the criteria for classification as oxidising.
9.2. Other information	
Other information	Not relevant.

SECTION 10: Stability and reactivity

10.1. Reactivity

Reactivity The following materials may react with the product: Acids.

10.2. Chemical stability

Stability Stable at normal ambient temperatures.

10.3. Possibility of hazardous reactions

Possibility of hazardous reactions Not applicable.

10.4. Conditions to avoid

Conditions to avoid Avoid excessive heat for prolonged periods of time. Avoid freezing.

10.5. Incompatible materials

Materials to avoid Strong acids.

10.6. Hazardous decomposition products

Hazardous decomposition products Does not decompose when used and stored as recommended.

Swarfega Jizer Bio

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity - oral

ATE oral (mg/kg) 7,142.85714286

Skin corrosion/irritation

Animal data Irritating.

Serious eye damage/irritation

Serious eye damage/irritation Based on available data the classification criteria are not met.

Skin sensitisation

Skin sensitisation Based on available data the classification criteria are not met.

Germ cell mutagenicity

Genotoxicity - in vivo Based on available data the classification criteria are not met.

Carcinogenicity

Carcinogenicity Does not contain any substances known to be carcinogenic.

Reproductive toxicity

Reproductive toxicity - fertility Does not contain any substances known to be toxic to reproduction.

Specific target organ toxicity - single exposure

STOT - single exposure Not classified as a specific target organ toxicant after a single exposure.

Specific target organ toxicity - repeated exposure

STOT - repeated exposure Not classified as a specific target organ toxicant after repeated exposure.

Aspiration hazard

Aspiration hazard Not anticipated to present an aspiration hazard based on chemical structure.

Inhalation

May cause respiratory system irritation.

Ingestion

May cause discomfort if swallowed.

Skin contact

Irritating to skin.

Eye contact

Irritating to eyes.

Toxicological information on ingredients.

C9-C11 ALCOHOL ETHOXYLATE (6MEO)

Acute toxicity - dermal

Acute toxicity dermal (LD₅₀ 2,000 mg/kg)

Species Rat

SODIUM METASILICATE

Acute toxicity - oral

Notes (oral LD₅₀) LD50 1152 1349 mg/kg bw Rat

Acute toxicity - dermal

Swarfega Jizer Bio

Notes (dermal LD₅₀) LD50 > 5000 mg/kg bw Rat

Acute toxicity - inhalation

Notes (inhalation LC₅₀) LC50 > 2.06 mg/L air Rat

Skin corrosion/irritation

Animal data Primary dermal irritation index: 8

REACTION PRODUCTS OF C12-18-(EVEN NUMBERED)-ALKYLAMINES & ACRYLIC ACID & SODIUM HYDROXIDE

Acute toxicity - oral

Acute toxicity oral (LD₅₀ mg/kg) 31,300

Species Rat Rat

ATE oral (mg/kg) 31,300.0

Acute toxicity - dermal

Acute toxicity dermal (LD₅₀ mg/kg) 5,000

Species Rat Rat

ATE dermal (mg/kg) 5,000.0

DIETHANOLAMINE

Acute toxicity - oral

Acute toxicity oral (LD₅₀ mg/kg) 1,100.0

Species Rat

ATE oral (mg/kg) 500

Skin corrosion/irritation

Animal data Erythema/eschar score: Very slight erythema - barely perceptible (1).

Skin sensitisation

Skin sensitisation Guinea pig maximization test (GPMT) - Guinea pig: Not sensitising.

SECTION 12: Ecological Information

Ecotoxicity The product components are not classified as environmentally hazardous. However, large or frequent spills may have hazardous effects on the environment. The product does not meet the requirement for classification as an environmental hazard in accordance with directive 1999/45/EEC

12.1. Toxicity

Toxicity The product does not meet the requirement for classification as an environmental hazard in accordance with directive 1999/45/EEC

12.2. Persistence and degradability

Swarfega Jizer Bio

Persistence and degradability The surfactant(s) contained in this product complies(comply) with the biodegradability criteria as laid down in Regulation (EC) No. 648/2004 on detergents. Data to support this assertion are held at the disposal of the competent authorities of the Member States and will be made available to them at their direct request, or at the request of a detergent manufacturer.

12.3. Bioaccumulative potential

Bioaccumulative potential No data available on bioaccumulation.

12.4. Mobility in soil

Mobility The product is soluble in water. The product is non-volatile.

12.5. Results of PBT and vPvB assessment

Results of PBT and vPvB assessment None known.

12.6. Other adverse effects

Other adverse effects None known.

SECTION 13: Disposal considerations

13.1. Waste treatment methods

General information Waste should be treated as controlled waste. Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

Disposal methods Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority. No specific disposal method required. Reuse or recycle products wherever possible.

SECTION 14: Transport information

Road transport notes Not classified.

Rail transport notes Not classified.

Sea transport notes Not classified.

14.1. UN number

Not applicable.

14.2. UN proper shipping name

Not applicable.

14.3. Transport hazard class(es)

Not applicable.

14.4. Packing group

Not applicable.

14.5. Environmental hazards

Environmentally hazardous substance/marine pollutant

No.

14.6. Special precautions for user

Not applicable.

14.7. Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code

Swarfega Jizer Bio

Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code Not applicable.

SECTION 15: Regulatory information

15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

EU legislation

Dangerous Substances Directive 67/548/EEC.
 Dangerous Preparations Directive 1999/45/EC.
 Regulation (EC) No 1907/2006 of the European Parliament and of the Council of 18 December 2006 concerning the Registration, Evaluation, Authorisation and Restriction of Chemicals (REACH) (as amended).
 Regulation (EC) No 1272/2008 of the European Parliament and of the Council of 16 December 2008 on classification, labelling and packaging of substances and mixtures (as amended).

15.2. Chemical safety assessment

No chemical safety assessment has been carried out.

SECTION 16: Other information

General information Only trained personnel should use this material.

Key literature references and sources for data Where Exposure Scenarios for the substances listed in Section 3 are available they have been assessed for the uses identified in this data sheet or on the product label and the appropriate relevant information is incorporated into this Safety Data Sheet.

Revision comments Revision of information NOTE: Lines within the margin indicate significant changes from the previous revision.

Revision date 08/05/2015

Revision 1

Supersedes date 08/01/2013

Risk phrases in full

R22 Harmful if swallowed.
 R34 Causes burns.
 R37 Irritating to respiratory system.
 R38 Irritating to skin.
 R41 Risk of serious damage to eyes.
 R48/22 Harmful: danger of serious damage to health by prolonged exposure if swallowed.
 R50 Very toxic to aquatic organisms.

Hazard statements in full

H302 Harmful if swallowed.
 H314 Causes severe skin burns and eye damage.
 H315 Causes skin irritation.
 H318 Causes serious eye damage.
 H335 May cause respiratory irritation.
 H373 May cause damage to organs through prolonged or repeated exposure.
 H400 Very toxic to aquatic life.
 H412 Harmful to aquatic life with long lasting effects.

Notes for Risk Phrases and Hazard Statements in Full The full text for Risk Phrases and Hazard Statements in section 16 relates to the reference numbers in sections 2 and 3 and not necessarily the finished product classification.

Swarfega Jizer Bio

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.