

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0016020102](#)  
**Status:** **Active**  
**Overview:** [C-Grid® Products](#)  
**Description:** SL™ Crimp Terminal, Series 70058, Female, with Tin (Sn) Plated Contact, 22-24 AWG, Bag

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Test Summary TS-70058-001 (PDF)</a>
<a href="#">Product Specification PS-70058 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-70400 (PDF)</a>	

**General**

Product Family	Crimp Terminals
Series	<a href="#">70058</a>
Application	Signal
Crimp Quality Equipment	Yes
Overview	<a href="#">C-Grid® Products</a>
Packaging Alternative	<a href="#">16-02-0086 (Reel)</a>
Product Name	SL™
UPC	800753595637

**Physical**

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.071/g
Packaging Type	Bag
Plating min - Mating	3.810µm
Plating min - Termination	1.905µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.63mm max.
Wire Size AWG	22, 24
Wire Size mm²	N/A

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

Old Part Number	70058-0222
-----------------	------------

**Reference - Drawing Numbers**

Product Specification	PS-70058, PS-70400
Sales Drawing	SD-70058-0222
Test Summary	TS-70058-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Contains SVHC(17. December 2014): No

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

**Search Parts in this Series**

[70058 Series](#)

**Application Tooling | [FAQ](#)**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

Description	Product #
Hand Crimp Tool	<a href="#">0638118700</a>
Insertion Tool	<a href="#">0011020022</a>

**Japan**

Description	Product #
Hand Crimp Tool	<a href="#">0570365000</a>
Hand Crimp Tool	<a href="#">0570375000</a>