


## Wire-wound Chip Power Inductors (BR series)

## BRC2518T680K



## ■ Features

- Item Summary  
68  $\mu$ H( $\pm$ 10%), 340mA, 230mA, 1007
- Lifecycle Stage  
Mass Production
- Standard packaging quantity (minimum)  
Taping 2000pcs

## ■ Products characteristics table

CaseSize (EIA/JIS)	1007/2518
Inductance	68 $\mu$ H( $\pm$ 10%)
Inductance Measuring Frequency	1MHz
Rated Current -Saturation Current	340mA
Rated Current -Temperature Rise Current	230mA
DC Resistance (max)	3.12 $\Omega$
Avg. of DC.Resistance	2.4 $\Omega$
Temperature Range	-40°C to 105°C
Self-resonant Frequency (min)	5.5MHz
RoHS Compliance	Yes
Halogen Free	Yes
Soldering Method	Reflow

## ■ External Dimensions

L	2.5mm $\pm$ 0.2
W	1.8mm $\pm$ 0.2
H	1.8mm $\pm$ 0.2

2013.08.20

The data is reference only. Electrical characteristics vary depending on environment or measurement condition.  
 TAIYO YUDEN reserves the right to make change to the Date at any time without notice.  
 Before making final selection, please check product specification.