

FP10-250

Electrical Specifications (@25C)

1. Maximum Power: 2.5 VA
2. Primary Voltage:
 - Series: 230V @ 50/60 Hz
 - Parallel: 115V @ 50/60Hz
3. Secondary:
 - Series: 10.0VCT @ 0.25 Amps
 - Parallel: 5.0V @ 0.5 Amps

Description:

The FP10-250 is part of a series which has a long history of reliable service in the field, made from a proven design and constructed with UL recognized materials.

Construction:

Wound on two dual channel nylon bobbin. Materials are UL recognized, Class B (130° C) rated.

Safety:

These products are 100% hipot tested with an insulation of 2000V between primary and secondary windings and 1500V between the primary / secondary windings and the core.

Agency File:

UL: File E53148, UL 506, Class B General Purpose Transformer,
 cUL: File E53148, UL 506, Class B General Purpose Transformer, Canadian Use




Dimensions:

A	B	C	D	E	F
1.875	1.562	0.650	0.267	0.375	1.600

Units: In inches

Weight: 5.0 oz
 Pin Dimension: .020 x .041 in

Schematic:



RoHS Compliance: As of manufacturing date February 2005, all standard products meet the requirements of 2011/65/EU, known as the RoHS initiative.

* Upon printing, this document is considered "uncontrolled". Please contact Triad Magnetics' website for the most current version.

