

LC1K0910F7

TeSys K contactor - 3P(3 NO) - AC-3 - ≤ 440 V 9 A - 110 V AC coil



Main

Range	TeSys
Product name	TeSys K
Device short name	LC1K
Contactor application	Motor control Resistive load
Utilisation category	AC-1 AC-3 AC-4
Power pole contact composition	3 NO
[Ie] rated operational current	9 A at ≤ 440 V AC AC-3 for power circuit 16 A (≤ 70 °C) at 690 V AC AC-1 for power circuit 20 A (≤ 50 °C) at ≤ 440 V AC AC-1 for power circuit
Motor power kW	4 kW at 660...690 V AC 50/60 Hz 4 kW at 500...600 V AC 50/60 Hz 4 kW at 480 V AC 50/60 Hz 4 kW at 440 V AC 50/60 Hz 4 kW at 380...415 V AC 50/60 Hz 2.2 kW at 220...230 V AC 50/60 Hz
Control circuit type	AC 50/60 Hz
Control circuit voltage	110 V AC 50/60 Hz
Auxiliary contact composition	1 NO
Overvoltage category	III
[Ith] conventional free air thermal current	10 A at ≤ 50 °C for signalling circuit 20 A at ≤ 50 °C for power circuit
Irms rated making capacity	110 A AC for signalling circuit conforming to IEC 60947 110 A AC for power circuit conforming to IEC 60947 110 A AC for power circuit conforming to NF C 63-110
Rated breaking capacity	70 A at 660...690 V conforming to IEC 60947 110 A at 380...400 V conforming to IEC 60947 110 A at 220...230 V conforming to IEC 60947 80 A at 500 V conforming to IEC 60947 110 A at 440 V conforming to IEC 60947 110 A at 415 V conforming to IEC 60947
Associated fuse rating	10 A gG for signalling circuit conforming to VDE 0660 10 A gG for signalling circuit conforming to IEC 60947 25 A aM for power circuit 25 A gG at ≤ 440 V for power circuit
Average impedance	3 mOhm at 50 Hz - Ith 20 A for power circuit
Product certifications	CSA UL
Operating time	10...20 ms coil energisation and NO closing 10...20 ms coil de-energisation and NO opening
Safety reliability level	B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1 B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1
Operating rate	3600 cyc/h

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Complementary

Control circuit voltage limits	0.2...0.75 U _c at ≤ 50 °C drop-out 0.8...1.15 U _c at ≤ 50 °C operational
Inrush power in VA	30 VA at 20 °C
Hold-in power consumption in VA	4.5 VA at 20 °C
Heat dissipation	1.3 W
Auxiliary contacts type	Type instantaneous (1 NO)
Signalling circuit frequency	≤ 400 Hz
Minimum switching current	5 mA for signalling circuit
Minimum switching voltage	17 V for signalling circuit
Non overlap distance	0.5 mm
Insulation resistance	> 10 MOhm for signalling circuit

Environment

Protective treatment	TC conforming to DIN 50016 TC conforming to IEC 60068
Operating altitude	2000 m without derating in temperature
Flame retardance	Requirement 2 conforming to NF F 16-102 Requirement 2 conforming to NF F 16-101 V1 conforming to UL 94
Mechanical robustness	Vibrations contactor opened 2 Gn, 5...300 Hz IEC 60068-2-6 Vibrations contactor closed 4 Gn, 5...300 Hz IEC 60068-2-6 Shocks contactor opened, on Z axis 10 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on Y axis 10 Gn for 11 ms IEC 60068-2-27 Shocks contactor opened, on X axis 6 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed, on Z axis 15 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed, on Y axis 15 Gn for 11 ms IEC 60068-2-27 Shocks contactor closed, on X axis 10 Gn for 11 ms IEC 60068-2-27

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0640 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Download Product Environmental
Product end of life instructions	Need no specific recycling operations

Contractual warranty

Period	18 months
--------	-----------