


ECM-10/WS - Desk Microphone



Built-in phantom microphone

- Especially suitable for PA applications
- Metal housing
- Black (SW) or white (WS) cartridge cover



Technical Data

System	: electret/omnidir.
Frequency range	: 30-17,000 kHz
Impedance	: 300 Ohm
Sensitivity	: 2.3 mV/Pa/1 kHz
Max. SPL	: 110 dB
S/N ratio	:
Power supply	: 9-48 V DC current , phantom power
Body	: metal
Dimensions	: Ø 30 mm x 71 mm
Weight	: 90 g
Connection, microphone	: XLR, bal.
Connection, cable	: -
Cable	: -