

# 3 Watts

- International Medical Approvals
- 4000 VAC Reinforced Insulation
- Meets IEC60601-1, 3rd Edition
- 2 µA Patient Leakage Current
- DIP24 Package
- EN55011 Level A With No External Components
- 3 Year Warranty



#### Dimensions:

#### JHL03:

 $1.25 \times 0.80 \times 0.40$ " (31.15 x 20.32 x 10.20 mm)

# **Models & Ratings**


Input Voltage	Output Voltage	Output Current	Input	Current	Maximum	Efficiency <sup>(4)</sup>	Model Number
input voitage		Output Guilent	No Load(1)	Full Load(2)	Capacitive Load(3)	Liliciency	
	5.0 V	600 mA	56 mA	325 mA	720 µF	77%	JHL0312S05
	12.0 V	250 mA	72 mA	316 mA	300 μF	79%	JHL0312S12
10-17 V	15.0 V	200 mA	67 mA	315 mA	240 μF	78%	JHL0312S15
	±12.0 V	±125 mA	43 mA	304 mA	±140 μF	82%	JHL0312D12
	±15.0 V	±100 mA	56 mA	303 mA	±120 μF	80%	JHL0312D15
	5.0 V	600 mA	38 mA	167 mA	720 µF	74%	JHL0324S05
	12.0 V	250 mA	37 mA	165 mA	300 μF	75%	JHL0324S12
20-30 V	15.0 V	200 mA	23 mA	146 mA	240 μF	83%	JHL0324S15
	±12.0 V	±125 mA	29 mA	150 mA	±140 μF	83%	JHL0324D12
	±15.0 V	±100 mA	42 mA	166 mA	±120 μF	87%	JHL0324D15

#### **Notes**

- 1. Input current measured at nominal input voltage.
- 2. Input current measured at lowest input voltage.

- 3. Maximum capacitive load is per output.
- 4. Typical values.

### **Mechanical Details**



0.12 (3.05) Min.

Pin Connections						
Pin	Single	Dual				
2	-Vin	-Vin				
3	-Vin	-Vin				
9	No Pin	Common				
10	Trim	Trim				
11	No Pin	-Vout				
14	+Vout	+Vout				
16	-Vout	Common				
22	+Vin	+Vin				
23	+Vin	+Vin				

#### Notes

- 1. All dimensions are in inches (mm)
- 2. Weight: 0.04 lbs (20 g) approx.
- 3. Pin diameter: 0.02 ±0.002 (0.5 ±0.05)
- 4. Pin pitch tolerance: ±0.014 (±0.35)
- 5. Case tolerance: ±0.02 (±0.5)

# **JHL03 Series**





Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Input Voltage Range	10		17	VDC	12 V nominal
	20		30	VDC	24 V nominal
Input Current					See Models and Ratings table
Inrush Current			20	А	at 36 V
Input Filter	Pi type	Pi type		•	
Patient Leakage Current			2	μΑ	
Undervoltage Lockout	On at >8.8 V. Of	f <8.3 V	•		12 V models
Ondervoltage Lockout	On at >17.5 V. O	ff <17.0 V			24 V models
Input Surge			25	VDC	12 V models for 3 s
input Suige			50	VDC	24 V models for 3 s

# Output

o.po.					
Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Output Voltage	5		15	V	See Models and Ratings table
Output Voltage Trim			±10	%	Via external resistors, see Application Notes
Initial Cat Appurage			±1	%	on V1
Initial Set Accuracy			±2	%	on V2 of dual output models
Minimum Load	0			А	No minimum load required
Start Up Delay		5		ms	
Start Up Rise Time		2		ms	
Line Regulation			±0.3	%	
Land Danielskins			±2	%	0 - 10% load
Load Regulation			±1	%	10 - 100% load
Cross Regulation			±4	%	On dual output models with one output set to 50% load and the other varied from 10% to 100% load (D05 20% to 100%)
Transient Response			4	% deviation	Recovery to within 1% in <500 µs for a 50% load change at 0.25 A/µs rate
Ripple & Noise			1	% pk-pk	20 MHz bandwidth
Short Circuit Protection					Trip & Restart (hiccup mode), auto recovery
Overload Protection	120		200	%	Trip & Restart (hiccup mode)
Overvoltage Protection	115		140	%	
Temperature Coefficient			0.03	%/°C	

# General

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions
Efficiency		86		%	See Models and Ratings table
Isolation			4000	VAC	For 1 min. Double/reinforced with a working voltage of 250 VAC. Meets 2 x MOPP per 3rd edition of IEC60601-1 5000 VAC for 10 ms in accordance with IEC60664-1
Input to Output Capacitance			20	pF	
Switching Frequency		250		kHz	
Power Density			23	W/in³	
Mean Time Between Failure		>1		MHrs	MIL-HDBK-217F, +25 °C GB
Weight		0.04 (20.0)		lb (g)	

# Environmental

Characteristic	Minimum	Typical	Maximum	Units	Notes & Conditions	
Operating Temperature	-40		+80	°C	See derating curve	
Storage Temperature	-55		+100	°C		
Case Temperature			+100	°C		
Humidity	5		90	%RH	Non-condensing	
Cooling					Natural convection	
Shock	±3 shocks in each plane, total 18 shocks of 30 g : 11 ms halfsine. Conforms to EN60068-2-27 & EN60068-2-47					
Vibration	10-500 Hz at 2 g	10-500 Hz at 2 g sweep and endurance at resonance in all 3 planes. Conforms to EN60068-2-6				

# **JHL03 Series**





### **EMC: Emissions**

Phenomenon	Standard	Test Level	Notes & Conditions
Conducted	EN55011 & EN55022	Level A	
Radiated	EN55011 & EN55022	Level A	

# **EMC: Immunity**


Phenomenon	Standard	Test Level	Criteria	Notes & Conditions		
Immunity	IEC60601-1-2, EN61204-3					
ESD Immunity	EN61000-4-2	2	A			
Radiated Immunity	EN61000-4-3	10 V/m	A			
EFT/Burst	EN61000-4-4	2	A			
Surges	EN61000-4-5	1	А			
Conducted Immunity	EN61000-4-6	10 Vm	A			
Magnetic Fields	EN61000-4-8	30 A/m	A			
Safety Approvals	ANSI/AMMI ES60601-1 3rd Edition, CSA-22.2 No.60601-1:2008, IEC60601-1 3rd Edition					

# Safety Approvals


Safety Agency	Safety Standard	Notes & Conditions
CB Report	IEC60601-1 Ed 3 Including Risk Management	Medical
UL	ANSI/AAMI ES60601-1 3rd Ed. & CSA C22.2, No.60601-1:2008	Medical

# **Application Notes**

## **Derating Curve**



#### **External Output Trim**



For 5 V output: Trim +10%, R = 3.4 k typical Trim -10%, R = 1.1 k typical

For 12 V output: Trim +10%, R = 5.9 k typical Trim -10%, R = 11.3 k typical

For 15 V output: Trim +10%, R = 8.4 k typical Trim -10%, R = 10.4 k typical

For  $\pm 12 \, V$  output: Trim  $\pm 10\%$ , R = 12.8 k typical Trim  $\pm 10\%$ , R = 9.5 k typical

For  $\pm 15\,V$  output: Trim +10%, R = 18 k typical Trim -10%, R = 14.8 k typical