



SIMATIC S7-1200, CPU 1215C, COMPACT CPU, DC/DC/DC, 2 PROFINET PORT, ONBOARD I/O: 14 DI 24V DC; 10 DO 24V DC 0.5A 2 AI 0-10V DC, 2 AO 0-20MA DC, POWER SUPPLY: DC 20.4 - 28.8 V DC, PROGRAM/DATA MEMORY: 100 KB

General information

Engineering with

- Programming package STEP 7 V13 SP1 or higher

Display

- with display No

Supply voltage

Rated value (DC)

- 24 V DC Yes

permissible range, lower limit (DC) 20.4 V

permissible range, upper limit (DC) 28.8 V

Load voltage L+

- Rated value (DC) 24 V
- permissible range, lower limit (DC) 5 V
- permissible range, upper limit (DC) 250 V

Input current

Current consumption (rated value) 500 mA

Current consumption, max. 1 500 mA

Inrush current, max. 12 A; at 28.8 V DC

Encoder supply

24 V encoder supply

- 24 V L+ minus 4 V DC min.

Output current

Current output to backplane bus (DC 5 V), max. 1 600 mA; Max. 5 V DC for SM and CM

| Power losses | |
|---|---|
| Power loss, typ. | 12 W |
| Memory | |
| Type of memory | EEPROM |
| Work memory | |
| • Integrated | 125 kbyte |
| • expandable | No |
| Load memory | |
| • Integrated | 4 Mbyte |
| • Plug-in (SIMATIC Memory Card), max. | with SIMATIC memory card |
| Backup | |
| • present | Yes; maintenance-free |
| • without battery | Yes |
| CPU processing times | |
| for bit operations, typ. | 0.085 µs; / instruction |
| for word operations, typ. | 1.5 µs; / instruction |
| for floating point arithmetic, typ. | 2.5 µs; / instruction |
| CPU-blocks | |
| Number of blocks (total) | DBs, FCs, FBs, counters and timers. The maximum number of addressable blocks ranges from 1 to 65535. There is no restriction, the entire working memory can be used |
| OB | |
| • Number, max. | Limited only by RAM for code |
| Data areas and their retentivity | |
| retentive data area in total (incl. times, counters, flags), max. | 10 kbyte |
| Flag | |
| • Number, max. | 8 kbyte; Size of bit memory address area |
| Process image | |
| • Inputs, adjustable | 1 kbyte |
| • Outputs, adjustable | 1 kbyte |
| Hardware configuration | |
| Number of modules per system, max. | 3 comm. modules, 1 signal board, 8 signal modules |
| Time of day | |
| Clock | |
| • Hardware clock (real-time clock) | Yes |
| • Deviation per day, max. | +/- 60 s/month at 25 °C |
| • Backup time | 480 h; Typical |
| Digital inputs | |
| Number of digital inputs | 14; Integrated |

| | |
|---|--|
| <ul style="list-style-type: none"> • of which, inputs usable for technological functions | 6; HSC (High Speed Counting) |
| integrated channels (DI) | 14 |
| m/p-reading | Yes |
| Number of simultaneously controllable inputs | |
| all mounting positions | |
| — up to 40 °C, max. | 14 |
| Input voltage | |
| <ul style="list-style-type: none"> • Rated value (DC) | 24 V |
| <ul style="list-style-type: none"> • for signal "0" | 5 V DC at 1 mA |
| <ul style="list-style-type: none"> • for signal "1" | 15 VDC at 2.5 mA |
| Input current | |
| <ul style="list-style-type: none"> • for signal "1", typ. | 1 mA |
| Input delay (for rated value of input voltage) | |
| for standard inputs | |
| — Parameterizable | 0.2 ms, 0.4 ms, 0.8 ms, 1.6 ms, 3.2 ms, 6.4 ms and 12.8 ms, selectable in groups of four |
| — at "0" to "1", min. | 0.2 ms |
| — at "0" to "1", max. | 12.8 ms |
| for interrupt inputs | |
| — Parameterizable | Yes |
| for counter/technological functions | |
| — Parameterizable | Single phase : 3 at 100 kHz & 3 at 30 kHz, differential: 3 at 80 kHz & 3 at 30 kHz |
| Cable length | |
| <ul style="list-style-type: none"> • shielded, max. | 500 m; 50 m for technological functions |
| <ul style="list-style-type: none"> • Unshielded, max. | 300 m; For technological functions: No |
| Digital outputs | |
| Number of digital outputs | 10 |
| <ul style="list-style-type: none"> • of which high-speed outputs | 4; 100 kHz Pulse Train Output |
| integrated channels (DO) | 10 |
| short-circuit protection | No; to be provided externally |
| Switching capacity of the outputs | |
| <ul style="list-style-type: none"> • with resistive load, max. | 0.5 A |
| Output delay with resistive load | |
| <ul style="list-style-type: none"> • "0" to "1", max. | 1 µs |
| <ul style="list-style-type: none"> • "1" to "0", max. | 5 µs |
| Relay outputs | |
| <ul style="list-style-type: none"> • Number of relay outputs, integrated | 0 |
| Cable length | |
| <ul style="list-style-type: none"> • shielded, max. | 500 m |
| <ul style="list-style-type: none"> • Unshielded, max. | 150 m |

| Analog inputs | |
|--|-------------------------------|
| Number of analog inputs | 2 |
| Integrated channels (AI) | 2 |
| Input ranges | |
| • Voltage | Yes |
| Input ranges (rated values), voltages | |
| • 0 to +10 V | Yes |
| • Input resistance (0 to 10 V) | ≥100k ohms |
| Cable length | |
| • shielded, max. | 100 m; twisted and shielded |
| Analog outputs | |
| Number of analog outputs | 2 |
| Integrated channels (AO) | 2; 0 to 20 mA |
| Output ranges, voltage | |
| • 0 to 10 V | Yes |
| Output ranges, current | |
| • 0 to 20 mA | Yes |
| Cable length | |
| • shielded, max. | 100 m; shielded, twisted pair |
| Analog value creation | |
| Integration and conversion time/resolution per channel | |
| • Resolution with overrange (bit including sign), max. | 10 bit |
| • Integration time, parameterizable | Yes |
| • Conversion time (per channel) | 625 μs |
| Encoder | |
| Connectable encoders | |
| • 2-wire sensor | Yes |
| 1st interface | |
| Interface type | PROFINET |
| Physics | Ethernet |
| Isolated | Yes |
| Automatic detection of transmission speed | Yes |
| Autonegotiation | Yes |
| Autocrossing | Yes |
| Functionality | |
| • PROFINET IO Device | Yes |
| • PROFINET IO Controller | Yes |
| PROFINET IO Controller | |
| • Transmission rate, max. | 100 Mbit/s |
| • Number of connectable IO devices, max. | 16 |

| | |
|---|--|
| <ul style="list-style-type: none"> • Prioritized startup <ul style="list-style-type: none"> — Number of IO Devices, max. | 16 |
| PROFINET IO Device | |
| Services | |
| <ul style="list-style-type: none"> — Shared device | Yes |
| <ul style="list-style-type: none"> — Number of IO controllers with shared device, max. | 2 |
| Communication functions | |
| S7 communication | |
| <ul style="list-style-type: none"> • supported | Yes |
| <ul style="list-style-type: none"> • as server | Yes |
| <ul style="list-style-type: none"> • As client | Yes |
| Open IE communication | |
| <ul style="list-style-type: none"> • TCP/IP | Yes |
| <ul style="list-style-type: none"> • ISO-on-TCP (RFC1006) | Yes |
| <ul style="list-style-type: none"> • UDP | Yes |
| Web server | |
| <ul style="list-style-type: none"> • supported | Yes |
| <ul style="list-style-type: none"> • User-defined websites | Yes |
| Number of connections | |
| <ul style="list-style-type: none"> • overall | 16; dynamically |
| Test commissioning functions | |
| Status/control | |
| <ul style="list-style-type: none"> • Status/control variable | Yes |
| <ul style="list-style-type: none"> • Variables | Inputs/outputs, memory bits, DBs, distributed I/Os, timers, counters |
| Forcing | |
| <ul style="list-style-type: none"> • Forcing | Yes |
| Diagnostic buffer | |
| <ul style="list-style-type: none"> • present | Yes |
| Traces | |
| <ul style="list-style-type: none"> • Number of configurable Traces | 2; Up to 512 KB of data per trace are possible |
| Integrated Functions | |
| Number of counters | 6 |
| Counter frequency (counter) max. | 100 kHz |
| Frequency meter | Yes |
| controlled positioning | Yes |
| PID controller | Yes |
| Number of alarm inputs | 4 |
| Number of pulse outputs | 4 |
| Limit frequency (pulse) | 100 kHz |

Galvanic isolation

Galvanic isolation digital inputs

- Galvanic isolation digital inputs No
- between the channels, in groups of 1

Galvanic isolation digital outputs

- between the channels No
- between the channels, in groups of 1

Permissible potential difference

between different circuits 500 V DC between 24 V DC and 5 V DC

EMC

Interference immunity against discharge of static electricity

- Interference immunity against discharge of static electricity acc. to IEC 61000-4-2 Yes
 - Test voltage at air discharge 8 kV
 - Test voltage at contact discharge 6 kV

Interference immunity to cable-borne interference

- Interference immunity on supply lines acc. to IEC 61000-4-4 Yes
- Interference immunity on signal lines acc. to IEC 61000-4-4 Yes

Surge immunity

- on the supply lines acc. to IEC 61000-4-5 Yes

Immunity against conducted interference induced by high-frequency fields

- Interference immunity against high-frequency radiation acc. to IEC 61000-4-6 Yes

Emission of radio interference acc. to EN 55 011

- Limit class A, for use in industrial areas Yes; Group 1
- Limit class B, for use in residential areas Yes; When appropriate measures are used to ensure compliance with the limits for Class B according to EN 55011

Degree and class of protection

Degree of protection to EN 60529

- IP20 Yes

Standards, approvals, certificates

CE mark Yes

UL approval Yes

cULus Yes

RCM (formerly C-TICK) Yes

FM approval Yes

Marine approval

- Marine approval Yes

Ambient conditions

| | |
|---|---|
| Free fall | |
| • Drop height, max. (in packaging) | 0.3 m; five times, in dispatch package |
| Ambient temperature in operation | |
| • Min. | -20 °C |
| • max. | 60 °C; Number of simultaneously activated inputs or outputs 7 or 5 (no adjacent points) at 60 °C horizontal or 50 °C vertical, 14 or 10 at 55 °C horizontal or 45 °C vertical |
| • horizontal installation, min. | -20 °C |
| • horizontal installation, max. | 60 °C |
| • vertical installation, min. | -20 °C |
| • vertical installation, max. | 50 °C |
| Storage/transport temperature | |
| • Min. | -40 °C |
| • max. | 70 °C |
| Air pressure acc. to IEC 60068-2-13 | |
| • Storage/transport, min. | 660 hPa |
| • Storage/transport, max. | 1 080 hPa |
| • Permissible operating height | -1000 to 2000 m |
| Relative humidity | |
| • Operation, max. | 95 %; no condensation |
| • Permissible range (without condensation) at 25 °C | 95 % |
| Vibrations | |
| • Vibrations | 2G wall mounting, 1G DIN rail |
| • Operation, checked according to IEC 60068-2-6 | Yes |
| Shock test | |
| • checked according to IEC 60068-2-27 | Yes; IEC 68, Part 2-27 half-sine: strength of the shock 15 g (peak value), duration 11 ms |
| Pollutant concentrations | |
| — SO ₂ at RH < 60% without condensation | SO ₂ : < 0.5 ppm; H ₂ S: < 0.1 ppm; RH < 60% condensation-free |
| Configuration | |
| Configuration software | |
| • STEP 7 | Yes |
| programming | |
| Programming language | |
| — LAD | Yes |
| — FBD | Yes |
| — SCL | Yes |
| Cycle time monitoring | |
| • can be set | Yes |
| Dimensions | |

| | |
|-----------------------|------------|
| Width | 130 mm |
| Height | 100 mm |
| Depth | 75 mm |
| Weights | |
| Weight, approx. | 500 g |
| last modified: | 12.03.2015 |