

## Technical Notice

### Lithium Battery Information Sheet

#### 1. Identification

- 1.1 Product Name:** Tadiran High Energy Lithium Battery, or  
Sonnenschein Lithium Inorganic Lithium Battery
- Voltage:** 3.6 Volts
- Chemistry System:** Lithium Thionyl chloride
- Anode:** Lithium metal
- Cathode:** Liquid, Thionyl chloride
- 1.2 Company:** Tadiran Batteries GmbH
- Address:** Industriestr. 22  
63654 BÜDINGEN  
Germany  
Tel.: +49(0)6042-954-0  
Fax: +49(0)6042-954-190  
Web: [www.tadiranbatteries.de](http://www.tadiranbatteries.de)
- 1.3 Emergency Telephone Number:** +49(0)6042/954-599

**Note:** This information sheet refers to cells and batteries assembled from them

---

#### 2. Hazards Identification

**Warning:** Fire, explosion, and severe, burn hazard. Do not recharge, disassemble, heat above 100 °C (series SL-500: 150 °C), incinerate, or expose contents to water.

##### **Protection from charging:**

Whenever lithium batteries are not the single power source in a circuit the following measures recommended by Underwriters Laboratories are relevant. The cells should not be connected in series with an electrical power source that would increase the forward current through the cells.

The circuit for these cells shall include one of the following:

- A. Two suitable diodes or the equivalent in series with the cells to prevent any reverse (charging) current. The second diode is used to provide protection in the event that one should fail. Quality control, or equivalent procedures, shall be established by the device manufacturer to ensure the diode polarity is correct for each unit,

*or*

- B. A blocking diode or the equivalent to prevent any reverse (charging) current and a resistor to limit current in case of a diode failure. The resistor should be sized to limit the reverse (charging) current to the maximums given in the data sheets.

Revised 2015-06-12

### 3. Composition/Information on Ingredients

Substance	CAS No.	Content w/w %	GHS Code	Sinal word	H-phrases
Lithium Metal	7439-93-2	2 - 6	GHS02, GHS05	Danger	260, 314, EUH014
Thionyl Chloride	7719-09-7	18 - 47	GHS05, GHS06	Danger	302, 331, 314, 335
Aluminium Chloride	7446-70-0	2 - 5	GHS05, GHS08	Danger	314, 372-373
Lithium Chloride	7447-41-8	1 - 2	GHS07	Warning	302, 315, 319
Carbon	7440-44-0	2 - 5	--		
Steel, Nickel plated	--	35 - 73	--		
Glass	--	0 - 2	--		
Organic polymeres	Different	0 - 2	--		

GHS-Code:      GHS02      Flame  
                     GHS05      Corrosion  
                     GHS06      Skull and crossbones  
                     GHS07      Exclamation mark  
                     GHS08      Health hazard

H-Phrases:      260      In contact with water releases flammable gases which may ignite spontaneously  
                          302      Harmful if swallowed  
                          314      Causes severe skin burns and eye damage  
                          315      Causes skin irritation  
                          319      Causes serious eye irritation  
                          331      Toxic if inhaled  
                          335      May cause respiratory irritation  
                          372-373      Causes damage to lung through prolonged or repeated exposure (inhale); may cause damage to central nervous system through prolonged exposure (swallow)  
                          EUH014      Reacts violently with water

**Important Note:** The material in this section may only represent a hazard if the integrity of the battery is compromised, or if the battery is physically or electrically abused.

---

#### **4. First Aid Measures**

##### **A. Electrolyte Contact**

- Skin    Immediately flush with plenty of water for at least 15 minutes. If symptoms are present after flushing, get medical attention.
- Eyes     Immediately flush with plenty of water for at least 15 minutes and get medical attention.
- Respiratory system:                        With large quantities and irritation of the respiratory tract medical surveillance for 48 hours.  
Immediately inhale Cortisone Spray, e.g. Pulmicort.

##### **B. Lithium Metal Contact**

- Skin     Remove particles of lithium from skin as rapidly as possible. Immediately flush with plenty of water for at least 15 minutes and get medical attention.
- Eyes     Immediately flush with plenty of water for at least 15 minutes and get immediate medical attention.

Revised 2015-06-12

## 5. Fire - fighting measures

### A. Extinguishing Media

- During a fire with lithium batteries, copious amounts of cold water are an effective medium to prevent expansion of the fire. Do not use warm water or hot water.
- Lith-X (Class D extinguishing media) is effective on fires involving only a few lithium batteries.
- Do not use CO<sub>2</sub> or Halon type extinguishers.
- Dry chemical type extinguishers have limited extinguishing potential.

### B. Fire Fighting Procedures

- Use a positive pressure self-contained breathing apparatus if batteries are involved in a fire.
- Full protective clothing is necessary.
- During water application caution is advised as burning pieces of lithium may be ejected from the fire.
- Where the cells or batteries are not at the centre of the fire copious amounts of water may be supplied to the cells using a diffuser type nozzle so that the cells remain cool during the containment and extinguishing of the fire. A sprinkler system should be sufficient for this purpose the critical factor being that the lithium cells do not experience temperatures above the melting point of lithium.
- Small amounts of water should never be used such as the volumes contained within portable fire extinguishers. Standard dry powder extinguishers are ineffective. Halon extinguishers must not be used when fighting lithium fires as toxic gases may be generated during fire fighting. It should be noted that a hazard of hydrogen formation exists whenever hot lithium metal comes into contact with water.

---

## 6. Accidental release measures

When the battery housing is damaged, small amounts of electrolyte may leak. Seal battery air tight in a plastic bag, adding some chalk (CaCO<sub>3</sub>) or lime (CaO) powder or Vermiculite. Electrolyte traces may be wiped off dryly using household paper. Rinse with water afterwards.

---

## 7. Handling and Storage

- Do not allow terminals to short-circuit.
- Storage preferably in a cool (below 21 °C), dry area that is subject to little temperature change.
- Do not place near heating equipment, nor expose to direct sunlight for long periods. Elevated temperatures can result in reduced battery service life.

Revised 2015-06-12

---

### 8. Exposure controls / personal protection

Lithium batteries are products, from which no substance is released under normal and reasonably foreseeable conditions of use.

---

### 9. Physical and chemical properties

Refer to information under item 3.

---

### 10. Stability and reactivity

May rupture violently when heated above 150 °C or when charged.

---

### 11. Toxicological information

Not applicable

Refer to information under item 3.


---

### 12. Ecological information

The batteries do not contain mercury, cadmium or other heavy metals.

---

### 13. Disposal Considerations

- Batteries do not contain hazardous materials according to EC directives 91/157/EEC, 93/86/EEC, and 2011/65/EU (RoHS directive)
  - EC battery directive 2006/66/EC has been implemented by most EC member states.
  - According to the EU Battery Directive, Batteries are marked with the symbol of the crossed-out wheeled bin (see figure). The symbol reminds the end user that batteries are not permitted to be disposed of with household waste, but must be collected separately.
- 
- Waste Batteries must effectively be protected against short circuit during storage and transport.
  - A disposal service is offered upon request by Tadiran Batteries.
  - For additional information a Technical Notice is available upon request
-

Revised 2015-06-12

#### **14. Transport information**

Class 9

UN 3090: LITHIUM METAL BATTERIES

UN 3091: LITHIUM METAL BATTERIES CONTAINED IN EQUIPMENT, or  
LITHIUM METAL BATTERIES PACKED WITH EQUIPMENT

Packing group: NA

Special provisions and packing instructions:

ADR, RID: 188, 230, 310, 360, 376, 377, 636, P903, P908, LP903, LP904

IATA: A48, A88, A99, A154, A164, A181, A182, A183, A185, A201, P968  
P969, P970

IMDG-Code: 188, 230, 310, 376, 377, P903, P908, P909, LP903, LP904

EmS: F-A, S-I

Storage and segregation: Category A, SW 19

For more information see [www.tadiranbatteries.de](http://www.tadiranbatteries.de) > products > Transport & Information

---

#### **15. Regulatory information**

Transport Regulations: see in section 14

EU Battery Directive: see in section 13

---

#### **16. Other information**

- Tadiran Lithium Batteries are registered by Underwriters Laboratories, Northbrook, U.S.A. under file MH 12827.
- Further information is given in
  - Tadiran Lithium Battery Product Data Catalogue
  - Tadiran Lithium Battery Technical Brochure.
- For lithium batteries in general, Safety standard IEC 60086-4 applies. It contains detailed recommendations for manufacturers of equipment and users.
- Battery packs  
The design and assembly of battery packs require special skills, expertise and experience. Therefore it is not recommended that the end user attempt to self-assemble battery packs. It is preferable that any battery using lithium cells be fabricated by TADIRAN to ensure proper battery design and construction. A full battery assembly service is available from TADIRAN who can be contacted for further information. If for any reason, this is not possible, TADIRAN can review the pack design in confidence to ensure that the design is safe (in assembly and use) and capable of meeting stated performance requirements.

---

*The REACH regulation (1907/2006/EC) has replaced the EU directive for safety data sheets (91/155/EU). Both the now valid REACH regulation and the no longer valid directive require safety data sheets to be created and updated for materials and preparations. For products - including lithium batteries - no EU safety data sheets are required according to European chemicals regulations.*

*The information contained herein is furnished without warranty of any kind. Users should consider these data only as a supplement to other information gathered by them and must make independent determinations of the suitability and completeness of information from all sources to assure proper use and disposal of these materials and the safety and health of employees and customers.*