

# MPC7410 RISC Microprocessor Hardware Specifications Addendum for the MPC7410TxxnnLE Series

This document describes part-number-specific changes to the *MPC7410 RISC Microprocessor Hardware Specifications* (Document No. MPC7410EC).

Specifications provided in this document supersede those in the *MPC7410 RISC Microprocessor Hardware Specifications*, Rev. 1 or later, for the part numbers listed in [Table A](#) only. Specifications not addressed herein are unchanged.

Because this document is frequently updated, see the website listed on the back page of this document or contact your Freescale sales office for the latest version.

*Freescale Part Numbers Affected:*

*MPC7410THX400LE*  
*MPC7410THX450LE*  
*MPC7410THX500LE*  
*MC7410TVU400LE*

**Table A. Part-Number-Specific Changes**

Freescale Part Number	Operating Conditions				Significant Changes from Hardware Specification
	CPU Frequency (MHz)	V <sub>DD</sub>	T <sub>J</sub> (°C)	OV <sub>DD</sub> (V)	
MPC7410THX500LE	500	1.8 V ±100 mV	–40 to 105	1.8/2.5/3.3	Extended temperature range. For all DC/AC specifications not mentioned in this document, see the MPC7410RX500LE specifications in the <i>MPC7410 RISC Microprocessor Hardware Specifications</i> .
MPC7410THX450LE	450	1.8 V ±100 mV	–40 to 105	1.8/2.5/3.3	Extended temperature range. For all DC/AC specifications not mentioned in this document, see the MPC7410RX450LE specifications in the <i>MPC7410 RISC Microprocessor Hardware Specifications</i> .
MPC7410THX400LE	400	1.8 V ±100 mV	–40 to 105	1.8/2.5/3.3	Extended temperature range. For all DC/AC specifications not mentioned in this document, see the MPC7410RX400LE specifications in the <i>MPC7410 RISC Microprocessor Hardware Specifications</i> .
MC7410TVU400LE	400	1.8 V ±100 mV	–40 to 105	1.8/2.5/3.3	Extended temperature range. For all DC/AC specifications not mentioned in this document, see the MC7410VU400LE specifications in the <i>MPC7410 RISC Microprocessor Hardware Specifications</i> .

## DC Electrical Characteristics

The MPC7410TxxnnnLE series DC electrical characteristics are identical to that of the MPC7410, with the exception shown in [Table B](#).

**Table B. Recommended Operating Conditions**

Characteristic	Symbol	Recommended Value	Unit
Die-junction temperature	T <sub>j</sub>	–40 to 105	°C

**Note:** See the *MPC7410 RISC Microprocessor Hardware Specifications*.

# Part Numbers Addressed by this Specification

Table C provides the ordering information for the MPC7410TxxnnnLE series.

Table C. Part Marking Nomenclature


MPC	7410	T	xx	nnn	L	E
Product Code	Part Identifier	Process Descriptor	Package	Processor Frequency <sup>1</sup>	Application Modifier	Revision Level
MPC	7410	T: -40 to 105°C	HX = HCTE_CBGA	400 450 500	L: 1.8 V ±100 mV	E: 1.4; PVR = 800C 1104
MC			VU = HCTE_CBGA (Lead Free C5 Solder Spheres)	400		

**Note:**

1. Processor core frequencies supported by parts addressed by this specification only. Parts addressed by other specifications may support other maximum core frequencies.

## Part Marking

Parts are marked as the example shown in Figure A.



**Notes:**

- nnn is the speed grade of the part.
- MMMMMM is the 6-digit mask number.
- ATWLYYWWA is the traceability code.
- CCCCC is the country of assembly. This space is left blank if parts are assembled in the United States.

Figure A. Part Marking for BGA Device

# Document Revision History

Table D provides a revision history for this document.

**Table D. Document Revision History**

Revision	Date	Substantive Chagnes(s)
1	11/2010	<ul style="list-style-type: none"><li>• Removed “HX” from document title.</li><li>• Added MC7410TVU400LE to list of devices covered by this document.</li><li>• Updated Table C, “Part Marking Nomenclature,” to include MC7410TVU400LE.</li></ul>
0.1	4/2005	Document template update
		Document ID change from MPC7410THXLEPNS for Part Number Specification to MPC7410ECS08AD for Hardware Specification Addendum.
0	10/2003	Initial release.

## **How to Reach Us:**

### **Home Page:**

[www.freescale.com](http://www.freescale.com)

### **Web Support:**

<http://www.freescale.com/support>

### **USA/Europe or Locations Not Listed:**

Freescale Semiconductor, Inc.  
Technical Information Center, EL516  
2100 East Elliot Road  
Tempe, Arizona 85284  
1-800-521-6274 or  
+1-480-768-2130  
[www.freescale.com/support](http://www.freescale.com/support)

### **Europe, Middle East, and Africa:**

Freescale Halbleiter Deutschland GmbH  
Technical Information Center  
Schatzbogen 7  
81829 Muenchen, Germany  
+44 1296 380 456 (English)  
+46 8 52200080 (English)  
+49 89 92103 559 (German)  
+33 1 69 35 48 48 (French)  
[www.freescale.com/support](http://www.freescale.com/support)

### **Japan:**

Freescale Semiconductor Japan Ltd.  
Headquarters  
ARCO Tower 15F  
1-8-1, Shimo-Meguro, Meguro-ku  
Tokyo 153-0064  
Japan  
0120 191014 or  
+81 3 5437 9125  
[support.japan@freescale.com](mailto:support.japan@freescale.com)

### **Asia/Pacific:**

Freescale Semiconductor China Ltd.  
Exchange Building 23F  
No. 118 Jianguo Road  
Chaoyang District  
Beijing 100022  
China  
+86 10 5879 8000  
[support.asia@freescale.com](mailto:support.asia@freescale.com)

### **For Literature Requests Only:**

Freescale Semiconductor  
Literature Distribution Center  
1-800 441-2447 or  
+1-303-675-2140  
Fax: +1-303-675-2150  
[LDCForFreescaleSemiconductor@hibbertgroup.com](mailto:LDCForFreescaleSemiconductor@hibbertgroup.com)

Information in this document is provided solely to enable system and software implementers to use Freescale Semiconductor products. There are no express or implied copyright licenses granted hereunder to design or fabricate any integrated circuits or integrated circuits based on the information in this document.

Freescale Semiconductor reserves the right to make changes without further notice to any products herein. Freescale Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does Freescale Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation consequential or incidental damages. "Typical" parameters which may be provided in Freescale Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. Freescale Semiconductor does not convey any license under its patent rights nor the rights of others. Freescale Semiconductor products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the Freescale Semiconductor product could create a situation where personal injury or death may occur. Should Buyer purchase or use Freescale Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold Freescale Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that Freescale Semiconductor was negligent regarding the design or manufacture of the part.

Freescale and the Freescale logo are trademarks of Freescale Semiconductor, Inc. Reg. U.S. Pat. & Tm. Off. All other product or service names are the property of their respective owners. The Power Architecture and Power.org word marks and the Power and Power.org logos and related marks are trademarks and service marks licensed by Power.org.  
© 2010 Freescale Semiconductor, Inc.

Document Number: MPC7410ECS08AD

Rev. 1  
11/2010

