


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0444412002](#)
Status: **Active**
Overview: Sabre™ Power Connector
Description: 7.50mm Pitch Sabre™ Receptacle Crimp Housing, UL 94V-0, 2 Circuits, Glow Wire Compatible

Documents:

3D Model	Packaging Specification PK-44441-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-44441-9999 (PDF)	Product Literature (PDF)
Packaging Specification PK-42295-001 (PDF)	



Series image - Reference only

Agency Certification

CSA	LR19980
TUV	R72130381
UL	E29179

General

Product Family	Crimp Housings
Series	44441
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	This Molex product is manufactured from material that has the following ratings, tested by independent agencies :. a) A Glow Wire Ignition Temperature (GWIT) of at least 775 deg C per IEC 60695-2-13.. b) A Glow Wire Flammability Index (GWFI) above 850 deg C per IEC 60695-2-12.and hence complies with the requirements set out in the International Standard IEC 60335-1 5th edition - household and similar electrical appliances - safety; section 30 Resistance to heat and fire.<P><P>The customers using this product must determine its suitability for use in their particular application through testing or other acceptable means as described in end-product glow-wire flammability test standard IEC 60695-2-11 and any applicable product end-use standard(s).<P>If it is determined during the customer's evaluation of suitability, that higher performance is required, please contact Molex for possible product options.
MolexKits	Yes
Overview	Sabre™ Power Connector
Product Literature Order No	987650-5662
Product Name	Sabre™
UPC	800754366786

Physical

Circuits (maximum)	2
Color - Resin	Black
Flammability	94V-0
Gender	Female
Glow-Wire Compliant	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	1.880/g
Number of Rows	1
Packaging Type	Bag

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contains SVHC(2014 December 17): No

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[44441](#) Series

Mates With

[43680-2002](#) Plug Housing. [43160](#) 2 Circuit, UL 94V-0 Vertical or Right Angle Headers. [46007](#) 2 Circuit, UL 94V-0 Right Angle, UL1977 finger proof compliant

Use With

[43375](#) Female Crimp Terminals

Panel Mount	No
Pitch - Mating Interface	7.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40°C to +75°C

Electrical

Current - Maximum per Contact	18.0A
-------------------------------	-------

Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info**Reference - Drawing Numbers**

Packaging Specification	PK-42295-001, PK-44441-001
Product Specification	PS-44441-9999, RPSX-44441-001
Sales Drawing	SD-44441-*002

This document was generated on 06/26/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION