

## 1.44kw Single-Phase Basic PDU, 120V Outlets (14 5-15R), 5-15P, 15ft Cord, 0U Vertical

MODEL NUMBER: PDUV15



### Description

Tripp Lite Basic Power Distribution Units / PDU systems offer reliable rackmount power distribution. Supplies equipment with continuous power from any protected UPS, generator or mains input power source. High quality design includes rugged all-metal housing and secure rackmount installation with included mounting accessories.

### Features

- 15A single phase 120V Basic Power Distribution Unit / PDU (Agency de-rated to 12A continuous)
- 0U 36in / 91.4cm vertical rackmount format PDU installs using no rack spaces
- 14 NEMA 5-15R outlets
- Attached NEMA 5-15P 15A 120V input plug with 15ft / 4.5m line cord
- 15A resettable circuit breaker
- Switch-free design prevents accidental shutoff
- Toolless mounting buttons enable simple installation in compatible equipment racks
- Rear facing installation buttons can be relocated to the left or right surface of the PDU for rear, center or forward-facing outlet orientation in compatible racks
- Included nut and bolt mounting brackets support installation in non button-mount compatible racks, wallmount and raceway applications

### Highlights

- 15A 120V Basic Power Distribution Unit
- 0U Vertical Rackmount format with 36 in / .9m height
- 14 NEMA 5-15R outlets
- NEMA 5-15P input plug
- 15 ft. / 4.6m attached line cord
- Toolless mounting buttons and bolt-down brackets included

### Applications

- Ideal for network power distribution in datacenters, comptuer rooms and network closets

### Package Includes

- PDUV15 Basic Vertical PDU
- Mounting hardware
- Owner's manual with warranty information

## Specifications

OVERVIEW	
PDU Type	Basic
OUTPUT	
Output Capacity Details	1.44kW (120V), 1.52kW (127V), 1.2kW (100V); 15A maximum (Agency de-rated to 12A continuous)



Frequency Compatibility	50 / 60 Hz
Output Receptacles	(14) 5-15R
Output Nominal Voltage	100-127V nominal, single phase
Overload Protection	15A breaker
Outlet Type	NEMA 5-15R
Individual Outlet Switching	No
<b>INPUT</b>	
PDU Input Voltage	100; 120; 127
Maximum Input Amps	15
PDU Plug Type	NEMA 5-15P
Input Cord Length (ft.)	15
Input Cord Length (m)	4.57
Input Phase	Single-Phase
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	n/a
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	40 x 2.8 x 3
Shipping Dimensions (hwd / cm)	101.6 x 7.11 x 7.62
Shipping Weight (lbs.)	3.8
Shipping Weight (kg)	1.72
Unit Dimensions (hwd / in.)	36 x 1.25 x 1.75
Unit Dimensions (hwd / cm)	91.44 x 3.18 x 4.45
Unit Weight (lbs.)	3.3
Unit Weight (kg)	1.50
Material of Construction	Metal
Form Factors Supported	Vertical (0U) mounting in rack enclosures, horizontal mount in raceways and a variety of other applications
PDU Form Factor	Vertical (0U)
<b>ENVIRONMENTAL</b>	
Storage Temperature Range	5 to 122F (-15 to 50C)
Relative Humidity	5 to 95% non-condensing
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

<b>CERTIFICATIONS</b>	
Certifications	Tested to UL60950-1 (USA) and CAN/CSA C22.2 No. 60950-1-03 (Canada), RoHS Compliant
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>