

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0039000040](#)  
**Status:** **Active**  
**Overview:** [Mini-Fit Jr.™ Power Connectors](#)  
**Description:** Mini-Fit® Male Crimp Terminal, Tin (Sn) over Copper (Cu) Plated Brass Contact, 18-24 AWG, Reel

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-52034-004 (PDF)</a>
<a href="#">Product Specification PS-51010-005 (PDF)</a>	<a href="#">Product Specification PS-5556-002 (PDF)</a>
<a href="#">Product Specification PS-51010-006 (PDF)</a>	<a href="#">Packaging Specification PK-5558-001 (PDF)</a>
<a href="#">Product Specification PS-51096-001 (PDF)</a>	<a href="#">Test Summary TS-5556-002 (PDF)</a>
<a href="#">Product Specification PS-52034-003 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**General**

Product Family	Crimp Terminals
Series	<a href="#">5558</a>
Application	Power
Crimp Quality Equipment	Yes
Overview	<a href="#">Mini-Fit Jr.™ Power Connectors</a>
Packaging Alternative	<a href="#">39-00-0041 (Loose)</a>
Product Name	Mini-Fit®
UPC	800753643239

**Physical**

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.123/g
Packaging Type	Reel
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.30-3.10mm
Wire Size AWG	18, 20, 22, 24
Wire Size mm²	N/A

**Electrical**

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

**Solder Process Data**


Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

Old Part Number	5558T
-----------------	-------

**Reference - Drawing Numbers**

Packaging Specification	<a href="#">PK-5558-001</a>
Product Specification	<a href="#">PS-51010-005</a> , <a href="#">PS-51010-006</a> , <a href="#">PS-51096-001</a> , <a href="#">PS-52034-003</a> , <a href="#">PS-52034-004</a> , <a href="#">PS-5556-002</a> , <a href="#">RPS-30067-002</a> , <a href="#">RPS-42474-001</a>
Sales Drawing	<a href="#">SD-5558****</a>
Test Summary	<a href="#">TS-5556-002</a>



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Contains SVHC(2014 December 17): No

**Halogen-Free**

**Status**

**Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS  
ELV

Green Image  
Not Relevant

**Search Parts in this Series**

[5558 Series](#)

**Mates With**

[5556 Mini-Fit® Crimp Terminal](#)

**Use With**

[5559 Mini-Fit Jr.™ Plug Housing](#), [30068 Mini-Fit® TPA Plug Housing](#), [42475 Mini-Fit® BMI Plug Housing](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

FineAdjust™  
Applicator for  
Insulation OD

**Product #**

[0639024900](#)

2.30-2.60mm - 18-24 AWG FineAdjust™	<u>0639002600</u>
Applicator for Insulation OD 2.50-2.95mm, 18-24 AWG Wire FineAdjust™	<u>0639015600</u>
Applicator for Insulation OD 1.90-2.30mm - 18-24 AWG FineAdjust™	<u>0639002900</u>
Applicator for Insulation OD 1.65-2.05mm, 18-24 AWG Wire FineAdjust™	<u>0639023900</u>
Applicator for Insulation OD 1.40-1.70mm - 18-24 AWG T2 Terminator™	<u>0639123900</u>
for insulation OD 1.40-1.70mm - 18-24 AWG T2 Terminator™	<u>0639124900</u>
for insulation OD 2.30-2.60mm - 18-24 AWG Hand Crimp Tool for	<u>0638190900</u>
Male and Female Crimp Terminals, 16-24 AWG Wire T2 Terminator™ for	<u>0639102900</u>
insulation OD 1.65 – 2.05mm – 18 – 24 AWG FineAdjust™	<u>0639024800</u>
Applicator for Insulation OD 2.50-2.95mm Optimized for 18 AWG Only T2 Terminator™	<u>0639102600</u>
for insulation OD 2.50-2.95mm - 18-24 AWG Extraction Tool	<u>0011030044</u>
T2 Terminator™	<u>0639115600</u>
for insulation OD 1.90-2.30mm - 18-24 AWG T2 Terminator™	<u>0639124800</u>
for insulation OD 2.50-2.95mm optimized for 18 AWG only	
<b>Japan</b>	
<b>Description</b>	<b>Product #</b>
Hand Extraction Tool	<u>0570316000</u>

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**