

Gigabit PoE+ Extender - 802.3at/af - 100m (330ft)

StarTech ID: POEEXT1GAT



This Gigabit PoE+ extender spans your Power over Ethernet (PoE) device over longer distances, letting you double the 100m limitations of a traditional PoE infrastructure.



Now you can connect your Gigabit PoE device up to a maximum of 200m away, so it's easy to install a remote IP camera or access point. Plus the extender can be daisy-chained for more scalability.

Unrestricted PoE+ range and convenience

Need more distance? This convenient PoE+ repeater maximizes range and flexibility by extending your PoE connection by an extra 100m (330ft), while providing 24-watt power output to compatible devices.

Simply connect the extender to your power sourcing equipment (PSE) and your PoE-powered device (PD) and you're all set. The extender is compliant with the 802.3at/af standard, so it will work with existing PSE, such as a StarTech.com [PoE+ injector](#) (POEINJ1G) or [PoE+ switch](#) (IES81000POE).

Daisy chain for longer distance and flexibility

Still need more distance? If an extra 100m isn't enough, this full-featured PoE extender offers daisy chain capability.

You can easily connect four extenders together, letting you install your PoE+ PD up to 500m (1640ft) away. It's perfect for business, education, and retail environments (output wattage is dependent on the number of daisy-chained extenders used).



Convenient installation options and durable construction

Get up and running quickly. This Gigabit PoE+ extender can be positioned right where you need it, with a wall-mountable design that requires no external power adapter.

You can enjoy reliable performance with little worry of downtime or failure, the extender features a rugged metal housing with built-in ESD and surge protection.

The POEEXT1GAT is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Applications

- Ideal for Wi-Fi® access points, IP phones, surveillance cameras, and kiosks where a power connection is not available
- Enable remote installation of PoE+ devices over longer distance than conventional PoE range capabilities
- Perfect for SOHO, SMB, system integrators, and IT administrators

Features

- Deploy and access your Gigabit PoE-powered devices (PD) further away
- Extend your PoE PDs over longer distances by daisy-chaining four extenders up to 500m (1640ft) total range (reduced power output at each connection)
- Compact, wall-mountable, and rugged metal housing for convenience and reliability
- 2kV ESD and surge protection
- Plug-and-play setup with no power adapter required
- IEEE 802.3at 30W input to IEEE 802.3at/af 24W output
- 52V to 56V input voltage
- Automatically detects your connected PD to prevent damage if incorrectly installed

Technical Specifications

Warranty	2 Years
Industry Standards	IEEE 802.3af PoE, IEEE 802.3at PoE+
Industry Standards	IEEE 802.3 10BASE-T, IEEE 802.3u 100BASE-TX, IEEE 802.3ab 1000BASE-T
Ports	1
Auto MDIX	Yes
Auto-Negotiation	Yes
Compatible Networks	10/100/1000 Mbps
Flow Control	Half-duplex back-pressure IEEE 802.3x pause frame for full-duplex
Full Duplex Support	Yes
Jumbo Frame Support	No
Maximum Cable Length	100 m [328 ft]
Maximum Data Transfer Rate	2 Gbps (Full-Duplex)
MTBF	50,000 Hours
Power Output	One extender - 24W Power Output: Two extender daisy chain - 20W Power Output: Three extender daisy chain - 16W Power Output: Four extender daisy chain - 12W
Surge Protection	EN61000-4-2 (ESD) - 2kV EN61000-4-5 (Surge) - 2kV
Switching Architecture	Store-and-Forward
Connector Type(s)	2 - RJ-45 Female
Note	Total extension distances can often be shorter due to power delivery voltage-drop on the connected cables. Maximum distances can vary based on the quality of the UTP cables and the environment.
Note	You may daisy chain up to 4 POEEXT1GAT units total, for a maximum of 500m. The 4th unit will supply IEEE 802.3af up to 12W output.

System and Cable Requirements	If your connected device does not meet the IEEE 802.3af or IEEE 802.3at PoE standard, then the POEEXT1GAT will not pass-through power to the connected device / Ethernet cable.
Color	Black
Enclosure Type	Steel
Product Height	25 mm [1 in]
Product Length	94 mm [3.7 in]
Product Weight	188 g [6.6 oz]
Product Width	69 mm [2.7 in]
LED Indicators	1 - PoE IN
LED Indicators	1 - LNK/ACT
LED Indicators	1 - PoE OUT
Input Voltage	52 ~ 56 DC
Power Consumption	3.2 W Max
Power Source	PoE-Powered
Humidity	5~95% RH (Non-Condensing)
Operating Temperature	0°C to 50°C (32°F to 122°F)
Storage Temperature	-10°C to 85°C (14°F to 185°F)
Shipping (Package) Weight	339 g [12 oz]
Included in Package	1 - Gigabit Power over Ethernet extender
Included in Package	1 - instruction manual

Certifications, Reports and Compatibility

