

SmartRack 6U Wall-Mount Standard-Depth Rack Enclosure Cabinet, White

MODEL NUMBER: **SRW6UW**



Description

The SRW6UW is a white 6U Wall-Mount Rack Enclosure Cabinet designed to integrate wall-mounting, easy equipment access, and cable management in IT network applications with limited floor space. Ventilated front door and side panels allow generous airflow to keep equipment operating safely. Adjustable front mounting rails have both square mounting holes (default position) and tapped holes to accommodate up to 6U of standard 19" rackmount equipment. Supports a max load capacity of 200 lbs. A sturdy wall-mount bracket allows the cabinet to quickly be hung on the wall. The SRW6UW comes with a 5-year product warranty.

Features

- 6U wall-mounted enclosure in white
- Ideal for VoIP wiring closets and education venues that require security
- Adjustable mounting depths up to 17" by 2 front vertical rackmount rails
- Dual threaded rails
- Ventilated front door and side panels for increased airflow
- Locking, reversible front door
- Locking, removable side panels
- Fully assembled for quick installation
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) Compliance

Highlights

- Designed for VoIP closets and education environments where equipment needs to be secure and out of the way
- 6U with dual threaded front vertical rails
- Locking, reversible front door and locking, removable side panels
- Fully assembled for quick installation
- Meets all enclosure requirements towards PCI DSS (Payment Card Industry Data Security Standard) Compliance
- Interior vertical posts have square holes for cage nuts plus 12-24 threaded mounting holes

Applications

IT network environments with limited floor space, VoIP closets, and classrooms where equipment needs to be secure and out of the way of students.

Package Includes

- SRW6UW Wallmount Rack Enclosure
- (12) M6 screws
- (12) M6 cage nuts
- (12) M6 washers
- (2) Keys
- Owner's Manual

Specifications

PHYSICAL	
Installed Whole System Maximum Rack Depth (in.)	16.5



Installed Whole System Maximum Rack Depth (cm)	41.91
Installed Whole System Minimum Rack Depth (in.)	3
Installed Whole System Minimum Rack Depth (cm)	7.62
Rack Height (U Spaces)	6
Shipping Dimensions (hwd / in.)	17.5 x 26.5 x 20.5
Shipping Dimensions (hwd / cm)	44.45 x 67.31 x 52.07
Shipping Weight (lbs.)	32
Shipping Weight (kg)	14.51
Unit Dimensions (hwd / in.)	14.5 x 23.5 x 17.5
Unit Dimensions (hwd / cm)	36.83 x 59.69 x 44.45
Unit Weight (lbs.)	29
Unit Weight (kg)	13.15
Color	White
Weight Capacity - Stationary (lbs.)	200
Weight Capacity - Stationary (kg)	90.72
Cable Access Hole Measurement (inches)	9.812 x 2.35 (l x w)
Hinged (Swings Away from Wall Bracket)	No
SPECIAL FEATURES	
Grounding Lug	Front and Back door frames
Seismic Rack	No
CERTIFICATIONS	
Certifications	EIA-310-E
NOM (Mexico)	Tested to NOM (Mexico)
Approvals	RoHS
WARRANTY	
Product Warranty Period (Worldwide)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <http://www.tripplite.com/products/product-certification-agencies>



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com