


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0039000095](#)
Status: **Active**
Overview: Mini-Fit Jr.™ Power Connectors
Description: Mini-Fit® Male Crimp Terminal, Selective Gold (Au) and Selective Tin (Sn) over Nickel (Ni), 16 AWG, Reel

Documents:

Drawing (PDF)	Packaging Specification PK-5558-001 (PDF)
Product Specification PS-5556-002 (PDF)	Test Summary TS-5556-002 (PDF)
Product Specification PS-58691-004 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-58696-004 (PDF)	



General

Product Family	Crimp Terminals
Series	5558
Application	Power
Crimp Quality Equipment	Yes
Overview	Mini-Fit Jr.™ Power Connectors
Packaging Alternative	39-00-0096 (Loose)
Product Name	Mini-Fit®
UPC	800754394994

Physical

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	125.900/mg
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.032µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.80-3.10mm
Wire Size AWG	16
Wire Size mm²	N/A

Electrical

Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

Material Info

Old Part Number	5558GS3
-----------------	---------

Reference - Drawing Numbers

Application Specification	AS-58696-004
Packaging Specification	PK-5558-001
Product Specification	PS-5556-002, PS-58691-004, RPS-51200-003, RPS-58691-003, RPS-58719-004
Sales Drawing	SD-5558-002
Test Summary	TS-5556-002

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Contains SVHC(2015 June 15): No

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS
ELV

Green Image
Not Relevant

Search Parts in this Series

[5558 Series](#)

Mates With

[5556 Mini-Fit® Crimp Terminal](#)

Use With

[5559 Mini-Fit Jr.™ Plug Housing](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
FineAdjust™ Applicator for Insulation OD 2.20-2.45mm,	0639039400

Optimized for 16 AWG Only FineAdjust™ Applicator for Insulation OD 1.80-2.20mm	<u>0639015300</u>
Optimized for 16 AWG Only FineAdjust™ Applicator for Insulation OD 2.60-3.15mm	<u>0639002800</u>
Optimized for 16 AWG Only Hand Crimp Tool for Male and Female Crimp Terminals, 16-24 AWG Wire	<u>0638190900</u>
T2 Terminator™ for insulation OD 2.20-2.45mm	<u>0639103000</u>
optimized for 16 AWG only Extraction Tool	<u>0011030044</u>
T2 Terminator™ for insulation OD 2.60-3.15mm	<u>0639102800</u>
optimized for 16 AWG only	

Japan

Description	Product #
Applicator for M21 1A Bench Press, 18-24 AWG Wire	<u>0570223000</u>
Side-Feed Applicator For Full-Auto Machine	<u>0570223200</u>

This document was generated on 07/21/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION