



## Safety Data Sheet according to (EC) No 1907/2006

Page 1 of 11

LOCTITE 577 known as Loctite 577 PIPE SEALANT 50ML

SDS No. : 168431  
V007.2

Revision: 19.06.2015  
printing date: 28.07.2015

Replaces version from: 01.04.2015

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

LOCTITE 577 known as Loctite 577 PIPE SEALANT 50ML

#### Contains:

Acetic acid, 2-phenylhydrazide  
Maleic acid

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:  
Anaerobic Adhesive

#### 1.3. Details of the supplier of the safety data sheet

Henkel Limited  
2 Bishop Square Business Park  
AL109EY Herfordshire Hatfield

Great Britain

Phone: +44 1606 593933  
Fax-no.: +44 1606 863762

ua-productsafety.uk@uk.henkel.com

#### 1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification (CLP):

Skin sensitizer  
H317 May cause an allergic skin reaction.

Category 1

#### 2.2. Label elements

##### Label elements (CLP):

##### Hazard pictogram:



##### Signal word:

Warning

<b>Hazard statement:</b>	H317 May cause an allergic skin reaction.
<b>Precautionary statement:</b>	***For consumer use only: P101 If medical advice is needed, have product container or label at hand. P102 Keep out of reach of children. P501 Dispose of waste and residues in accordance with local authority requirements***
<b>Precautionary statement: Prevention</b>	P280 Wear protective gloves.
<b>Precautionary statement: Response</b>	P333+P313 If skin irritation or rash occurs: Get medical advice/attention.

**2.3. Other hazards**  
None if used properly.

### SECTION 3: Composition/information on ingredients

#### 3.2. Mixtures

**General chemical description:**  
Anaerobic Sealant

**Declaration of the ingredients according to CLP (EC) No 1272/2008:**

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Lauryl methacrylate 142-90-5	205-570-6	1- < 6 %	Eye Irrit. 2 H319 Skin Irrit. 2 H315 STOT SE 3 H335
Hexadecyl methacrylate 2495-27-4	219-672-3	1- < 2 %	STOT SE 3 H335 Skin Irrit. 2 H315 Eye Irrit. 2 H319
Tetradecyl methacrylate 2549-53-3	219-835-9	1- < 2 %	STOT SE 3 H335 Skin Irrit. 2 H315 Eye Irrit. 2 H319
Acetic acid, 2-phenylhydrazide 114-83-0	204-055-3	0,1- < 1 %	Acute Tox. 3; Oral H301 Skin Irrit. 2 H315 Skin Sens. 1 H317 Eye Irrit. 2 H319 STOT SE 3; Inhalation H335 Carc. 2 H351
Maleic acid 110-16-7	203-742-5 01-2119488705-25	0,1- < 1 %	Acute Tox. 4; Oral H302 Acute Tox. 4; Dermal H312 Skin Irrit. 2 H315 Skin Sens. 1 H317 Eye Irrit. 2 H319 STOT SE 3 H335
Cumene hydroperoxide 80-15-9	201-254-7	0,1- < 1 %	Acute Tox. 4; Dermal H312 STOT RE 2 H373 Acute Tox. 4; Oral H302 Org. Perox. E H242 Acute Tox. 3; Inhalation H331 Aquatic Chronic 2 H411 Skin Corr. 1B H314
1,4-Naphthalenedione 130-15-4	204-977-6	0,01- < 0,1 %	Acute Tox. 3; Oral H301 Skin Irrit. 2; Dermal H315 Skin Sens. 1; Dermal H317 Eye Irrit. 2 H319 Acute Tox. 1; Inhalation H330

			STOT SE 3; Inhalation H335 Aquatic Acute 1 H400 Aquatic Chronic 1 H410 M factor: 10
--	--	--	---

**For full text of the H - statements and other abbreviations see section 16 "Other information".  
Substances without classification may have community workplace exposure limits available.**

**SECTION 4: First aid measures**

**4.1. Description of first aid measures**

Inhalation:

Move to fresh air. If symptoms persist, seek medical advice.

Skin contact:

Rinse with running water and soap.

Obtain medical attention if irritation persists.

Eye contact:

Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

Ingestion:

Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

**4.2. Most important symptoms and effects, both acute and delayed**

SKIN: Rash, Urticaria.

Prolonged or repeated contact may cause eye irritation.

**4.3. Indication of any immediate medical attention and special treatment needed**

See section: Description of first aid measures

**SECTION 5: Firefighting measures**

**5.1. Extinguishing media**

**Suitable extinguishing media:**

Carbon dioxide, foam, powder

**Extinguishing media which must not be used for safety reasons:**

None known

**5.2. Special hazards arising from the substance or mixture**

Oxides of carbon, oxides of nitrogen, irritating organic vapors.

**5.3. Advice for firefighters**

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

**Additional information:**

In case of fire, keep containers cool with water spray.

**SECTION 6: Accidental release measures**

**6.1. Personal precautions, protective equipment and emergency procedures**

Avoid skin and eye contact.

Ensure adequate ventilation.

**6.2. Environmental precautions**

Do not let product enter drains.

**6.3. Methods and material for containment and cleaning up**

For small spills wipe up with paper towel and place in container for disposal.

For large spills absorb onto inert absorbent material and place in sealed container for disposal.

Dispose of contaminated material as waste according to Section 13.

**6.4. Reference to other sections**

See advice in section 8

**SECTION 7: Handling and storage****7.1. Precautions for safe handling**

Avoid skin and eye contact.

See advice in section 8

Hygiene measures:

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

Good industrial hygiene practices should be observed.

**7.2. Conditions for safe storage, including any incompatibilities**

Store in original containers at 8-21°C (46.4-69.8°F) and do not return residual materials to containers as contamination may reduce the shelf life of the bulk product.

Do not store together with food or other consumables (coffee, tea, tobacco, etc.).

**7.3. Specific end use(s)**

Anaerobic Adhesive

**SECTION 8: Exposure controls/personal protection****8.1. Control parameters****Occupational Exposure Limits**

Valid for  
Great Britain

Ingredient [Regulated substance]	ppm	mg/m <sup>3</sup>	Value type	Short term exposure limit category / Remarks	Regulatory list
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS, INHALABLE DUST]		6	Time Weighted Average (TWA):		EH40 WEL
Silicon dioxide 112945-52-5 [SILICA, AMORPHOUS, RESPIRABLE DUST]		2,4	Time Weighted Average (TWA):		EH40 WEL

**Predicted No-Effect Concentration (PNEC):**

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Maleic acid 110-16-7	aqua (freshwater)					0,074 mg/L	
Maleic acid 110-16-7	aqua (intermittent releases)					0,744 mg/L	
Maleic acid 110-16-7	sediment (freshwater)				0,0624 mg/kg		
Maleic acid 110-16-7	STP					3,33 mg/L	

**Derived No-Effect Level (DNEL):**

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Maleic acid 110-16-7	Workers	Dermal	Acute/short term exposure - local effects		0,55 mg/cm <sup>2</sup>	
Maleic acid 110-16-7	Workers	Dermal	Long term exposure - local effects		0,04 mg/cm <sup>2</sup>	
Maleic acid 110-16-7	Workers	Dermal	Acute/short term exposure - systemic effects		58 mg/kg bw/day	
Maleic acid 110-16-7	Workers	Dermal	Long term exposure - systemic effects		3,3 mg/kg bw/day	

**Biological Exposure Indices:**

None

**8.2. Exposure controls:**

## Respiratory protection:

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A

## Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to &gt; 30 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq$  0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to &gt; 480 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq$  0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

## Eye protection:

Wear protective glasses.

## Skin protection:

Wear suitable protective clothing.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties**

Appearance

paste  
yellow

Odor

mild

Odour threshold

No data available / Not applicable

pH

3 - 6

()

Initial boiling point

&gt; 149 °C (&gt; 300.2 °F)

Flash point

&gt; 100 °C (&gt; 212 °F); Pensky Martens closed cup

Decomposition temperature

No data available / Not applicable

Vapour pressure

&lt; 5 mm hg

(27 °C (80.6 °F))

Vapour pressure

&lt; 300 mbar

(50 °C (122 °F))

Density	1,15 - 1,20 g/cm <sup>3</sup>
( )	
Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative)	Slight
(23 °C (73.4 °F); Solvent: Water)	
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	Not available.
Vapor density	Not available.
Oxidising properties	No data available / Not applicable

## 9.2. Other information

No data available / Not applicable

## SECTION 10: Stability and reactivity

### 10.1. Reactivity

Reaction with strong acids.  
Reacts with strong oxidants.

### 10.2. Chemical stability

Stable under recommended storage conditions.

### 10.3. Possibility of hazardous reactions

See section reactivity

### 10.4. Conditions to avoid

Stable

### 10.5. Incompatible materials

See section reactivity

### 10.6. Hazardous decomposition products

Irritating organic vapours.  
carbon oxides.

## SECTION 11: Toxicological information

### 11.1. Information on toxicological effects

#### General toxicological information:

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

#### Oral toxicity:

This material is considered to have low toxicity if swallowed.

#### Skin irritation:

Prolonged or repeated contact may cause skin irritation.

#### Eye irritation:

May cause mild irritation to the eyes.

#### Sensitizing:

May cause an allergic skin reaction.

**Acute oral toxicity:**

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Maleic acid 110-16-7	LD50	708 mg/kg	oral		rat	
Cumene hydroperoxide 80-15-9	LD50	550 mg/kg	oral		rat	

**Acute inhalative toxicity:**

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
---------------------------------	---------------	-------	-------------------------	------------------	---------	--------

**Acute dermal toxicity:**

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Maleic acid 110-16-7	LD50	1.560 mg/kg	dermal		rabbit	

**Skin corrosion/irritation:**

Hazardous components CAS-No.	Result	Exposure time	Species	Method
Cumene hydroperoxide 80-15-9	corrosive		rabbit	Draize Test

**Germ cell mutagenicity:**

Hazardous components CAS-No.	Result	Type of study / Route of administration	Metabolic activation / Exposure time	Species	Method
Cumene hydroperoxide 80-15-9	positive	bacterial reverse mutation assay (e.g Ames test)	without		OECD Guideline 471 (Bacterial Reverse Mutation Assay)
Cumene hydroperoxide 80-15-9	negative	dermal		mouse	

**Repeated dose toxicity**

Hazardous components CAS-No.	Result	Route of application	Exposure time / Frequency of treatment	Species	Method
Cumene hydroperoxide 80-15-9		inhalation: aerosol	6 h/d5 d/w	rat	

**SECTION 12: Ecological information****General ecological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation 1272/2008/EC. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

**12.1. Toxicity****Ecotoxicity:**

Do not empty into drains / surface water / ground water.



Hazardous components CAS-No.	Value type	Value	Acute Toxicity Study	Exposure time	Species	Method
Maleic acid 110-16-7	LC50	> 245 mg/l	Fish	48 h	Leuciscus idus	DIN 38412-15
Maleic acid 110-16-7	EC50	42,81 mg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Cumene hydroperoxide 80-15-9	LC50	3,9 mg/l	Fish	96 h	Oncorhynchus mykiss	OECD Guideline 203 (Fish, Acute Toxicity Test)
Cumene hydroperoxide 80-15-9	EC50	18 mg/l	Daphnia	48 h	Daphnia magna	OECD Guideline 202 (Daphnia sp. Acute Immobilisation Test)
Cumene hydroperoxide 80-15-9	ErC50	3,1 mg/l	Algae	72 h	Pseudokirchnerella subcapitata	OECD Guideline 201 (Alga, Growth Inhibition Test)
1,4-Naphthalenedione 130-15-4	EC50	0,011 mg/l	Algae	72 h	Dunaliella bioculata	OECD Guideline 201 (Alga, Growth Inhibition Test)

## 12.2. Persistence and degradability

### Persistence and Biodegradability:

The product is not biodegradable.

Hazardous components CAS-No.	Result	Route of application	Degradability	Method
Maleic acid 110-16-7	readily biodegradable	aerobic	97,08 %	OECD Guideline 301 B (Ready Biodegradability: CO2 Evolution Test)
Cumene hydroperoxide 80-15-9		no data	0 %	OECD Guideline 301 B (Ready Biodegradability: CO2 Evolution Test)
1,4-Naphthalenedione 130-15-4		no data	0 - 60 %	OECD 301 A - F

## 12.3. Bioaccumulative potential / 12.4. Mobility in soil

### Mobility:

Cured adhesives are immobile.

### Bioaccumulative potential:

No data available.

Hazardous components CAS-No.	LogKow	Bioconcentration factor (BCF)	Exposure time	Species	Temperature	Method
Acetic acid, 2- phenylhydrazide 114-83-0	0,74					
Maleic acid 110-16-7	-1,3				20 °C	OECD Guideline 107 (Partition Coefficient (n- octanol / water), Shake Flask Method)
Cumene hydroperoxide 80-15-9		9,1		calculation		OECD Guideline 305 (Bioconcentration: Flow- through Fish Test)
Cumene hydroperoxide 80-15-9	2,16					
1,4-Naphthalenedione 130-15-4	1,71					

## 12.5. Results of PBT and vPvB assessment

Hazardous components CAS-No.	PBT/vPvB

Maleic acid 110-16-7	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.
-------------------------	---

#### 12.6. Other adverse effects

No data available.

### SECTION 13: Disposal considerations

#### 13.1. Waste treatment methods

Product disposal:

Dispose of in accordance with local and national regulations.

Contribution of this product to waste is very insignificant in comparison to article in which it is used

Disposal of uncleaned packages:

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Waste code

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.

### SECTION 14: Transport information

#### 14.1. UN number

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.2. UN proper shipping name

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.3. Transport hazard class(es)

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.4. Packaging group

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.5. Environmental hazards

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.6. Special precautions for user

Not hazardous according to RID, ADR, ADN, IMDG, IATA-DGR.

#### 14.7. Transport in bulk according to Annex II of MARPOL 73/78 and the IBC Code

not applicable

### SECTION 15: Regulatory information

#### 15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture

VOC content < 3 %  
(2010/75/EC)

#### 15.2. Chemical safety assessment

A chemical safety assessment has not been carried out.

## SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

- H242 Heating may cause a fire.
- H301 Toxic if swallowed.
- H302 Harmful if swallowed.
- H312 Harmful in contact with skin.
- H314 Causes severe skin burns and eye damage.
- H315 Causes skin irritation.
- H317 May cause an allergic skin reaction.
- H319 Causes serious eye irritation.
- H330 Fatal if inhaled.
- H331 Toxic if inhaled.
- H335 May cause respiratory irritation.
- H351 Suspected of causing cancer.
- H373 May cause damage to organs through prolonged or repeated exposure.
- H400 Very toxic to aquatic life.
- H410 Very toxic to aquatic life with long lasting effects.
- H411 Toxic to aquatic life with long lasting effects.

### Further information:

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

### Label elements (DPD):

Xi - Irritant



### Risk phrases:

R43 May cause sensitisation by skin contact.

### Safety phrases:

S24 Avoid contact with skin.  
S37 Wear suitable gloves.  
S51 Use only in well-ventilated areas.

### Additional labeling:

For consumer use only: S2 Keep out of the reach of children.  
S46 If swallowed, seek medical advice immediately and show this container or label.

### Contains:

Maleic acid

**Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.**