

PC Based Oscilloscope 40MHz, 2 Channel



Features:

- 40MHz high bandwidth
- 100MSPS real time sampling rate
- USB 2.0 interface, no external power required
- 23 measurement functions, PASS/FAIL check, FFT
- OS: Windows NT, Windows 2000, Windows XP, Windows 7
- Labview/VB/VC SDK

Specifications:

	Model	72-10155
Horizontal	Channel	2
	Bandwidth	40MHz (-3dB)
	Rise Time	≤8.8ns
	Real-time Sampling Rate	100MSPS
	Equivalent Sampling Rate	50GSPS
	Time Base Range	4ns/div~1h/div (1-2-4 sequences)
	Time Base Precision	±50ppm
Vertical	Input Impedance	Resistance: 1MΩ ; Capacitance: 25 pF
	Input Sensitivity	10mV/div to 5V/div
	Input Coupling	AC, DC and GND (ground level indicator)
	Vertical Resolution	8 bits
	Memory Depth (Sample Points)	10K-64K
	Maximum Input	300V (DC + AC Peak)
Trigger	Source	CH1, CH2, EXT, EXT/10
	Mode	Edge, Alternative
X-Y Mode	X-Axis Input	Channel 1
	Y-Axis Input	Channel 2
	Phase Shift	Max. 3 degree
Cursors and Measurement	Voltage Measurement	Vpp, Vamp, Vmax, Vmin, Vtop, Vmid, Vbase, Vavg, Vrms, Vcrms, Preshoot, Overshoot
	Time Measurement	Frequency, Period, Rise Time, Fall Time, Positive Width, Negative Width, Duty Cycle
	Cursors Measurement	Horizontal, Vertical, Track, Auto Measure Modes
	Waveform Signal Process	.+, -, ×, ÷, FFT, Invert
Others	Auto Set	yes
	Voltage Range	10mV to 5V/div @ × 1 probe 100mV to 50V/div @ × 10 probe 1V to 500V/div @ × 100 probe 10V to 5,000V/div @ × 1,000 probe
	Cursor	Time/frequency difference, voltage difference



PC Based Oscilloscope 40Mhz, 2 Channel



	Model	72-10155
Others	FFT	Rectangular, Hanning, Hamming, Blackman window
	Math	Addition, subtraction, multiplication, division
	Interface	USB2.0
	Power Source	No external power, bus-powered from USB
Mechanics	Dimension	Length: 190mm Width: 100mm Height: 35mm
	Weight	0.29kgs (exclusive of packing and accessories)
	Accessories	2pcs probes, 1pc 2-plugs USB cable

Part Number Table

Description	Part Number
2 Channels PC USB Oscilloscope	72-10155

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.

