

## 2.3-2.9kW Single-Phase Switched PDU, 200-240V (8 C13), C14, 200-240V Input, 6.5ft Cord, 1U Rack-Mount

MODEL NUMBER: PDUMH15HVNET



### Description

Tripp Lite Switched PDU / Power Distribution Unit offers advanced network control and monitoring with the ability to turn on, turn off, recycle or lock-out power to each individual receptacle, monitor site electrical conditions and remotely monitor output power consumption. PowerAlert interface supports remote control and custom notification of user-specified conditions via email, secure web, SNMP, Telnet or SSH interface. Individually switched outlets can be controlled in real-time to remotely reboot unresponsive network hardware, or be custom programmed for user-defined power-up and power-down sequences to ensure proper startup of interdependent IT systems and prevent inrush-related overloads as network equipment is first energized. Unused PDU outlets can be electronically locked off to prevent the connection of unauthorized hardware. PDU output current consumption in amps is displayed locally via visual meter and remotely via web/network interface to warn of potential overloads before critical IT mains or branch breakers trip.

### Features

- 200/208/230/240V Switched Power Distribution Unit / PDU with built-in web/network interface(15A maximum; Agency de-rated to 12A 200/208/240V and 10A at 230V)
- C14 power inlet accepts a wide variety of worldwide input cord options
- Includes 6.5 ft. / 2m C14 cable
- 1U horizontal rackmount form factor
- 8 switched C13 outlets
- Supports power-on, power-off or reboot of each outlet on a real-time or programmable basis
- Enables reboot of locked equipment, custom power-on/power-off sequences, load-shedding of optional loads and disabling unused outlets
- Network interface provides PDU control and data regarding input voltage and output load levels
- Supports user-specified alarm notification thresholds
- In-rack environmental reporting with optional [ENVIROSENSE](#) temperature / humidity sensor and rack access notification with up to 4 optional [SRSWITCH](#) door sensors

### Highlights

- Switched 10/12A 200-240V PDU; 1U horizontal rackmount
- Reports voltage, frequency & loading information via ethernet interface
- Visual current meter; reversible housing
- C14 inlet; 6.5ft / 2m C14 power cable included
- 8 C13 switched outlets with cord retention brackets
- Temperature, humidity and contact-closure monitoring options

### Applications

- Ideal for network configurations requiring a switched, metered and monitored PDU supporting individual outlet rebooting, load shedding and remote web/network current monitoring of critical networking components

### Package Includes

- 1U Switched PDU
- Mounting brackets
- Cord retention plates
- C13 to C14 power cable



- DHCP/Manual configuration support
- 10/100 Mbps auto-sensing
- Real-time clock backup maintains the time of day and date even if the PDU is unpowered
- Tiered access privileges allow an administrator and a guest to login via web browser
- Alert notifications via email or SNMP traps offer immediate event notification
- Firmware upgrade ability supports future product enhancements
- Supports HTTP, HTTPS, PowerAlert Network Management System, SMTP, SNMPv1, SNMPv2, SNMPv3, Telnet, SSH, FTP, DHCP, BOOTP, NTP protocols
- Fully compatible with FREE PowerAlert Network Management System / NMS Software
- Included cord retention brackets keep vital network equipment plugged in and continuously powered

## Specifications

OVERVIEW	
PDU Type	Switched
OUTPUT	
Output Capacity Details	2.5kW (208V), 2.6kW (220V), 2.9kW (240V), 2.4kW (200V), 2.3kW (230V); 15A maximum output at 200/208/220/240V (agency de-rated to 12A continuous) / 10A maximum at 230V
Frequency Compatibility	50 / 60 Hz
Output Receptacles	(8) C13
Output Nominal Voltage	200-240V nominal, single phase
Overload Protection	n/a
Outlet Type	IEC-C13
Customized Load Management Receptacles	8 individually switched output receptacles
Individual Outlet Switching	Yes
INPUT	
PDU Input Voltage	200; 208; 220; 230; 240
Recommended Electrical Service	10A 230V; 12A 208/240V
Maximum Input Amps	15
Maximum Input Amps Details	Agency de-rated to 12A at 200, 208, 220 & 240V; Agency de-rated to 10A at 230V
PDU Plug Type	IEC-320 C14
Input Cord Length (ft.)	6.5
Input Cord Length (m)	2
Input Phase	Single-Phase
USER INTERFACE, ALERTS & CONTROLS	



Front Panel LCD Display	Digital display reports total PDU output current in amps
Front Panel LEDs	8 LEDs display power on-off status for each output receptacle
Switches	n/a
<b>PHYSICAL</b>	
Shipping Dimensions (hwd / in.)	5.3 x 20.7 x 23.2
Shipping Dimensions (hwd / cm)	13.5 x 52.6 x 37.6
Shipping Weight (lbs.)	13.5
Shipping Weight (kg)	6.1
Unit Dimensions (hwd / in.)	1.75 x 17.3 x 14.8
Unit Dimensions (hwd / cm)	2.87 x 43.9 x 37.6
Unit Weight (lbs.)	9
Unit Weight (kg)	4.1
Material of Construction	Metal
Form Factors Supported	1U rackmount. Includes mounting accessories for 2-4 post racks
PDU Form Factor	Horizontal (1U, 2U, etc)
<b>ENVIRONMENTAL</b>	
Storage Temperature Range	5 to 122F (-15 to 50C)
Relative Humidity	5-95% non-condensing
Operating Elevation (ft.)	0-10,000
Operating Elevation (m)	0-3000
<b>COMMUNICATIONS</b>	
SNMP Compatibility	Yes, pre-installed <a href="#">SNMPWEBCARD</a> provides remote monitoring via web, telnet, and SNMP management systems. Remote management gives user ability to turn connected loads on or off individually
<b>SPECIAL FEATURES</b>	
TVSS Grounding	Back panel grounding lug
<b>CERTIFICATIONS</b>	
Certifications	Tested to UL 60950-1 (USA, Canada), Class A (Emissions), NOM (Mexico), CE (IEC 60950), RoHS compliant
<b>WARRANTY</b>	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Worldwide)	2-year limited warranty
-------------------------------------	-------------------------

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>