

# TAA-Compliant Protect It! 6-Outlet Surge Protector, 6-ft. Cord, 1080 Joules, Ethernet Protection, Safety Covers

MODEL NUMBER: TLP66NETAA



## Description

Tripp Lite's TLP66NETAA is compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases. It has 6 outlets, a 6-ft. cord and diagnostic LEDs. The TLP66NETAA has a surge suppression rating of 1080 joules to handle the strongest surges. Built-in RJ45 jacks prevent surges from damaging your network equipment (6ft network cable included). \$25,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only).

## Features

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- 6 outlets with integrated child safety covers
- 6ft cord
- Built-in RJ45 jacks prevent surges from damaging your network equipment (6ft. network cable included)
- Surge suppression rating: 1080 joules
- EMI/RFI noise filtering
- Can accommodate up to 2 transformers without blocking remaining outlets
- Diagnostic LEDs indicate protection present & ground present
- Keyhole supports for wall mounting
- Lighted power switch
- \$25,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

## Highlights

- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases
- 6 outlets / 6-ft cord
- 1080 joule rating
- Ethernet Surge protection
- \$25,000 Ultimate Lifetime Insurance (U.S., Canada, and Puerto Rico only)

## Applications

Personal computers, modems, CAD/CAM/CAE workstations, network nodes, file servers, point-of-sale terminals and more.

## Package Includes

- TLP66NETAA
- 6-ft. network cable
- Instruction manual with warranty information

## Specifications

OUTPUT	
Frequency Compatibility	60 Hz



Output Receptacles	(6) 5-15R
Output (Watts)	1800
Circuit Breaker (amps)	15
Overload Protection	15A resettable illuminated combo switch / circuit breaker
Transformer Accommodation	Supports 2 large transformer plug accessories without covering remaining outlets, accepts up to 4 transformers total
Outlet Safety Covers	6
Outlet Orientation	Block style with two rows of 3 outlets
USB Charging	No
<b>INPUT</b>	
Nominal Input Voltage(s) Supported	120V AC
Recommended Electrical Service	120V (110-125V)
Input Connection Type	NEMA 5-15P
Input Cord Length (ft.)	6
Input Cord Length (m)	1.83
Input Cord Gauge Type	14 gauge, SJT
Voltage Compatibility (VAC)	120
<b>USER INTERFACE, ALERTS &amp; CONTROLS</b>	
Switches	Combination AC circuit breaker and 2-position red illuminated on/off power switch
Diagnostic LED Details	Built-in LEDs confirm suppressor "protection present" (green) and "grounded" (red) status
<b>SURGE / NOISE SUPPRESSION</b>	
AC Suppression Joule Rating	1080
AC Suppression Response Time	< 1 ns
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line surge suppression
Clamping Voltage (RMS)	150
UL1449 Let Through Rating	400v
EMI / RFI Filtering	Up to 40 dB
<b>DATALINE SURGE SUPPRESSION</b>	
Telephone/DSL Protection	No
Cable (Coax) Protection	No
Network (Ethernet) Protection	Yes
<b>PHYSICAL</b>	



Shipping Dimensions (hwd / in.)	11.02 x 7.08 x 1.77
Shipping Dimensions (hwd / cm)	27.99 x 17.98 x 4.50
Shipping Weight (lbs.)	1.97
Shipping Weight (kg)	0.89
Unit Dimensions (hwd / in.)	1.5 x 4.23 x 8.29
Unit Dimensions (hwd / cm)	3.81 x 10.74 x 21.06
Unit Weight (lbs.)	1.32
Unit Weight (kg)	0.60
Material of Construction	Plastic
Integrated Keyhole Mounting Tabs	Keyhole mounting tabs enable wall mounting
Housing Color	Light Gray
Receptacle Color	Dark Gray
Color (AC Line Cord)	Light Gray
Metal Case	No
<b>SPECIAL FEATURES</b>	
Right-Angle Plug	No
<b>CERTIFICATIONS</b>	
UL1449 3rd Edition (AC Suppression)	UL1449 3rd Edition
UL1363 (Power Tap)	UL1363
cUL / CSA (Canada)	cUL
Industry Canada (Communications)	Industry Canada
Approvals	Exceeds IEEE 587 category A&B specifications
<b>WARRANTY</b>	
Product Warranty Period (Worldwide)	Lifetime limited warranty
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$25,000 <a href="#">Ultimate Lifetime Insurance</a>

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>