

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0016021114](#)
Status: **Active**
Overview: [C-Grid® Products](#)
Description: SL™ Crimp Terminal, Series 71851, Female, with Tin (Sn) Plated Contact, 22-24 AWG, Bag

Documents:

[Drawing \(PDF\)](#) [Product Specification PS-71851 \(PDF\)](#)
[Product Specification PS-70400 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family [Crimp Terminals](#)
Series [71851](#)
Application [Signal](#)
Crimp Quality Equipment [Yes](#)
Overview [C-Grid® Products](#)
Packaging Alternative [16-02-1110 \(Reel\)](#)
Product Name [SL™](#)
UPC [800753595798](#)

Physical

Gender [Female](#)
Material - Metal [Phosphor Bronze](#)
Material - Plating Mating [Tin](#)
Material - Plating Termination [Tin](#)
Net Weight [0.067/g](#)
Packaging Type [Bag](#)
Plating min - Mating [3.810µm](#)
Plating min - Termination [1.905µm](#)
Termination Interface: Style [Crimp or Compression](#)
Wire Insulation Diameter [1.63mm max.](#)
Wire Size AWG [22, 24](#)
Wire Size mm² [N/A](#)

Solder Process Data


Lead-freeProcess Capability [N/A](#)

Material Info

Old Part Number [71851-0222](#)

Reference - Drawing Numbers

Product Specification [PS-70400, PS-71851](#)
Sales Drawing [SD-71851-0222](#)



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contains SVHC(17.
December 2014): No

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

[71851 Series](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	0638118700
Insertion Tool	0011020022
Extraction Tool	0011030036