

Duplex Multimode 50/125 Fiber Patch Cable (LC/LC), 3M (10-ft.)

MODEL NUMBER: **N520-03M**



Description

Tripp Lite's 3-meter multimode duplex Fibre Channel optic LC/LC patch cable is manufactured from 50/125 zipcord fiber. The cable has LC connectors on each end. It has a PVC jacket and is FDDI and OFNR rated.

50/125 Duplex multimode fiber is most commonly used in Fibre Channel applications. It is backward compatible with 62.5 micron fiber and provides built-in headroom for future applications. The cable provides higher bandwidth optimized for Gigabit and 10Gbps networks as well. Also available in 1, 2, 5, 10, 15, 20, 25, 30, and 50 meter lengths. Enter "N520-" in the search field to bring up all lengths. For LC-SC cables, search "N516-", and for SC-SC, search "N506-".

Features

- Constructed with 50/125 micron cable
- Length - 3M
- Use on fiber and fibre channel installations
- LC male to LC male connectors
- Higher bandwidth optimized for gigabit and 10Gbps networks
- Backward compatible with 62.5 micron fiber
- Built-in headroom for future applications
- Number of fibers: 2
- Fiber type: all glass graded index
- Core diameter: two 50+/-3 microns
- CLAD diameter: 125+/-2 microns
- Primary coating diameter: 245+/-15 microns
- Primary coating material: acrylate
- Secondary coating diameter: 900+/-50 microns
- Secondary coating material: PVC
- Attenuation @850NM: 3.5DB/KM maximum, @1300NM: 1.0DB/KM maximum
- Bandwidth @850NM: 220 MHz-KM minimum, @1300NM: 600 MHz-KM minimum
- Numeric aperture: .275 nominal

Highlights

- Premium PVC multimode patch cables
- Attenuation loss meets or exceeds the latest industry standards
- Higher bandwidth, optimized for gigabit and 10Gbps networks
- Backward compatible with 62.5 micron fiber
- Built-in headroom for future applications

System Requirements

- Any fiber optic hardware or NIC card requiring multimode duplex cable with LC/LC connectors

Package Includes

- 3M duplex MMF cable LC/LC 50/125 fiber



- Proof test level: 100,000 PSI
- Insertion loss testing performed on every connector (0.2db typical) and provided with cable
- Beveled edge on ends of glass makes insertion of plug a breeze

Specifications

OVERVIEW	
Attenuation @ 1300NM	1.0 DB/KM maximum
Attenuation @ 850NM	3.5 DB/KM maximum
Bandwidth @ 1300NM	600 MHZ-KM minimum
Bandwidth @ 850NM	220 MHZ-KM minimum
Clad Diameter	125 +/- 2 microns
Core Diameter	Two 50 +/- 3 microns
Number of Fibers	2
Numerical Aperture	.275 nominal
Primary Coating Diameter	245 +/- 15 microns
Primary Coating Material	Acrylate
Proof Test Level	100,000 PSI
Secondary Coating Diameter	900 +/- 50 microns
Secondary Coating Material	PVC
Fiber Type	50/125 - OM2
Cable Type	Multimode
INPUT	
Cable Length (ft.)	10
Cable Length (m)	3
PHYSICAL	
Color	Orange
COMMUNICATIONS	
Network Speed	1Gbps
CONNECTIONS	
Connector A	LC DUPLEX (MALE)
Connector B	LC DUPLEX (MALE)



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

WARRANTY	
Product Warranty Period (Worldwide)	Lifetime limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>