

## 3M™ Ground Pro Ground Integrity Meter Model CTM051

Proper grounding is crucial for the safe and uninterrupted operation of equipment. Proper grounding has become one of the most important concerns in facility and tool management. This device is not intended to be used to measure mains voltage.

The Ground Pro Ground Integrity Meter offers a suite of features designed to verify critical grounding parameters in any facility. The Ground Pro measures ground impedance in accordance with ANSI 6.1 standard. One of the key features of the Ground Pro is its data integrity—its proprietary technology allows it to provide accurate measurements of ground impedance on a working tool when ground noise is present, an area where most regular instruments fail.

The Ground Pro is an essential tool for anyone concerned with ensuring proper grounding of equipment during installation, maintenance and throughout regular use.

### Applications

- Front-End Semiconductors
- Photolithography Equipment
- Back-End Semiconductor Tools
- Disk Drive Manufacturing
- Surface Mounted Assembly
- Industrial Robotics
- Tool Clusters

### Features

- ANSI 6.1 compliant measurements
- Auto-zero of test lead impedance
- Broadband EMI measurements
- Signal on ground
- Low-battery Indicator
- Audio alarms

### Key Advantages

- ANSI 6.1 compliant
- Accurate readings in a noisy environment
- EMI – High-frequency noise on a ground increases the probability of equipment malfunction and downtime. EMI can also provide dangerous exposure to sensitive components. The Ground Pro measures high-frequency noise on grounds in a broad frequency range—both average and envelope peak signals.



Properties	Value
<b>Ground Impedance</b>	
Range	Range: 0.000 - 1.999 Ohm, 2% + 0.01 Ohm Range: 00.00 - 19.99 Ohm, 1% + 0.05 Ohm Range: 000.0 - 199.9 Ohm, 1% + 0.5 Ohm Range: 0000 - 1999 Ohm, 1% + 5 Ohm  Automatic auto-zero for test leads
<b>EMI (Noise on Ground)</b>	
Bandwidth	9 kHz - 450 MHz
Measurement Range	10mV ... 5Vpeak 80dBuV ... 134 dBuV
Measurement Type	Average, Peak
<b>Voltage on Ground</b>	
AC (50-500 Hz)	0.001-10V RMS
DC	0.001-10V
<b>General</b>	
Power	Power by battery, 9V Alkaline
Dimension (approx.)	4.5" x 2.4" x 1.1" (114 mm x 60 mm x 28 mm)
Weight (approx.)	223 gm

# 3M™ Ground Pro Ground Integrity Meter Model CTM051

3M is a trademark of 3M Company.

### Important Notice

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.



### Electronics Materials Solutions Division Static Control Products

926 JR Industrial Drive  
Sanford, NC 27332-9733  
Toll-Free: 866-722-3736  
International: 919-718-0000  
Email: [3mstaticinfo@mmm.com](mailto:3mstaticinfo@mmm.com)  
[www.3mstatic.com](http://www.3mstatic.com)

### Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for one year from the time of purchase. **3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE.** If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. **Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.**