

# 2 Channel Thermometer



## Description

This thermometer is microprocessor-based, digital thermometer designed to use external J-, K-, T-, E-, R-, S- and N- type thermocouples as temperature sensors. This model is a dual input (T1, T2) suitable for K-, J-, T-, E-, R-, S- and N- type thermocouples. Equipped with over limit alarm, over limit signal output and user self-debug features.



## Features

- °C/°F/K Selection
- Data Hold
- Auto Power Off
- Low Battery Indication
- MAX Mode
- MIN Mode
- AVG Mode
- Data Logging : 100
- USB Interface
- High Alarm
- Lower Alarm
- High/Lower Signal Output
- LCD Backlight
- Auto Calibration
- Electricity Cut-off Memory

## Specifications

Single or Dual Input	Range	Dual Accuracy	
Temperature	Type K	-200°C to 1372°C(-328°F to 2501°F)	±(0.2%+0.6)
	Type J	-210°C to 1200°C(-346°F to 2192°F)	±(0.2%+0.6)
	Type T	-250°C to 400°C(-418°F to 752°F)	±(0.2%+0.6)
	Type E	-150°C to 1000°C(-238°F to 1832°F)	±(0.2%+0.6)
	Type R	0.0°C to 1767°C(+32°F to 3212°F)	±(0.2%+2)
	Type S	0.0°C to 1767°C(+32°F to 3212°F)	±(0.2%+2)
	Type N	-200°C to 1300°C(-328°F to 2372°F)	±(0.2%+1.5)
Resolution	0.1°C (When Value > 999.9°C:1°C)		

## General Characteristic

Power	USB or 9V Battery (6F22)
LCD Size	30mm × 32mm
Product Colour	Orange and Grey
Product Net Weight	270g
Product Size	175mm × 85mm × 30mm
Standard Accessories	Battery, USB Interface Cable, PC Software CD, Type K Temperature Probe

## Part Number Table

Description	Part Number
2 Channel Thermometer	72-7715

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.

