

# Handheld Digital Storage Oscilloscope **TENMA™**



## Features

- Automatic waveform and status configuration
- Storage of waveforms, setups and interfaces; waveforms and setups reproduction
- Screen copy function
- Fine window extension; precise analysis of waveform details and overview
- Unique waveform recording, storage and replay function
- HD colour 5.7 inch LCD panel at 320 × 240 pixel aspect ratio
- Multiple waveform mathematics functions (including add, subtract, multiply and divide)
- Multimeter function
- USB drive system software upgrade

## Specifications

Channels	: 2
Bandwidth	: 60MHz
Sample Rate	: 250MSPS
Rise Time	: ≤5.8ns
Memory Depth	: 7.5 kpts
Vertical Sensitivity	: 5mV - 50V/div
Time-based Range	: 5ns/div - 50s/div
Storage	: Setup, Waveform, Bitmap
Trigger Modes	: Edge, Pulse, Video and Alternative
Interface	: USB Host

## Multimeter Specifications

	Range	Best Accuracy
DC Voltage (V)	600mV/6V/60V/600V/1000V	±(1% +5)
AC Voltage (V) (45Hz to 400Hz)	600mV/6V/60V/600V/700V	±(1.2% +5), Frequency : <200Hz
		±(1.5% +5), Frequency : ≥200Hz
DC Current (A) (External module)	6mA/60mA/600mA	±(1.2% +5)
	6A	±(1.5% +5)
AC Current (A) (45Hz to 400Hz) (External module)	6mA/60mA/600mA	±(2% +5)
	6A	±(2.5% +5)
Resistance (Ω)	6kΩ/60kΩ/600kΩ	±(1.2% +5)
	600Ω/6MΩ/60MΩ	±(1.5% +5)
Capacitance (F)	6nF/6mF	±(5% +10)
	60nF/600nF/6μF/60μF/600μF	±(4% +5)
Display Count	6,000	
Auto Range	√	

# Handheld Digital Storage Oscilloscope

## General Characteristic

Power	: Lithium Battery: 7.4V 4,400mAh; DC Adapter : 100 - 240V 50/60Hz input, 9V 4A Output
Display	: 5.7 Inches 64K Colour TFT LCD, 320 × 240
Product Colour	: White and Grey
Product Net Weight	: 1.8 kg
Product Size	: 268mm × 168 mm × 60mm
Standard Accessories	: Probe × 2(1×,10× Switchable), Current Voltage Converter × 2(UT-M03,UT-M04), Power Cord, DC Adaptor, Test Lead, PC Software CD
Safety Rating	: DSO CAT III 300V : DMM CAT III 600V

## Part Number Table

Description	Part Number
Oscilloscope, Handheld DSO, 2CH, 60MHz	72-9355

**Important Notice** : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.