

# Modern Digital Multimeter



## Description

The digital multimeter is product designed for multi-functional, high precision, high performance and automatic measurements. The meter can measure AC/DC voltage and current, resistance, diode, circuit continuity, capacitance, frequency, temperature, electromagnetic induction, etc. The meter is widely used in industrial production and service, technological research and design, college education (Laboratory, Courses), and automotive industry.

## Features

- Large LCD screen
- High resolution analog pointer display
- Full range overload protection
- Data hold, REL, Peak value measurement
- Low battery indication, backlight, and sleep mode
- External interface supports RS-232C and USB cable.
- Display Count : 6,000
- Auto Range
- True RMS
- Bandwidth (Hz) : 45Hz to 3kHz
- Duty Cycle : 0.1% to 99.9%
- Diode Test
- Continuity Buzzer
- Low Battery Indication :  $\leq 7.5V$
- Data Hold
- Relative Mode
- MAX/MIN
- Analogue Bar Graph : 61
- Input Protection
- Input Impedance for DCV : Around 10M $\Omega$

## Specifications

	Range	Best Accuracy
DC Voltage (V)	60mV/600mV/6V/60V/600V/1000V	$\pm(0.5\%+1)$
AC Voltage (V)	60mV/600mV/6V/60V/600V/750V	$\pm(1.0\%+3)$
DC Current (A)	600 $\mu$ A/6000 $\mu$ A/60mA/600mA/6A/10A	$\pm(1.0\%+3)$
AC Current (A)	600 $\mu$ A/6000 $\mu$ A/60mA/600mA/6A/10A	$\pm(1.2\%+5)$
Resistance ( $\Omega$ )	600 $\Omega$ /6k $\Omega$ /60k $\Omega$ /600k $\Omega$ /6M $\Omega$ /60M $\Omega$	$\pm(1.0\%+2)$
Capacitance (F)	40nF/400nF/4 $\mu$ F/40 $\mu$ F/400 $\mu$ F/4000 $\mu$ F	$\pm(3.0\%+5)$
Frequency (Hz)	10Hz - 10MHz	$\pm(0.1\%+4)$

## General Characteristic

Power	9V Battery (6F22)
LCD Size	65mm $\times$ 43mm
Product Colour	Orange and Grey
Product Net Weight	370g
Product Size	180mm $\times$ 87mm $\times$ 47mm
Standard Accessories	Battery, Test Lead, Multi-Purpose Socket, RS-232 Interface Cable, PC Software CD
Safety Rating	CAT III 1000V
	CAT IV 600V

## Part Number Table

Description	Part Number
Modern Digital Multimeter	72-10410

**Important Notice :** This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.

