

Light Meter



Features:

- Light Sensor uses exclusive photo diode & colour correction filter, spectrum meets C.I.E. photopic.
- Sensor cosine correction factor meets standard
- Wide range measurement both for Lux & Foot Candle units
- Four lighting type selection (Tungsten, Fluorescent, Sodium or Mercury)
- Microprocessor circuit assures maximum possible accuracy, provides special functions and features
- Large LCD display, easy readout
- Zero adjustment by push button
- Heavy duty & compact housing case
- Separate Light Sensor allows user to measure the light at an optimum position
- Records Maximum, Minimum and Average readings with recall
- Data hold
- Auto shut off saves battery life
- Operates from 006P DC 9V battery

General Specifications:

Circuit	Custom one-chip of micro-processor LSI circuit
Display	13mm (0.5") large LCD
Measurement & ranges	Lux : 0 - 100,000 Lux, 3 ranges
	Foot-candle(Fc) : 0 -10,000 Fc, 3 ranges
Lighting Type Selection	Tungsten, Fluorescent, Sodium, Mercury lamp
Sensor	The exclusive photo diode & colour correction filter, spectrum designed to meet C.I.E.
Memory Recall	Records Maximum, Minimum and Average readings with recall
Zero Adj.	By push button
Sampling Time	Approx. 0.4sec
Power off	Auto shut off saves battery life, or manual off by push button
Over input indication	Indication of " - - - - "
Operating Temp.	0°C to 50°C (32°C to 122°C)
Operating Humidity	Less than 80% RH
Power Supply	006P DC 9V battery (Heavy Duty Type)
Power Current	Approx. DC 5.3 mA
Weight	335g/0.77lb.
Dimension	Main instrument : 185mm × 78mm × 38mm (7.3" × 3.1" × 1.5")
	Sensor probe : 85mm × 55mm × 12mm (3.2" × 2.2" × 0.5")
Optional Carrying case	Soft Carrying Case Hard Carrying Case



Light Meter



Electrical Specifications (23 ±5°C)

Measurement	Range	In-range Display	Resolution	Accuracy
Lux	2,000 Lux	0 - 1,999 Lux	1 Lux	±(5% + 2d)
	20,000 Lux	1,800 - 19,990 Lux	10 Lux	±(5% + 2d)
	100,000 Lux	18,000 - 10,000 Lux	100 Lux	≤50,000 Lux : (5 % + 2 d) > 50,000 Lux : for reference only, no specify the accuracy
Foot-candle (Fc)	200 Fc	0 - 186 Fc	0.1 Fc	± (5% + 2d)
	2,000 Fc	167 - 1,860 Fc	1 Fc	± (5% + 2d)
	10,000 Fc	1,670 - 10,000 Fc	10 Fc	≤4,650 Fc : ± (5% + 2d) > 4,650 Fc : for reference only, no specify the accuracy

Carrying Case Optional

Soft carrying case,	Dimensions : 210mm × 100mm × 70mm, Weight : 81 g
Hard carrying case,	Dimensions : 275mm × 195mm × 64mm, Weight : 465 g

Part Number Table

Description	Part Number
Light Meter	72-6693

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Tenma is the registered trademark of the Group. © Premier Farnell plc 2012.

