

Capacitor, film, 0.047 uF, +/-10% Tol, -40/+110C, General Purpose, 520 VDC@105C, Lead Spacing=10 mm



Dimensions (mm)		
Symbol	Dimension	Tolerance
L	13	+0.2
H	9	+0.1
T	4	+0.2
S	10	+/-0.4
LL	30	+5/-0
F	0.6	+/-0.05

Notes:

-L,H,T are nominal dimensions and do not imply a minimum.

General Information	
Supplier:	KEMET
Dielectric:	Metallized Polypropylene
Application:	General Purpose
Sub Application:	Pulse
Style:	Radial Box
Lead Form:	Wire Leads
RoHS:	Yes

Specifications	
Capacitance:	0.047 uF
Voltage:	520 VDC
Tolerance:	+/-10%
Voltage AC:	250 VAC
Rated Temperature:	105C
Temperature Range:	-40/+110C
Dissipation Factor @ 1 kHz:	0.1%
Dissipation Factor @ 10 kHz:	0.1%
Dissipation Factor @ 100kHz:	0.1%
Insulation Resistance:	100 GOhm
Inductance:	9
Maximum dVdT:	300 v/us
Miscellaneous:	Above 105C DC and AC voltage derating is 4%/C

Packaging Specifications	
Package Kind:	Bulk
Package Quantity:	1800