

SPEC Pak

4 Position - Sealed Power For Environmental Connections



Marine | Wind Power | Lighting | Transportation | Pumps | Ground Support
Machine Tool | Industrial Automation | Motor | Solar Power | Harsh Environments




APP
Anderson Power Products

Rugged and Sealed (IP67) Plugs and Receptacles

For Use with APP Powerpole® Signal, Power & Ground Contacts & Housings

APP's new SPEC Pak Connector Series uses rugged and environmentally sealed (IP67) shells to protect existing APP contacts and housings. Customer configured SPEC Pak Connectors may be used anywhere a rugged or water proof high power, signal and ground interconnect solution is required such as in; mass transportation, off- road vehicles, factory automation, oil and petrochemical exploration, agricultural equipment, and many more.

The core APP Powerpole technology within the SPEC Pak is proven reliable and cost effective. The broad selection of touch safe, color coded Powerpole housings with power, signal and ground contacts accepts a broad range of wire gauges, #24 to #10 AWG (0.25 to 4.0 mm²), giving users 1,000's of flexible design solutions in a single interconnect.



1 - Industry Standard Panel Cut Out (26482/5015 shell size 20)

2 - Panel Mount Gasket (IP67)

3 - Touch Safe Housings (UL1977, Section 10.2)

4 - Interfacial Sealing Gasket (IP67)

5 - Latch (top or bottom of plug or receptacle)

6 - Power Contacts (up to 4) and / or **Signal Contacts** (up to 16)

7 - Uses Industry Standard Sealing Components

8 - First Mate / Last Break Ground Contacts

9 - Color Coded Housings To Wire

10 - Ruggedized Shells

11 - Plug PG Thread (size 16)

HEADQUARTERS: Anderson Power Products®, 13 Pratts Junction Road, Sterling, MA 01564-2305 USA T:978-422-3600 F:978-422-3700

EUROPE: Anderson Power Products® Ltd., Unit 3, Europa Court, Europa Boulevard, Westbrook, Warrington, Cheshire, WA5 7TN United Kingdom T: +44 (0) 1925 428390 F: +44 (0) 1925 428399

ASIA / PACIFIC: IDEAL Anderson Asia Pacific Ltd., Unit 922-928 Topsail Plaza, 11 On Sum Street, Shatin N.T., Hong Kong T:+(852) 2636 0836 F:+(852) 2635 9036

CHINA: IDEAL Anderson Technologies (Shenzhen) Ltd., Block A8 Tantou Western Industrial Park, Songgang Baoan District, Shenzhen, P.R. China 518105 T: +(86) 755 2768 2118 F: +(86) 755 2768 2218

TAIWAN: IDEAL Anderson Asia Pacific Ltd., Taiwan Branch, 4F.-2, No.116, Dadun 20th St., Situn District, Taichung City 407, Taiwan (R.O.C.) T: +(886) 4 2310 6451 F:+(886) 4 2310 6460

www.andersonpower.com

Specifications

SPEC Pak Shell* / Components

Electrical

Voltage Rating (AC/DC)	600
Dielectric Withstanding Voltage (AC)	3000
Operating Temperature (°C)	-20° to 105°
(°F)	-4° to 221°
Flammability Rating of SPEC Shells	UL 94V-0

Mechanical

Shells / Latch Mating Cycles	1500 Min
Average Connect / Disconnect (lbf)	12 Max
(N)	53 Max
IP Rating	IP67
Sealing Exceeds (IP67), Meets Sealing Requirements Of	UL50

Material

SPEC, Shells (Plug / Receptacle)	PBT
SPEC & Latch	Nylon
SPEC Holder	Polycarbonate

* Standard shell color is black (consult factory for other colors)

PP4x (4327 Series) Powerpole® Signal Contact**

Ratings for SPEC Pak Use

Electrical

UL Current Rating (Amperes)	1
Voltage Rating (AC/DC)	300
Contact Barrel Wire Size (AWG)	#20 to #24
(mm ²)	0.5 to 0.25
Contact Retention Force (lbf)	5.4
(N)	24.0
Insertion Force - Max (lbf)	3.3
(N)	14.7
Operating Temperature (°C)	-20° to 105°
(°F)	-4° to 221°

Mechanical

Life	
• Mating Cycles	
- Gold, 30 μ	300
- Tin, 40 μ	30

Material

Housing Material	PBT
Contact Material	Copper Alloy

** PP4x - 4 signal contacts per housing

Powerpole® Power (1327FP Series) & Ground Contact (1827 Series)

Ratings for SPEC Pak Use

Electrical

UL Current Rating (Amperes)	15 to 40
CSA (30°C Rise) (Amperes)	10 to 26
Voltage Rating (AC/DC)	600
Contact Barrel Wire Size (AWG)	20 to 10
(mm ²)	0.5 to 4.0
Average Contact Resistance (micro-ohms)	600
Contact Retention Force (lbf)	25
(N)	111
Operating Temperature (°C)	-20° to 105°
(°F)	-4° to 221°
Flammability Rating	UL94 V-0
Contact Material	Copper
Contact Plating	Tin or Silver

Mechanical


Life	
• No Load (mating cycles)	
- Tin	1,500
- Silver	10,000
• Under Load (Hot Plug 250 mating cycles @ 120V) *	30A
(Hot Plug 250 mating cycles @ 72V) *	45A
Mechanical Shock (50 g)	Mil Standard 202 213 Cond. A
Vibration (10 g)	Mil Standard 202 204 Cond. A

Material

Housing Material	Polycarbonate
Touch Safe (Power / Signal Housing)	UL1977 Sec. 10.2

* Hot Plug testing completed with individual Powerpole housings

TEMPERATURE CHART



NOTE: Agency approvals - TUV Pending / Patents Pending



File No. E26226



HEADQUARTERS: Anderson Power Products®, 13 Pratts Junction Road, Sterling, MA 01564-2305 USA T:978-422-3600 F:978-422-3700

EUROPE: Anderson Power Products® Ltd., Unit 3, Europa Court, Europa Boulevard, Westbrook, Warrington, Cheshire, WA5 7TN United Kingdom T: +44 (0) 1925 428390 F: +44 (0) 1925 428399

ASIA / PACIFIC: IDEAL Anderson Asia Pacific Ltd., Unit 922-928 Topsail Plaza, 11 On Sum Street, Shatin N.T., Hong Kong T: +(852) 2636 0836 F: +(852) 2635 9036

CHINA: IDEAL Anderson Technologies (Shenzhen) Ltd., Block A8 Tantou Western Industrial Park, Songgang Baoan District, Shenzhen, P.R. China 518105 T: +(86) 755 2768 2118 F: +(86) 755 2768 2218

TAIWAN: IDEAL Anderson Asia Pacific Ltd., Taiwan Branch, 4F.-2, No.116, Dadun 20th St., Situn District, Taichung City 407, Taiwan (R.O.C.) T: +(886) 4 2310 6451 F: +(886) 4 2310 6460


www.andersonpower.com

Part Number Configurator


PART NUMBER PLAN

SPEC Pak Series (1 Fixed Character)	Shell Color (1 Character)	Shell Style (1 Character)	Dash	Shell Size (mm) (3 Characters)	Insert Arrangement (3 Characters)
S	K	2	-	050	B04
S = SPEC Pak Series	K = Black	2 = Panel Mount Receptacle 6 = Straight Plug 9 = Cover		050 = 50 mm - 4 Pole Shell	B04 = PP15/45 Housing (any type), 4 Pole


RECEPTACLE KIT



PLUG KIT



COVER KIT



NOTE:
 - Mounting hardware not included
 - Recommended mounting hardware is #4 screw
 - Recommended torque for mounting hardware is 2½ to 4 in-lbf (0.28 to 0.45 Nm)

ORDERING INFORMATION

SPEC Pak Kits

Part Number	Description
SK6-050B04	Plug Kit - plug shell (includes interfacial sealing gasket) - powerpole holder for plug
SK2-050B04	Receptacle Kit - panel mount gasket for receptacle - powerpole holder for receptacle - receptacle shell with latch
SK9-050	Cover Kit - protective sealing cover for receptacle with lanyard

Component Replacement Parts

Part Number	Description
114805P1	Panel mount gasket for receptacle
2-8673P1	4 position latch

HEADQUARTERS: Anderson Power Products®, 13 Pratts Junction Road, Sterling, MA 01564-2305 USA T:978-422-3600 F:978-422-3700

EUROPE: Anderson Power Products® Ltd., Unit 3, Europa Court, Europa Boulevard, Westbrook, Warrington, Cheshire, WA5 7TN United Kingdom T: +44 (0) 1925 428390 F: +44 (0) 1925 428399


ASIA / PACIFIC: IDEAL Anderson Asia Pacific Ltd., Unit 922-928 Topsail Plaza, 11 On Sum Street, Shatin N.T., Hong Kong T: +(852) 2636 0836 F: +(852) 2635 9036

CHINA: IDEAL Anderson Technologies (Shenzhen) Ltd., Block A8 Tantou Western Industrial Park, Songgang Baoan District, Shenzhen, P.R. China 518105 T: +(86) 755 2768 2118 F: +(86) 755 2768 2218

TAIWAN: IDEAL Anderson Asia Pacific Ltd., Taiwan Branch, 4F.-2, No.116, Dadun 20th St., Situn District, Taichung City 407, Taiwan (R.O.C.) T: +(886) 4 2310 6451 F: +(886) 4 2310 6460

www.andersonpower.com

PART NUMBER PLAN



Part Numbering Notes:

- 1) To order SPEC Pak "Kits Only" (no internal Powerpole housings or contacts), use part numbering on page 4 only. Powerpole housings and contacts may be ordered separately, see page 10 for information. **Plug Kit Example: SK6-050B04**
- 2) To order complete standard configured SPEC Pak connectors (including internal Powerpole housings and contacts) use part numbering on page 4 and 5. **Standard SPEC Pak Plug Configuration Example: SK6-050B04PS01-B01**
- 3) To order a configuration which is not listed on page 8 and 9 (Custom Configuration), use APP custom part number configurator on the APP website, www.andersonpower.com.

PG Glands

SPECIFICATIONS

Material (Push-in Conduit)

Shell	Nylon PA
Gasket	TPE
Color**	Black

Mechanical

Operating Temp	-30°C to 100°C (-22°F to 212°F)
IP Rating	IP68*
Thread Type	PG

Material (All Others)

Shell	Nylon PA66 (UL94 V-2)**
Gasket	EPDM
Color**	Black

Mechanical

Operating Temp	-40°C to 100°C (-40°F to 212°F)
IP Rating	IP68***
Thread Type	PG

Torque Requirements

Cable Gland Body to Plug Housing
- Hand tighten until snug, tighten additional 1/8 - 1/4 turn with wrench


Sealing Nut to Cable
- Hand tighten until snug, tighten additional 1/2 - 3/4 turn with wrench



* Per EN60529 ** Contact factory for UL94 V-0 material *** (5 Bar pressure)


NOTE: Only UL listed cable glands are UL recognized components when used with SPEC Pak connector(s). Contact Factory for Gray Color Housing.

STRAIGHT PLASTIC SHORT THREAD TYPE



APP P/N	Wire Protection Designation (4 Characters)	Cable Range Wire Outer Dia. mm (in)	Thread O. D. C1 mm (in)	Panel Mounting Hole mm (in)	Thread Length C2 mm (in)	Wrench Size Lock Nut (mm)	Wrench Size Sealing Nut (mm)	Std. Pkg. Pcs.	UL Listed
PS1P16-10X	PS01	11.2 - 5.5 (0.44 - 0.22)	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	10.0 (0.39)	30	27	50	Yes
PS1P16-14X	PS02	14.1 - 8.0 (0.56 - 0.31)	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	10.0 (0.39)	30	27	50	Yes

STRAIGHT PLASTIC WITH FLEX SPRING



APP P/N	Wire Protection Designation (4 Characters)	Cable Range Wire Outer Dia. mm (in)	Thread O. D. C1 mm (in)	Panel Mounting Hole mm (in)	Thread Length C2 mm (in)	Wrench Size Lock Nut (mm)	Wrench Size Sealing Nut (mm)	Std. Pkg. Pcs.	UL Listed
PF1P16-10X	PF01	11.2 - 5.5 (0.44 - 0.22)	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	11.0 (0.43)	30	27	50	Yes
PF1P16-13X	PF02	13.8 - 8.0 (0.54 - 0.31)	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	11.0 (0.43)	30	27	50	Yes

RIGHT ANGLE



APP P/N	Wire Protection Designation (4 Characters)	Cable Range Wire Outer Dia. mm (in)	Thread O. D. C1 mm (in)	Panel Mounting Hole mm (in)	Thread Length C2 mm (in)	Wrench Size Lock Nut (mm)	Wrench Size Sealing Nut (mm)	Std. Pkg. Pcs.	UL Listed
PR1P16-10X	PR01	11.0 - 7.0 (0.43 - 0.28)	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	12.0 (0.47)	30	27	50	No
PR1P16-13X	PR02	13.0 - 8.0 (0.51 - 0.31)	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	12.0 (0.47)	30	27	50	No

HEADQUARTERS: Anderson Power Products®, 13 Pratts Junction Road, Sterling, MA 01564-2305 USA T:978-422-3600 F:978-422-3700

EUROPE: Anderson Power Products® Ltd., Unit 3, Europa Court, Europa Boulevard, Westbrook, Warrington, Cheshire, WA5 7TN United Kingdom T: +44 (0) 1925 428390 F: +44 (0) 1925 428399


ASIA / PACIFIC: IDEAL Anderson Asia Pacific Ltd., Unit 922-928 Topsail Plaza, 11 On Sum Street, Shatin N.T., Hong Kong T:+(852) 2636 0836 F:+(852) 2635 9036

CHINA: IDEAL Anderson Technologies (Shenzhen) Ltd., Block A8 Tantou Western Industrial Park, Songgang Baoan District, Shenzhen, P.R. China 518105 T: +(86) 755 2768 2118 F: +(86) 755 2768 2218

TAIWAN: IDEAL Anderson Asia Pacific Ltd., Taiwan Branch, 4F.-2, No. 116, Dadun 20th St., Situn District, Taichung City 407, Taiwan (R.O.C.) T: +(886) 4 2310 6451 F: +(886) 4 2310 6460


www.andersonpower.com

STRAIGHT PLASTIC MULTI-HOLE TYPE




APP P/N	Wire Protection Designation (4 Characters)	Cable Range Wire Outer Dia. mm (in)	Thread O.D. C1 mm (in)	Panel Mounting Hole mm (in)	Thread Length C2 mm (in)	Wrench Size Lock Nut (mm)	Wrench Size Sealing Nut (mm)	Std. Pkg. Pcs.	UL Listed
PS2P16-3X	PM21	3.5 - 2.5 (0.14 - 0.10)	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	11.0 (0.43)	30	27	50	No
PS2P16-4X	PM22	4.3 - 3.3 (0.17 - 0.13)	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	11.0 (0.43)	30	27	50	No
PS2P16-6X	PM23	6.1 - 4.3 (0.24 - 0.17)	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	11.0 (0.43)	30	27	50	No
PS3P16-3X	PM31	3.6 - 2.6 (0.14 - 0.10)	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	11.0 (0.43)	30	27	50	No
PS3P16-5X	PM32	5.2 - 3.5 (0.20 - 0.14)	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	11.0 (0.43)	30	27	50	No
PS4P16-2X	PM41	2.5 - 1.6 (0.10 - 0.06)	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	11.0 (0.43)	30	27	50	No
PS4P16-3X	PM42	3.6 - 2.5 (0.14 - 0.10)	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	11.0 (0.43)	30	27	50	No
PS4P16-4X	PM43	4.8 - 3.4 (0.19 - 0.13)	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	11.0 (0.43)	30	27	50	No
PS5P16-2X	PM51	2.1 - 1.3 (0.08 - 0.05)	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	11.0 (0.43)	30	27	50	No
PS5P16-3X	PM52	3.1 - 2.0 (0.12 - 0.08)	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	11.0 (0.43)	30	27	50	No
PS5P16-4X	PM53	4.1 - 3.0 (0.16 - 0.12)	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	11.0 (0.43)	30	27	50	No
PS6P16-2X	PM61	2.0 - 1.3 (0.08 - 0.05)	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	10.0 (0.39)	30	27	50	No
PS6P16-3X	PM62	3.0 - 2.0 (0.12 - 0.08)	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	11.0 (0.43)	30	27	50	No

STRAIGHT CONDUIT ADAPTER THREAD TYPE



APP P/N	Wire Protection Designation (4 Characters)	Max. Joint F1 mm (in)	Thread O.D. C1 mm (in)	Panel Mounting Hole mm (in)	Thread Length C2 mm (in)	Wrench Size Lock Nut (mm)	APP Conduit P/N	Conduit Trade Size	Std. Pkg. Pcs.	UL Listed
CT1P16-15X	CT01	16.0 (0.63)	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	11.0 (0.43)	30	NGN - 12B	AD15.8	50	No
CT1P16-18X	CT02	18.3 (0.72)	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	11.0 (0.43)	30	NGN - 14B	-	50	No
CT1P16-21X	CT03	22.0 (0.87)	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	10.0 (0.39)	30	NGN - 17B	AD21.2	50	No

STRAIGHT CONDUIT PUSH-IN TYPE



APP P/N	Wire Protection Designation (4 Characters)	Thread O.D. C1 mm (in)	Panel Mounting Hole mm (in)	Thread Length C2 mm (in)	Wrench Size Lock Nut (mm)	Wrench Size Sealing Nut (mm)	APP Conduit P/N	Conduit Trade Size	Std. Pkg. Pcs.	UL Listed
CAP16-15X	CA01	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	10.0 (0.39)	30	21	NGN - 12B	AD15.8	50	No
CAP16-18X	CA02	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	10.0 (0.39)	30	21	-	AD18.5	50	No
CAP16-21X	CA03	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	10.0 (0.39)	30	27	NGN - 17B	AD21.2	50	No
CAP16-28X	CA04	22.5 (0.89)	22.5 - 22.8 (0.89 - 0.90)	12.0 (0.47)	30	34	NGN - 23B	AD28.5	50	No

For R/A versions contact Factory

CORRUGATED NYLON PLASTIC TUBING

APP P/N	Conduit I. D. mm (in)	Conduit O. D. mm (in)	Conduit Size	Trade Size	Std. Pkg. Meters (Feet)
NGN - 12B	11.8 (0.46)	15.8 (0.62)	3/8"	AD15.8	50 (164)
NGN - 14B	13.8 (0.54)	17.8 (0.70)	-	-	50 (164)
NGN - 17B	16.7 (0.66)	21.2 (0.83)	1/2"	AD21.2	50 (164)
NGN - 23B	21.7 (0.85)	28.5 (1.12)	3/4"	AD28.5	50 (164)

LOCK NUT FOR PG16 CABLE GLANDS



APP P/N	Std. Pkg. Size
124G31	50

HEADQUARTERS: Anderson Power Products®, 13 Pratts Junction Road, Sterling, MA 01564-2305 USA T:978-422-3600 F:978-422-3700

EUROPE: Anderson Power Products® Ltd., Unit 3, Europa Court, Europa Boulevard, Westbrook, Warrington, Cheshire, WA5 7TN United Kingdom T: +44 (0) 1925 428390 F: +44 (0) 1925 428399

ASIA / PACIFIC: IDEAL Anderson Asia Pacific Ltd., Unit 922-928 Topsail Plaza, 11 On Sum Street, Shatin N.T., Hong Kong T: +(852) 2636 0836 F: +(852) 2635 9036

CHINA: IDEAL Anderson Technologies (Shenzhen) Ltd., Block A8 Tantou Western Industrial Park, Songgang Baoan District, Shenzhen, P.R. China 518105 T: +(86) 755 2768 2118 F: +(86) 755 2768 2218

TAIWAN: IDEAL Anderson Asia Pacific Ltd., Taiwan Branch, 4F.-2, No.116, Dadun 20th St., Situn District, Taichung City 407, Taiwan (R.O.C.) T: +(886) 4 2310 6451 F: +(886) 4 2310 6460

www.andersonpower.com

Standard Housing Arrangements & Contacts

HOUSING ARRANGEMENTS FOR POWER, SIGNAL & GROUND CONNECTORS

ARRANGEMENTS REPRESENT FRONT VIEW OF RECEPTACLE

Custom configurations may be created using APP's part number configurator at www.andersonpower.com

E = Empty

1327 Series = Power

1827 Series = Ground

4327 Series = Signal

0 Housings Purchased Separately

AC Single Phase

A	1327G6FP	E
	1327G7FP	1827G1

AC 3 Phase, 3 Wire

B	1327G6FP	1327FP
	1327G7FP	1827G1

DC 2 Circuit, 4 Wire

C	1327G6FP	1327G6FP
	1327FP	1327FP

DC 2 Wire With Ground

D	1327G6FP	1327FP
	E	1827G1

DC 2 Wire With 8 Signal

H	4327G6	4327G6
	1327G6FP	1327FP

AC Single Phase With 4 Signal

J	1327G6FP	4327G6
	1327G7FP	1827G1

DC 2 Wire With 4 Signal

L	1327G6FP	1327FP
	E	4327G6

DC 2 Wire With Ground & 4 Signal

N	1327G6FP	1327FP
	4327G6	1827G1

HEADQUARTERS: Anderson Power Products®, 13 Pratts Junction Road, Sterling, MA 01564-2305 USA T:978-422-3600 F:978-422-3700

EUROPE: Anderson Power Products® Ltd., Unit 3, Europa Court, Europa Boulevard, Westbrook, Warrington, Cheshire, WA5 7TN United Kingdom T: +44 (0) 1925 428390 F: +44 (0) 1925 428399

ASIA / PACIFIC: IDEAL Anderson Asia Pacific Ltd., Unit 922-928 Topsail Plaza, 11 On Sum Street, Shatin N.T., Hong Kong T: +(852) 2636 0836 F: +(852) 2635 9036

CHINA: IDEAL Anderson Technologies (Shenzhen) Ltd., Block A8 Tantou Western Industrial Park, Songgang Baoan District, Shenzhen, P.R. China 518105 T: +(86) 755 2768 2118 F: +(86) 755 2768 2218

TAIWAN: IDEAL Anderson Asia Pacific Ltd., Taiwan Branch, 4F.-2, No.116, Dadun 20th St., Situn District, Taichung City 407, Taiwan (R.O.C.) T: +(886) 4 2310 6451 F: +(886) 4 2310 6460

www.andersonpower.com

CONTINUOUS CURRENT RATINGS - POWER CONTACT CODE SELECTION

Contact Code	Power Contact	Housing Configuration	Wire Size / Current Rating					
			#10	#12	#14	#16	#18	#20
00	Contacts Purchased Separately							
01	261G2	A - D	25/38	20/30	15/25	-	-	-
		H,J,L,N	26/40	25/35	17/27	-	-	-
02	200G1L	A - D	23/35	18/28	15/23	-	-	-
		H,J,L,N	24/37	23/32	15/25	-	-	-
03	261G1	A - D	-	20/30	15/25	11/16	-	-
		H,J,L,N	-	25/35	17/27	13/20	-	-
04	1331	A - D	-	16/25	15/23	12/18	-	-
		H,J,L,N	-	17/27	17/25	13/20	-	-
05	262G1	A - D	-	-	-	11/16	8/13	6/9
		H,J,L,N	-	-	-	13/20	10/15	7/10
06	1332	A - D	-	-	-	12/18	8/13	6/9
		H,J,L,N	-	-	-	13/20	10/15	7/10

NOTES:


1. Current ratings:

- First number represents current rating per pole for 30°C temperature rise [25 / 38]
- Second number is the maximum recommended current per pole based on a 25°C ambient (25 / 38)

2. Configuration H - N based on signal contacts crimped to #20 AWG wire and carrying 1 amp

3. — Denotes wire size not appropriate for power contact

HOLDER LOCATIONS (VIEWS)



Individual Components

POWERPOLE HOUSINGS & CONTACTS

Standard PP 15/45

Housing Only

Part Number	Description
1327	Red Housing
1327G5	Green Housing
1327G6	Black Housing
1327G7	White Housing
1327G8	Blue Housing
1327G16	Yellow Housing
1327G17	Orange Housing
1327G18	Gray Housing
1327G21	Brown Housing
1327G22	Pink Housing
1327G23	Purple Housing

Fingerproof PP15/45

Housing Only

Part Number	Description
1327FP	Red Housing
1327G5FP	Green Housing
1327G6FP	Black Housing
1327G7FP	White Housing
1327G8FP	Blue Housing
1327G16FP	Yellow Housing

15/45 Powerpole Contacts

Loose Piece

Part Number	Description
#16 to #20 AWG (1.0 to 0.5 mm ²)	
1332	Individual-LD-Silver Plate
262G1-LPBK	Singulated Reel-LD-Tin Plate
200G2L-LPBK	Superflex, Sing. Reel-LD-Tin Plate
#12 to #16 AWG (2.5 to 1.0 mm ²)	
1331	Individual-LD-Silver Plate
261G1-LPBK	Singulated Reel-LD-Tin Plate
#10 to #14 AWG (4.0 to 1.5 mm ²)	
261G2-LPBK	Singulated Reel-LD-Tin Plate
200G1L-LPBK	Superflex, Sing. Reel-LD-Tin Plate

Reel - 15/45 Powerpole Contacts

Part Number	Description
#16 to #20 AWG (1.0 to 0.5 mm ²)	
262G1	Reel-LD-Tin Plate
200G2L	SuperFlex, Reel-LD-Tin Plate
#12 to #16 AWG (2.5 to 1.0 mm ²)	
261G1	Reel-LD-Tin Plate
#10 to #14 AWG (4.0 to 1.5 mm ²)	
261G2	Reel-HD-Tin Plate
200G1L	SuperFlex, Reel-LD-Tin Plate

Premate Ground PP15/45

Housing Only

Part Number	Description
1827G1	Green Housing
1827G2	Brown Housing

Premate Ground Contacts

Loose Piece

Part Number	Description
#10 to #14 AWG (4.0 to 1.5 mm ²)	
1830G1-LPBK	Singulated Reel-LD

Reel

Part Number	Description
#10 to #14 AWG (4.0 to 1.5 mm ²)	
1830G1	Reel-LD

LD - low detent

NOTE: For additional housing colors please contact customer service

HEADQUARTERS: Anderson Power Products®, 13 Pratts Junction Road, Sterling, MA 01564-2305 USA T:978-422-3600 F:978-422-3700

EUROPE: Anderson Power Products® Ltd., Unit 3, Europa Court, Europa Boulevard, Westbrook, Warrington, Cheshire, WA5 7TN United Kingdom T: +44 (0) 1925 428390 F: +44 (0) 1925 428399

ASIA / PACIFIC: IDEAL Anderson Asia Pacific Ltd., Unit 922-928 Topsail Plaza, 11 On Sum Street, Shatin N.T., Hong Kong T: +(852) 2636 0836 F: +(852) 2635 9036

CHINA: IDEAL Anderson Technologies (Shenzhen) Ltd., Block A8 Tantou Western Industrial Park, Songgang Baoan District, Shenzhen, P.R. China 518105 T: +(86) 755 2768 2118 F: +(86) 755 2768 2218

TAIWAN: IDEAL Anderson Asia Pacific Ltd., Taiwan Branch, 4F.-2, No.116, Dadun 20th St., Situn District, Taichung City 407, Taiwan (R.O.C.) T: +(886) 4 2310 6451 F: +(886) 4 2310 6460

www.andersonpower.com

PP4X (4327G6) HOUSING & CONTACTS

PP4x

Housing Only

Part Number	Description
4327G6	Black housing

PP4x Housing & Contacts

100 Black Housings, 210 Male Contacts,
210 Female Contacts



Part Number	Description
4330G6	Tin plated contacts - pin & socket
4350G6	30u gold plated contacts - pin & socket

Contacts

#20 to #24 AWG (0.50 to 0.25 mm²) - Reel

Part Number	Description
4202G1	Female Socket, Tin Plated reel contact
4203G1	Male Pin, Tin Plated reel contact
4202G3	Female Socket, 30u Gold Plated reel contact
4203G3	Male Pin, 30u Gold Plated reel contact

PP15/45 POWERPOLE HOUSING STYLES



CONNECTOR TOOLING

Contacts			Hand Tools *		Pneumatic * Bench Mount Tools	Semi-Automatic Tooling		
Contact	Type	Wire Size	Contact Insertion / Extraction Tool	Hand Tool P/N	Pneumatic Tool P/N	Applicator	Press	Adapter Kit
1332	Closed Barrel	#16 to #20 AWG (1.0 to 0.5mm ²)	111038G2	1309G2 1309G8**	1367G1	N/A	N/A	N/A
262G1	Reel				N/A	1385519	1725900-2	1424266-1
							354500-1	354578-1
1331	Closed Barrel	#12 to #16 AWG (2.5 to 1.0mm ²)	111038G2	1309G3 1309G8**	1367G1	N/A	N/A	N/A
261G1	Reel				N/A	1385520	1725900-2	1424266-1
							354500-1	354578-1
261G2	Reel	#10 to #14 AWG (4.0 to 1.5mm ²)	111038G2	1309G3 1309G8**	N/A	1385458	1725900-2	1424266-1
							354500-1	354578-1
200G1L	Reel	#10 to #14 AWG for Superflex (4.0 to 1.5mm ²)	111038G2	1309G6 1309G8**	N/A	1385460	1725900-2	1424266-1
							354500-1	354578-1
200G2L	Reel	#16 to #20 AWG for Superflex (1.0 to 0.5mm ²)	111038G2	1309G6 1309G8**	N/A	260G19	250G1	N/A
							260G1	N/A
1830G1	Reel	#10 to #14 AWG (4.0 to 1.5mm ²)	111038G2	1309G6 1309G8**	N/A	1385460	354500-1	354578-1
4202G1	Reel	#20 to #24 AWG (0.5 to 0.25mm ²)	N/A	1313G1	N/A	680673-3	354500-1	N/A
4202G3	Reel							
4203G1	Reel							
4203G3	Reel							

* All Hand Tools for use with Loose Piece contacts only. All reeled contacts can be ordered singulated, (Loose Piece) with the suffix "- LPBK"

** 1309G8 is a hand tool kit- includes dies and locators to make up 1309G2, 1309G3, & 1309G6

HEADQUARTERS: Anderson Power Products®, 13 Pratts Junction Road, Sterling, MA 01564-2305 USA T:978-422-3600 F:978-422-3700

EUROPE: Anderson Power Products® Ltd., Unit 3, Europa Court, Europa Boulevard, Westbrook, Warrington, Cheshire, WA5 7TN United Kingdom T: +44 (0) 1925 428390 F: +44 (0) 1925 428399

ASIA / PACIFIC: IDEAL Anderson Asia Pacific Ltd., Unit 922-928 Topsail Plaza, 11 On Sum Street, Shatin N.T., Hong Kong T: +(852) 2636 0836 F: +(852) 2635 9036

CHINA: IDEAL Anderson Technologies (Shenzhen) Ltd., Block A8 Tantou Western Industrial Park, Songgang Baoan District, Shenzhen, P.R. China 518105 T: +(86) 755 2768 2118 F: +(86) 755 2768 2218


TAIWAN: IDEAL Anderson Asia Pacific Ltd., Taiwan Branch, 4F.-2, No.116, Dadun 20th St., Situn District, Taichung City 407, Taiwan (R.O.C.) T: +(886) 4 2310 6451 F: +(886) 4 2310 6460

www.andersonpower.com


Dimensions

PLUG 4 POSITION FOR PP15/45


Top View




Front View



Side View




Mated Side View




RECEPTACLE 4 POSITION FOR PP15/45 HOUSINGS

Panel Cut Out




PANEL CUT OUT \varnothing
(SAME AS 26482/5015 SHELL SIZE 20)


Front View



Side View




Back View




NOTE: Mounting hardware #4 screw / torque receptacle to panel 2½ to 4 in-lbf (0.28 to 0.45 Nm)

PG GLANDS


PR - Right Angle




PS - Plastic Short




CT - Threaded Conduit Adapter



CA - Push-in Conduit Adapter




PF - Plastic Flex PG




RECEPTACLE COVER KIT


Front View



Side View



Mated Side View



All Data Subject To Change Without Notice **Patents Pending**

DS-4PSPAK REV00

HEADQUARTERS: Anderson Power Products®, 13 Pratts Junction Road, Sterling, MA 01564-2305 USA T:978-422-3600 F:978-422-3700

EUROPE: Anderson Power Products® Ltd., Unit 3, Europa Court, Europa Boulevard, Westbrook, Warrington, Cheshire, WA5 7TN United Kingdom T: +44 (0) 1925 428390 F: +44 (0) 1925 428399

ASIA / PACIFIC: IDEAL Anderson Asia Pacific Ltd., Unit 922-928 Topsail Plaza, 11 On Sum Street, Shatin N.T., Hong Kong T: +(852) 2636 0836 F: +(852) 2635 9036

CHINA: IDEAL Anderson Technologies (Shenzhen) Ltd., Block A8 Tantou Western Industrial Park, Songgang Baoan District, Shenzhen, P.R. China 518105 T: +(86) 755 2768 2118 F: +(86) 755 2768 2218

TAIWAN: IDEAL Anderson Asia Pacific Ltd., Taiwan Branch, 4F.-2, No. 116, Dadun 20th St., Situn District, Taichung City 407, Taiwan (R.O.C.) T: +(886) 4 2310 6451 F: +(886) 4 2310 6460

www.andersonpower.com