





DIN Rail Mount Pluggable Thermal Circuit Breakers

Conductor Range:	AWG 24 - 10 AWG (stranded and solid)	Terminal Block Width:	8 mm / 0.315 in
		Strip Length:	 12 - 13 mm / 0.49 in
Electrical Specs:	600 V maximum* 25/30 A maximum*	*Current / Voltage limited to circuit breaker specifications. Consult factory for other ratings.	





DIN rail mount pluggable miniature **thermal circuit breakers** are used for protection of power distribution systems, automation systems, and process control applications. These wide variety of circuit breakers have unique characteristics that tailor to the needs and performance of many different applications.


The WAGO circuit breaker terminal block uses CAGE CLAMP[®] connection technology that reduces wiring time and provides a connection that is corrosion-resistant, temperature cycling resistant and maintenance-free. An excellent alternative to traditional fusing methods.


	Technical Data		
	Voltage rating: AC 250 V; DC 65 V Current ratings: 0.1...10 A Typical life: 3,000 operations at 1 x I _N (low-resistive) 500 operations at 2 x I _N (inductive) Ambient temperature: -20...+60°C (T 60) -4...+140°F Insulation co-ordination: (IEC 60664 and 60664A) Rated impulse withstand voltage 2.5 kV reinforced insulation in operating area Insulation resistance: >100 MΩ (DC 500 V)	Interrupting capacity: AC 250 V: 2,000 A (UL 1077) DC 65 V: 200 A Vibration: 5 g (57-500 Hz) ±0.38 mm (10-57Hz) to IEC 60068-2-6, test Fc, 10 frequency cycles/axis Shock: 25 g (11 ms) to IEC 60068-2-27, test Ea Corrosion: 96 hours at 5% salt mist, to IEC 60068-2-11, test Ka 240 hours at 95% RH Humidity: to IEC 60068-2-3, test Ca	


Description	Item No.	Pack.-unit pcs	Typical time/current characteristics at +23°C/+73.4° F
Thermal circuit breaker, plug-in type, push button reset			
0.10 A AC 250 V DC 65 V	51014625	1	
0.25 A AC 250 V DC 65 V	51011135	1	
0.5 A AC 250 V DC 65 V	51011136	1	
1.0 A AC 250 V DC 65 V	51011137	1	
2.0 A AC 250 V DC 65 V	51011138	1	
3.0 A AC 250 V DC 65 V	51011139	1	
4.0 A AC 250 V DC 65 V	51011140	1	
5.0 A AC 250 V DC 65 V	51017673	1	
6.0 A AC 250 V DC 65 V	51011141	1	
7.0 A AC 250 V DC 65 V	51014524	1	
8.0 A AC 250 V DC 65 V	51011142	1	
10.0 A AC 250 V DC 65 V	51011143	1	
Thermal circuit breaker, plug-in type, on-off switch, switching duty rated			
0.10 A AC 250 V DC 65 V			
0.25 A AC 250 V DC 65 V	51012494	1	
0.5 A AC 250 V DC 65 V	51012495	1	
1.0 A AC 250 V DC 65 V	51012496	1	
2.0 A AC 250 V DC 65 V	51012497	1	
3.0 A AC 250 V DC 65 V	51012498	1	
4.0 A AC 250 V DC 65 V	51012499	1	
5.0 A AC 250 V DC 65 V	51012500	1	
6.0 A AC 250 V DC 65 V	51012501	1	
7.0 A AC 250 V DC 65 V	51014523	1	
8.0 A AC 250 V DC 65 V	51012502	1	
10.0 A AC 250 V DC 65 V	51012503	1	







	Technical Data		Vibration 3 or 4 A: 8 g (57-500 Hz) ±0.65 mm (10-57 Hz) 5...25 A: 10 g (57-500 Hz) ±0.76 mm (10-57 Hz), to IEC 60068-2-6, test Fc, 10 frequency cycles/axis Shock 3 or 4 A: 35 g (11 ms) 5...25 A: 50 g (11 ms) to IEC 60068-2-27, test EA Corrosion: 96 hours at 5% salt mist, to IEC 60068-2-11, test Ka Humidity: 240 hours at 95% RH to IEC 60068-2-3, test Ca
	Voltage rating: DC 28 V Current ratings: 3...25 A (30 A upon request) Typical life: 6,000 operations at I_N 3,000 operations at $2 \times I_N \leq 20$ A 1,000 operations at $2 \times I_N \leq 25$ A Ambient temperature: -30...+60°C (-22...140°F) Interrupting capacity I_{EN}: 3...15 A 200 A 3...15 A 400 A 20...25 A 400 A		

Description	Item No.	Pack.-unit pcs	Typical time/current characteristics at +23°C/+73.4° F
Miniaturized thermal automotive circuit breaker, color coded, manual release			
15 A DC 28 V	51014338	1	
20 A DC 28 V	51014339	1	
25 A DC 28 V	51014340	1	
Miniaturized thermal automotive circuit breaker, on-off switch			
15 A DC 28 V	51014689	1	

	Technical Data		Vibration: 5 g (57-500 Hz) ±0.38mm (10-57 Hz) (with mounting socket 12) to IEC 60068-2-6, Test Fc, 10 frequency cycles/axis Shock: 25 g (11 ms) (with mounting socket 12) to IEC 60068-2-27, Test Ea Corrosion: 96 hours at 5% salt. mist, to IEC 60068-2-11, test Ka Humidity: 240 hours at 95% RH to IEC 60068-2-3, test Ca
	Voltage rating: DC 32 V Current ratings: 6...30 A Service short-circuit breaking capacity: 300 operations at ≤ 50 A Ambient temperature: -30...+60°C (-22...140°F) Ultimate short-circuit breaking capacity: ≥ 3 break operations at 150 A, or ≥ 1 break operation at 2,000 A		

Description	Item No.	Pack.-unit pcs	Typical time/current characteristic curve
Thermal automotive circuit breaker, color coded housing, standard fuseblock mounting			
15 A DC 28 V	51016020	1	
20 A DC 28 V	51014617	1	
25 A DC 28 V	51014618	1	
30 A DC 28 V	51014619	1	

Base Terminal Blocks	Item No.	Description	Pack.-unit pcs
	282-696	2-conductor circuit breaker terminal block, gray	25
	282-698/281-413	...with 24 V indicator, tripped circuit	25
	51012247	...with 110 V indicator, tripped circuit	25

Accessories	Item No.	Pack.-unit pcs	Item No.	Pack.-unit pcs	Item No.	Pack.-unit pcs		
End plate, 2 mm /0.079 in thick 	282-333 orange	100 (4 x 25)	Adjacent jumper, insulated, I_N 41 A 	282-402 gray	100 (4 x 25)	Alternate jumper, insulated, I_N 41 A 	282-409 gray	100 (4 x 25)
	282-334 gray	100 (4 x 25)		249-116	100 (4 x 25)		210-112	10
Test plug adapter, for test plug 4 mm /0.157 in Ø 	209-170	50 (2 x 25)	End stop, for DIN 35 rail 	249-117	50 (2 x 25)	DIN Rail, 35 mm x 7.5 mm, slotted, 2 M long 		

WAGO Service Worldwide

Germany

WAGO Kontakttechnik
Minden
Tel. ++0571/887-443
Fax ++0571/887-541

Austria

WAGO Kontakttechnik
GmgH Wien
Tel. ++43/1/615 07 80
Fax ++43/1/615 07 75

Belgium

WAGO Kontakttechnik
Zaventem
Tel. ++32/2/7 17 90 90
Fax ++32/2/7 17 90 99

China

WAGO ELECTRONIC Co. Ltd.
Tianjin
Tel. ++86/22/82125854/64/74
Fax ++86/22/82125984

England

WAGO, Ltd.
Rugby
Tel. ++44/1788/568008
Fax ++44/1788/568050

France

WAGO CONTACT SA.
Paris
Tel. ++33/148172590
Fax ++33/148632520

Italy

WAGO ELETTRONICA SRL
San Lazzaro di Savena (BO)
Tel. ++39/051/625-91-25
Fax ++39/051/625-91-27

Japan

WAGO Co. of JAPAN Ltd.
Tokyo
Tel. ++81/3/3254/8881
Fax ++81/3/3254/8885

Poland

WAGO ELWAG sp. z o. o.
Wroclaw
Tel. ++48/71/33-66-626
Fax ++48/71/33-60-952

Singapore


WAGO Electronic Pte. Ltd.
Singapur
Tel. ++65/2866776
Fax ++65/2842425

Switzerland

WAGO CONTACT SA
Domdidier
Tel. ++65/2866776
Fax ++65/2842425

WAGO Corporation
N120 W19129 Freistadt Road
Germantown, Wisconsin 53022
Telephone: 800 / DIN Rail (346-7245)
Fax: 262 / 255-3232
info.us@wago.com
www.wago.us





• Circuit Breakers

- DIN Rail Mount Pluggable Circuit Breakers