

ShrinKit 321 Basic

Features and Benefits

This compact and handy kit is part of the basic toolbox for every assembler. Its ideal shrink ratio of 3:1 replaces many differently sized tubings.

An application range from 1 mm to 16 mm can be covered with ShrinKit 321 Basic.

Content

This kit contains a selection of widely used black tubing in seven sizes and different lengths.



ShrinKit 321 Basic.

Material Data

Material	Polyolefin, Cross-linked (POX)
Shrink Ratio	3:1
Longitudinal change after shrinkage	+5%/-10% max.
Minimum Shrink Temperature	+90 °C
Operating Temperature	-55 °C to +135 °C
Dielectric Strength	20 kV/mm according to ASTM D 2671
Flammability	Self extinguishing

Technical Table

Article-No.	Comp.	Supplied Ø D	Recov. Ø d	Length (L)	Colour	Number of tubes
380-03001 ShrinKit 321 Basic	1	1.5	0.5	35	Black (BK)	50
	2	6	2	35	Black (BK)	30
Pack Cont.	3	3	1	35	Black (BK)	25
	4	6	2	35	Black (BK)	15
	5	6	2	35	Black (BK)	15
	6	3	1	35	Black (BK)	25
	7	1.5	0.5	35	Black (BK)	50
	8	18	6	80	Black (BK)	5
	8	12	4	80	Black (BK)	5

All dimensions in mm. Subject to technical changes.