

Capacitor, film, 0.22 uF, +/-20% Tol, -40/+110C, Safety: X2, 275 VAC, Lead Spacing=15 mm



| Dimensions (mm) | | |
|-----------------|-----------|-----------|
| Symbol | Dimension | Tolerance |
| L | 18 | +0.3 |
| H | 12 | +0.1 |
| T | 6 | +0.2 |
| S | 15 | +/-0.4 |
| LL | 30 | +5/-0 |
| F | 0.6 | +/-0.05 |

Notes:

-L,H,T are nominal dimensions and do not imply a minimum.

| General Information | |
|---------------------|--------------------------|
| Supplier: | KEMET |
| Dielectric: | Metallized Polypropylene |
| Application: | Safety: X2 |
| Style: | Radial Box |
| Lead Form: | Wire Leads |
| Approvals: | ENEC,UL,cUL,CQC |
| RoHS: | Yes |

| Specifications | |
|-----------------------------|-----------|
| Capacitance: | 0.22 uF |
| Voltage: | 560 VDC |
| Tolerance: | +/-20% |
| Voltage AC: | 275 VAC |
| Rated Temperature: | 110C |
| Temperature Range: | -40/+110C |
| Dissipation Factor @ 1 kHz: | 0.1% |
| Insulation Resistance: | 100 GOhm |
| Maximum dVdT: | 400 v/us |

| Packaging Specifications | |
|--------------------------|------|
| Package Kind: | Bulk |
| Package Quantity: | 900 |